

INDOOR Single Core Termination Kits



3M™ Cold Shrink QT-III Silicone Rubber Indoor Terminations for use with Compression Lugs

Kit Number	BIL	Cable Insulation O.D. Range Inches (mm)	Conductor Size Range AWG and kcmil (mm ²)				
			5 kV	8 kV	15 kV	25/28 kV	35 kV*

Tape Shield, Wire Shield, UniShield® Cable Kits (Each kit makes three terminations.)

7620-T-95	95 kV	0.32 – 0.59 (8,1 – 15,0)	8 – 4	8 – 6	—	—	—
7621-T-95	95 kV	0.44 – 0.89 (11,2 – 22,6)	2 – 3/0	4 – 2/0	—	—	—
7622-T-95	95 kV	0.64 – 1.08 (16,3 – 27,4)	4/0 – 400	3/0 – 300	—	—	—
7624-T-95	95 kV	0.83 – 1.53 (21,1 – 38,9)	500 – 750	350 – 700	—	—	—
7625-T-95	95 kV	1.05 – 1.80 (26,7 – 45,7)	700 – 1500	600 – 1250	—	—	—
7622-T-110	110 kV	0.64 – 1.08 (16,3 – 27,4)	4/0 – 400	3/0 – 300	2 – 2/0 (35 – 70)	—	—
7623-T-110	110 kV	0.72 – 1.29 (18,3 – 32,8)	300 – 500	250 – 500	2/0 – 300 (70 – 150)	—	—
7624-T-110	110 kV	0.83 – 1.53 (21,1 – 38,9)	500 – 750	350 – 700	4/0 – 500 (120 – 240)	—	—
7625-T-110	110 kV	1.05 – 1.80 (26,7 – 45,7)	700 – 1500	600 – 1250	500 – 1000 (240 – 500)	—	—
7626-T-110	110 kV	1.53 – 2.32 (38,9 – 58,9)	1750 – 2000	1500 – 2000	1250 – 2000 (625 – 1000)	—	—
7693-T-150	150 kV	0.72 – 1.29 (18,3 – 32,8)	300 – 500	250 – 500	2/0 – 300 (70 – 150)	2 – 4/0 (35 – 120)	2 – 2/0 (35 – 70)
7695-T-150	150 kV	1.05 – 1.80 (26,7 – 45,7)	700 – 1500	600 – 1250	500 – 1000 (240 – 500)	250 – 800 (150 – 400)	3/0 – 600 (95 – 325)
7696-T-150	150 kV	1.53 – 2.32 (38,9 – 58,9)	1750 – 2000	1500 – 2000	1250 – 2000 (625 – 1000)	900 – 1750 (500 – 800)	700 – 1500 (400 – 725)

Concentric and Jacketed Concentric Neutral Cable Kits (Each kit makes one termination.)

7642-T-110	110 kV	0.64 – 1.08 (16,3 – 27,4)	4/0 – 400	3/0 – 300	2 – 2/0 (35 – 70)	—	—
7643-T-110	110kV	0.72 – 1.29 (18,3 – 32,8)	300 – 500	250 – 500	2/0 – 300 (70 – 150)	—	—
7644-T-110	110 kV	0.83 – 1.53 (21,1 – 38,9)	500 – 750	350 – 700	4/0 – 500 (120 – 240)	—	—
7645-T-110	110 kV	1.05 – 1.80 (26,7 – 45,7)	700 – 1500	600 – 1250	500 – 1000 (240 – 500)	—	—
7646-T-110	110 kV	1.53 – 2.32 (38,9 – 58,9)	1750 – 2000	1500 – 2000	1250 – 2000 (625 – 1000)	—	—
7653-T-150	150 kV	0.72 – 1.29 (18,3 – 32,8)	300 – 500	250 – 500	2/0 – 300 (70 – 150)	2 – 4/0 (35 – 120)	2 – 2/0 (35 – 70)
7655-T-150	150 kV	1.05 – 1.80 (26,7 – 45,7)	700 – 1500	600 – 1250	500 – 1250 (240 – 625)	250 – 800 (150 – 400)	3/0 – 600 (95 – 325)
7656-T-150	150 kV	1.53 – 2.32 (38,9 – 58,9)	1750 – 2000	1500 – 2000	1250 – 2000 (625 – 1000)	900 – 1750 (500 – 800)	700 – 1500 (400 – 725)

High Fault Current Cable Kits for Tape Shield, Wire-Over-Tape Shield, Longitudinally Corrugated (LC) Shield Cables (Each kit makes one termination.)

7642-T-HSG-110	110 kV	0.64 – 1.08 (16,3 – 27,4)	4/0 – 400	3/0 – 300	2 – 2/0 (35 – 70)	—	—
7643-T-HSG-110	110 kV	0.72 – 1.29 (18,3 – 32,8)	300 – 500	250 – 500	2/0 – 300 (70 – 150)	—	—
7644-T-HSG-110	110 kV	0.83 – 1.53 (21,1 – 38,9)	500 – 750	350 – 700	4/0 – 500 (120 – 240)	—	—
7645-T-HSG-110	110 kV	1.05" – 1.80" (26,7 – 45,7)	700 – 1500	600 – 1250	500 – 1000 (240 – 500)	—	—
7646-T-HSG-110	110 kV	1.53 – 2.32 (38,9 – 58,9)	1750 – 2000	1500 – 2000	1250 – 2000 (625 – 1000)	—	—
7653-T-HSG-150	150 kV	0.72 – 1.29 (18,3 – 32,8)	300 – 500	250 – 500	2/0 – 300 (70 – 150)	2 – 4/0 (35 – 120)	2 – 2/0 (35 – 70)
7655-T-HSG-150	150 kV	1.05 – 1.80 (26,7 – 45,7)	700 – 1500	600 – 1250	500 – 1000 (240 – 500)	250 – 800 (150 – 400)	3/0 – 600 (95 – 325)
7656-T-HSG-150	150 kV	1.53 – 2.32 (38,9 – 58,9)	1750 – 2000	1500 – 2000	1250 – 2000 (625 – 1000)	900 – 1750 (500 – 800)	700 – 1500 (400 – 725)

* 150 kV impulse level meets the impulse requirements for 35 kV class equipment where indoor terminations are used.

