

E-Z Bore Self-Feed Bits

NEW PRODUCT



- Double-end replaceable screw point. Choose the right feed for the material you are drilling. Fine thread for hardwoods, coarse thread for fast, effortless drilling even in soft, gummy woods.
- Tapered backside for easier removal.
- Open design won't clog with wood chips.
- Three milled flats for use in portable electric or pneumatic drills and stationary boring machines.
- Shank size = 7/16"

E-Z BORE SELF-FEED BITS

CAT. NO.	UPC NO.	PIPE & CONDUIT SIZE	HOLE DIA.		LENGTH		WEIGHT	
			INCH	MM	INCH	MM	LBS.	KG
149H2-1	01247	1/2"	1"	25.4	5"	127.0	0.3	137
149H2-1-1/8	01250	1/2"	1-1/8"	28.6	5"	127.0	0.3	137
149H2-1-1/4	01249	3/4"	1-1/4"	31.8	5"	127.0	0.3	137
149H2-1-3/8	01252	3/4"	1-3/8"	34.9	5"	127.0	0.4	182
149H2-1-1/2	01248	1"	1-1/2"	38.1	5"	127.0	0.4	182
149H2-1-3/4	01251	1-1/4"	1-3/4"	44.4	5"	127.0	0.5	227
149H2-2	01257	1-1/4"	2"	50.8	5"	127.0	0.6	273
149H2-2-1/8	01260	1-1/2"	2-1/8"	54	5"	127.0	0.7	318
149H2-2-1/4	01258	1-1/2"	2-1/4"	57.2	5"	127.0	0.7	318
149H2-2-9/16	01261	2"	2-9/16"	65.1	5"	127.0	0.8	363
149H2-3	01262	2-1/2"	3"	76.2	5"	127.0	1.1	499
149H2-3-5/8	01263	3"	3-5/8"	92.1	6-1/4"	158.8	2.1	953
149H2-4-5/8	01272	4"	4-5/8"	117.5	6-1/4"	158.8	2.6	1179

E-Z BORE SELF-FEED BITS

CAT. NO.	UPC NO.	DESCRIPTION	HEX SHANK SIZE		HOLE DIA.		WEIGHT	
			INCH	MM	INCH	MM	LBS.	KG
904H2-5-1/2	01266	Bit Extension	7/16"	11.1	5-1/2"	140.0	0.3	137

E-Z BORE SELF-FEED BITS

CAT. NO.	UPC NO.	DESCRIPTION	SCREW POINT SIZE		HOLE DIA.		WEIGHT	
			INCH	MM	INCH	MM	LBS.	KG
149H2-1/4	01254	Screw Point	1/4"	6.4	2"	50.8	0.1	45
149H2-3/8	01271	Screw Point	3/8"	9.5	2-3/4"	69.9	0.1	45

E-Z Bore Self-Feed Bits Kit

NEW PRODUCT

149H2KIT
Contractor Bit Kit



- Complete assortment of the most commonly used E-Z Bore® bits.
- High-impact, rugged plastic carrying case.
- Full complement of accessories conveniently stored.

E-Z BORE SELF-FEED BIT KIT

CAT. NO.	UPC NO.	DESCRIPTION	PIPE & CONDUIT SIZE	HOLE DIA.		WEIGHT	
				INCH	MM	LBS.	KG
149H2KIT	01273	Contractor Bit Kit	1/2" to 2"	1" to 2-9/16"	25.4 to 65.1	6.0	2.72
34997	34997	Plastic Case					