

4800DW Endothermic Firestop Caulking

PRODUCT DESCRIPTION

PFP Partners' 4800DW is a one-component endothermic firestop sealant based on our environmentally friendly chemistry. 4800DW is a latex-based product designed and tested predominately for firestopping construction joints.

4800DW is virtually odourless also provides a flexible seal which is non-reactive with most substrates.

4800DW can be used on a variety of construction material substrates and removes the guesswork by having one universal product solution for almost all applications.

4800DW is non-hazardous, safe for the environment and does not require special shipping procedures. It does not contain solvents and is VOC compliant. Cleaning up is easy with just soap and water (non-cured state.)

Meets the green building guidelines for adhesives and sealants as specified by both the US and Canada Green Building Council's LEED (Leadership in Energy and Environmental Design) Green Building Rating Systems.

GENERAL APPLICATION AND USES

4800DW has been designed specifically to seal through-penetrations of pipes, cables, HVAC ducts and construction joints against the spread of fire, smoke, fumes and toxic gases in 1, 2, 3 & 4 hour rated floor and wall assemblies.

4800DW has been tested in hundreds of firestopping installations by third party testing agencies; Underwriters Laboratories (UL & ULC) and Intertek Testing Services - Warnock Hersey (WHI) and meets the requirements of ASTM E-84, ASTM E-119, ASTM E-814, ASTM E-1399, CAN/ULC S101, CAN/ULC S102, CAN/ULC S115, UL 263, UL 763, UL 1479 & UL 2079.

Refer to UL or WHI respective published Fire Resistance Directories or their websites. PFP Partners recommends that this product be installed by those trained in proper installation procedures (TQ Card) and be able to read and understand a firestop system design listing (i.e. UL and/or WHI listing designs).

Tested and Classified for use in Fire Rated Assemblies:

- Concrete Floors
- Concrete Walls
- Framed Floors
- Framed Walls

Firestopping Penetration Items:

- Voids
- Electrical, cables, cable trays, busways
- Metallic pipe, conduit and tubing
- Insulated pipe or tubing
- Mechanic ducts
- Grouped penetrations

Firestopping Joints:

- Bottom-of-Wall
- Floor-to-Floor
- Floor-to-Wall
- Head-of-Wall
- Wall-to-Wall

PRODUCT FEATURES

- Water based formulation
- Elastic properties – non-hardening
- Environmental Safe – No harmful components, solvent free and is VOC compliant – LEEDs – California Air Resource Board SCM Districts – Rule 113 – South Coast Air Quality Management Districts (SCAQMD)
- Can be shipped without restriction and is environmentally friendly
- Inert formula will not interact with substrates
- Works on virtually every base material
- Improves STC Values and upgrades sound quality
- Product is stable over several freeze/thaw cycles; however, care should be taken to not freeze the product
- Cured product is mold and mildew resistant
- Easily installed
- Product flows readily, does not slump or sag, easy to tool
- Accepts primer and paint unlike silicone based sealants
- Easy cleanup with water and soap (in wet stage)
- Post-consumer recyclable

SECTION CONTENTS	Page No.
General Information	1
Technical Data	2
Installation Guidelines and Suggested Use	3
Estimating Charts.....	3
Ordering Information.....	4



4800DW – Endothermic Caulking

PACKAGING

- 10 fl. oz. (300 ml) cartridge
- 20 fl. oz. (600 ml) foil sausage pack
- 29 fl. oz. (850 ml) cartridge
- 5 us gal. (18.9 L) pail (tapered)

COLOR

Rust Red

SPECIAL ORDER COLORS

Blue, Grey, White and Yellow
Minimum quantity orders required

Disclaimer: All technical advices, recommendations and services rendered by the seller are gratis. They are based on technical data which the seller believes to be reliable and are intended for use by person having the skills and know how at their own discretion and risk. In no event will the seller be liable for any consequential damages arising out of the use of this product.



Recycled
Recyclable



1.800.810.1788 Technical Support
1.800.810.1788 Customer Service

www.firestop.com
email: firestop@firestop.com

Passive Fire Protection Partners
1412 Derwent Way Delta, BC V3M 6H9

© 2014 PFP Partners. All rights reserved.

PFP1114-1

PDS - 4800DW

TECHNICAL DATA

Base	Vinyl Acetate Polymers	Color	Rust Red
Shelf Life	24 months when product is stored in its original undamaged, unopened packaging and stored in a cool dry place, 40°F to 90°F (4°C to 32°C). Product and substrates should be warmed to at least 43°F (6°C) prior to installation.	Odour	Mild Latex
Aging Test (ASTM D-1791)	Passed	VOC (less water)	0.25 lbs/us. gal (32.5 g/L)
Storage Temperature	40°F to 90°F (4°C to 32°C)	Solids Content (wt. %)	75 to 79%
Application Temperature	45°F to 90°F (7°C to 32°C)	Elasticity	Up to 33%
In-Service Temperature	Up to 120°F (49°C)	Elongation (ASTM D-2370)	1400%
Curing System	One-component – Air cured	Slump (ASTM D-2202)	Passed
Curing Time (ASTM D-1640)	Dry to touch @ 6 mil 20 to 30 min Fully cured time 7 to 21 days (depending on thickness & environment)	Specific Gravity (ASTM D-1475)	1.40 to 1.50
Chemical Compatibility (ASTM D-543)	Passed	Viscosity (ASTM D-2196)	560,000 to 744,000 cps
Corrosion (ASTM B-117)	Passed	pH (ASTM E-70)	8.0 to 9.0
Freeze-Thaw (ASTM D-2243)	Passed	Surface Burning Characteristics (ASTM E-84)	Flame Spread Index <25 Smoke Development Index <50
Extrudability After Package Aging (Freeze-Thaw Stability) (ASTM C-731)	Passed	Fungus Resistance (wet) (ASTM D-2574)	Passed
		Fungus Resistance (dry) (ASTM D-3273)	Passed
		STC – Breached Wall Recovery (ASTM E-90)	59 Tested in a U411 wall assembly
		Volume Shrinkage (ASTM C-1241)	Passed
		Water Resistance (28 day Solubility Loss)	3%

MAINTENANCE

The 4800DW does not require maintenance after installation. If, after installation, the firestop sealant is damaged or cut, repairs should be made with the same sealant. Use only materials approved by through-penetration firestop manufacturer as suitable for repair of original seal. Never mix different manufacturer's firestopping materials.

CHEMICAL COMPATIBILITY

4800DW is chemically compatible with all types of metal, plastic pipe, plastic jacketed wires and cables listed in the system designs.

STORAGE, HANDLING, TRANSPORTATION

Manufacturer recommends storage temperatures between 40°F to 90°F (4°C to 32°C). Keep product stored in a protected covered area in its original containers. Storage in high heat, high humidity conditions may reduce products shelf life. A stock rotation program is recommended. Transportation temperatures 45°F to 85°F (7°C to 30°C) **DO NOT ALLOW TO FREEZE.**

WARRANTY

Passive Fire Protection Partners will not accept liability for more than product refund. Any claim regarding product defect must be received in writing within 1 year from date of shipment. Passive Fire Protection Partners makes no other warranty or guarantee, express or implied, including warranties or fitness for a particular purpose or merchantability. The seller shall assume on other liability for incidental or consequential damages arising out of the sale or use of this product.

Disclaimer: All technical advices, recommendations and services rendered by the seller are gratis. They are based on technical data which the seller believes to be reliable and are intended for use by person having the skills and know how at their own discretion and risk. In no event will the seller be liable for any consequential damages arising out of the use of this product.



General Penetration Estimating – Imperial - Use this chart to calculate the volume of sealant required for each penetration

Diameter of Opening (Inches)	Nominal Diameter of Pipe (inches)												
	0.50	0.75	1.00	1.50	2.00	2.50	3.00	3.50	4.00	6.00	8.00	10.00	12.00
	Actual Diameter of SCH 40 Pipe (inches)												
	0.840	1.050	1.315	1.900	2.375	2.875	3.500	4.000	4.500	6.625	8.625	10.750	12.750
1.00	0.23												
2.00	2.59	2.28	1.78	0.31									
3.00	6.51	6.20	5.71	4.23	2.64	0.58							
4.00	12.01	11.70	11.21	9.73	8.14	6.07	2.95						
5.00	19.08	18.77	18.28	16.80	15.20	13.14	10.01	7.07	3.73				
6.00	27.72	27.41	26.93	25.44	23.84	21.78	18.65	15.71	12.37				
7.00	37.93	37.62	37.13	35.65	34.05	31.99	28.86	25.92	22.58	4.01			
8.00	49.71	49.40	48.91	47.43	45.84	43.77	40.64	37.70	34.36	15.79			
10.00	77.99	77.67	77.18	75.70	74.11	72.05	68.92	65.97	62.64	44.07	20.11		
12.00	112.54	112.23	111.74	110.26	108.67	106.61	103.48	100.53	97.19	78.63	54.67	22.33	
14.00	153.38	153.07	152.58	151.10	151.10	147.45	144.32	141.37	138.03	119.47	95.51	63.18	26.26

4800DW - Volumes

Packaging Size	Volume
10 fl. oz. (300 ml) cartridge	18 cu. in. (300 cm ³)
20 fl. oz. (600 ml) foil sausage pack	36 cu. in. (600 cm ³)
29 fl. oz. (850 ml) cartridge	52 cu. in. (850 cm ³)
5 us gal. (18.9 L) pail (tapered)	1155 cu. in. (18900 cm ³)

ORDERING INFORMATION

4800DW - Packaging

Code	Packaging Size	Color	Dispenser	Units per Case	Units per Skid
DW1	10 fl. oz. (300 ml) cartridge	Rust Red	Caulking Gun	12	1680
DW9	20 fl. oz. (600 ml) foil sausage pack	Rust Red	Caulking Gun	12	720
DW2	29 fl. oz. (850 ml) cartridge	Rust Red	Caulking Gun	12	720
DW4	5 us gal. (18.9 L) pail (tapered)	Rust Red	Bulk Loader / Trowel	1	36

Disclaimer: All technical advices, recommendations and services rendered by the seller are gratis. They are based on technical data which the seller believes to be reliable and are intended for use by person having the skills and know how at their own discretion and risk. In no event will the seller be liable for any consequential damages arising out of the use of this product.

