


# INDUSTRIAL SPEC GRADE TURNLOK® LOCKING DEVICES


## L630C & L630P Connector & Plug

- A. Raised ribs** provide non-slip gripping profile for turning to lock and unlock.
- B. Quick-thread assembly screws** and cord-grip screws come backed-out, ready-to-wire.
- C. Industrial-strength, brass alloy plug blades**, and connector contacts resist heat rise, provide excellent conductivity.
- D. Rounded back contour** reduces snags and hang-ups on the job site.
- E. Impact- and corrosion-resistant** durable nylon 6 shell material.
- F. Integral flexible rubber cord grommet** conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.
- G. New-design external cord grips** provide visible assurance of safe and proper cord retention.
- H. Scallop shell design** provides non-slip gripping surface for insertion and withdrawal.
- I. Double dovetail design** provides superior protection against cord pull-out forces.
- J. Visible stamped NEMA configuration and device rating.**



## L630R Receptacles

- A. Compact, impact-resistant nylon face and body** are ultrasonically welded together for unrivaled strength.
- B. Clearly marked NEMA configuration, rating, and third party listing** on each unit's face.
- C. One-piece, high-grade brass contacts** offer excellent conductivity and heat-rise resistance.
- D. Single-piece, solid brass mounting strap** is free of easily loosened rivets found on other brands.
- E. Side and external screw-pressure-plate back wire capability.** Accepts #14 - #10 AWG.



**F. P&S Turnlok Receptacles.** Voltage color coding on the outside. Proven designs and quality materials on the inside. Any way you look at them, they're the standard of the industry.



# INDUSTRIAL SPEC GRADE TURNLOK® LOCKING DEVICES

## NEMA Configurations

### Locking Plugs & Receptacles

	15 AMPERE		20 AMPERE		30 AMPERE		
	RECEPTACLE	PLUG	RECEPTACLE	PLUG	RECEPTACLE	PLUG	
<b>2 POLE, 2 WIRE NON-GROUNDING</b>							
125V	L1						
	L2						
250V							
<b>2 POLE, 3 WIRE GROUNDING</b>							
125V	L5						
	L6						
250V							
277VAC	L7						
	L24						
347VAC							
480VAC	L8						
	L9						
600VAC							
<b>3 POLE, 3 WIRE NON-GROUNDING</b>							
125/250V	L10						
	L11						
3ø250V							
3ø480V	L12						
	L13						
3ø600V							
<b>3 POLE, 4 WIRE GROUNDING</b>							
125/250V	L14						
	L15						
3ø250V							
3ø480V	L16						
	L17						
3ø600V							
<b>4 POLE, 4 WIRE NON-GROUNDING</b>							
3øY 120/208V	L18						
	L19						
3øY 277/480V							
3øY 347/600V	L20						
<b>4 POLE, 5 WIRE GROUNDING</b>							
3øY 120/208V	L21						
	L22						
3øY 277/480V							
3øY 347/600V	L23						

### Midget – Locking


	15 AMPERE		
	RECEPTACLE	PLUG	
<b>2 POLE, 2 WIRE NON-GROUNDING</b>			
125V	ML1		
<b>2 POLE, 3 WIRE GROUNDING</b>			
125V	ML2		
<b>3 POLE, 3 WIRE NON-GROUNDING</b>			
125/250V	ML3		

### Labels & Their Meaning

X, Y, Z	Hot Lead
W	Neutral Lead
G	Grounding Lead

#### Open Slots

Indicate receptacle configurations (female).




#### Closed Slots

Indicate plug blade configurations (male).



# INDUSTRIAL SPEC GRADE TURNLOK® LOCKING DEVICES

**Watertight Plugs, Connectors & Receptacles** 2 Pole, 3 Wire Grounding 15 & 20A, 125/250, 250 & 277V



## Features

- Thermoplastic elastomer body construction stands up to impacts, oils, chemicals, heat, and weather.
- Large ribs on body for a superior grip when mating.
- Quick-drive assembly screws allow for fast installation, saving time and money.
- NEMA 4, 4X, 6, 6P Watertight. IP65, 66, 67. Rated watertight for 1,500 psi highpressure hose-down.
- Terminal screws backed-out, ready-to-wire, saving time and money.
- Multipoint sealing system between plug and connector ensures protection from water and contaminants.
- Valox compression-type cord grip provides watertight seal and great pull out strength.
- Nickel-plated blades and contacts for long-lasting, superior corrosion resistance.

CATALOG NUMBER	RATING		DESCRIPTION	NEMA CONFIG. NO.	3rd PARTY COMPLIANCE	
	A.	V.			UL498	C22.2 No. 42M
<b>WATERTIGHT PLUGS, CONNECTORS &amp; RECEPTACLES</b>						
24W47	15	125	Plug, Yellow, NEMA 4X/6P	L5-15P	•	•
25W47	15	125	Connector, Yellow, NEMA 4X/6P	L5-15R	•	•
65W47	15	125	Single Receptacle, Yellow, NEMA 4X/6P	L5-15R	•	•
65W47DPLX	15	125	Duplex Receptacle, Yellow, NEMA 4X/6P	L5-15R	•	•
26W47	20	125	Plug, Yellow, NEMA 4X/6P	L5-20P	•	•
27W47	20	125	Connector, Yellow, NEMA 4X/6P	L5-20R	•	•
67W47	20	125	Single Receptacle, Yellow, NEMA 4X/6P	L5-20R	•	•
28W47	30	125	Plug, Yellow, NEMA 4X/6P	L5-30P	•	•
29W47	30	125	Connector, Yellow, NEMA 4X/6P	L5-30R	•	•
69W47	30	125	Single Receptacle, Yellow, NEMA 4X/6P	L5-30R	•	•
24W49	15	250	Plug, Yellow, NEMA 4X/6P	L6-15P	•	•
25W49	15	250	Connector, Yellow, NEMA 4X/6P	L6-15R	•	•
65W49	15	250	Single Receptacle, Yellow, NEMA 4X/6P	L6-15R	•	•
65W49DPLX	15	250	Duplex Receptacle, Yellow, NEMA 4X/6P	L6-15R	•	•
26W48	20	250	Plug, Yellow, NEMA 4X/6P	L6-20P	•	•
27W48	20	250	Connector, Yellow, NEMA 4X/6P	L6-20R	•	•
67W48	20	250	Single Receptacle, Yellow, NEMA 4X/6P	L6-20R	•	•
28W48	30	250	Plug, Yellow, NEMA 4X/6P	L6-30P	•	•
29W48	30	250	Connector, Yellow, NEMA 4X/6P	L6-30R	•	•
69W48	30	250	Single Receptacle, Yellow, NEMA 4X/6P	L6-30R	•	•
24W34	15	277	Plug, Yellow, NEMA 4X/6P	L7-15P	•	•
25W34	15	277	Connector, Yellow, NEMA 4X/6P	L7-15R	•	•
65W34	15	277	Single Receptacle, Yellow, NEMA 4X/6P	L7-15R	•	•
65W34DPLX	15	277	Duplex Receptacle, Yellow, NEMA 4X/6P	L7-15R	•	•
26W49	20	277	Plug, Yellow, NEMA 4X/6P	L7-20P	•	•
27W49	20	277	Connector, Yellow, NEMA 4X/6P	L7-20R	•	•
67W49	20	277	Single Receptacle, Yellow, NEMA 4X/6P	L7-20R	•	•
28W49	30	277	Plug, Yellow, NEMA 4X/6P	L7-30P	•	•
29W49	30	277	Connector, Yellow, NEMA 4X/6P	L7-30R	•	•
69W49	30	277	Single Receptacle, Yellow, NEMA 4X/6P	L7-30R	•	•

