



PRO

The FLOOD-IT™ **PRO** is a portable light that incorporates high quality lithium-ion batteries and COB LED chips giving clear bright light for up to 4 hours on one charge. The **PRO** means you can push on and get the job done, even in the worst conditions.

95FT BEAM RANGE // FL10YCW

- » **SUPER VERSATILE & LIGHTWEIGHT**
- » **RANGE OF AVAILABLE ACCESSORIES**
- » **RECHARGEABLE & CORDLESS**
- » **MAINS & CAR CHARGER INCLUDED**

Light source	10W
Dimensions	145 x 240 x 165 mm // 5.5 x 9.5 x 6.3 inches
Luminous flux	700+ Lm
Color Temperature	5,500 - 6000K
Color rendering index	RA>70
Housing material	Aluminium and iron
Adaptor (input)	100-240V AC 50/60Hz
Operating temperature	-25°C to 50°C // -13°F to 122°F
Charge temperature	0°C to 40°C // 32°F to 113°F
Beam angle	120°
Battery specifications	7.4V 4.4Ah Li-ion
Charging time	5 Hours
Working time	4 Hours*
Certificates	CE / RoHS / UL / CSA / IP65
Warranty	2 Years



*Battery life may vary based on your use

PRIME

130FT BEAM RANGE // FL20YCW

The **PRIME** is a high power LED light that offers a robust and reliable solution to portable lighting in tough situations. Used by railway maintenance, the coast guard and the emergency services thanks to the lack of trailing leads and generators - just safe portable lighting.

- » **IDEAL FOR LIGHTING A SCENE**
- » **NO TRAILING LEADS**
- » **NO GENERATORS**
- » **MAINS & CAR CHARGER INCLUDED**

Light source	20W
Dimensions	215 x 285 x 185 mm // 8.5 x 11.2 x 7.3 inches
Luminous flux	1500+ Lm
Color Temperature	5,500 - 6000K
Color rendering index	RA>70
Housing material	Aluminium and iron
Adaptor (input)	100-240V AC 50/60Hz
Operating temperature	-25°C to 50°C // -13°F to 122°F
Charge temperature	0°C to 40°C // 32°F to 113°F
Beam angle	120°
Battery specifications	7.4V 8.8Ah Li-ion
Charging time	5 Hours
Working time	4 Hours*
Certificates	CE / RoHS / UL / CSA / IP65
Warranty	2 Years



*Battery life may vary based on your use



FREE CAR CHARGER INCLUDED



FREE CAR CHARGER INCLUDED