

TABLE OF CONTENTS



Crimpers — Battery Actuated

PAT46LWS..... N-8
 PAT46LW N-9
 PAT750..... N-10
 PAT644..... N-11
 PAT81KFT..... N-12
 PAT4PC834..... N-13
 PAT600..... N-14
 PAT500SJ6 Series N-15
 PATMD6 Series N-16
 PATMD6LIWCJ Series N-17
 PATMD6LICUTKIT1 Series N-18
 CSMD6 Series N-19



Crimpers — Self-Contained Hydraulic

Y750HSXT N-20
 Y35..... N-21
 Y39..... N-22
 Y644HSXT N-23
 Y81KFT N-24
 Y4PC834 N-25
 Y500CTHS..... N-26



Y750HSXT

12-Ton, C-Head, HYPRESS™
 Hydraulic Self-Contained, Hand Operated Tool

- 355° head rotation
- 1.65" jaw opening
- Rapid advance pump
- Uses standard BURNDY U dies (sold separately)

For Use On:

Tension Sleeves

Copper	#8 sol. - 500 kcmil
Aluminum	#8 sol. - 587.2 kcmil
ACSR	#4 - 556.5 kcmil

Taps

Copper	#14 sol. - 500 kcmil
Aluminum	#8 - 500 kcmil

Aerial Cable

Copper	#6 - 500 kcmil
--------	----------------

Terminals & Splices

Copper	#8 - 750 kcmil
Aluminum	#8 - 750 kcmil
ACSR	#4 - 556 kcmil

HYGROUNDR® (Compression Grounding)

Copper	#8 - 500 kcmil
Ground Rods	1/2" - 1" diameter

Variations:

Catalog Number:	Description:
Y750HSXT	Standard version
Y750CHSXT	Rubber covered head version



Specifications:

Output Force:	12 Tons
Tool Weight:	14.5 lbs
Size:	24.00" x 8.75" x 2.88"
Die Style:	U style
Jaw Opening:	1.65"
Warranty:	5 year limited warranty

Accessories:

Catalog Number:	Description:
PT10024162:	Plastic carrying case for Y750HSXT/Y750CHSXT
FORCEGAUGE1215:	Force test gauge for accurate reading of output force
PT29291:	Steel die case for U dies