

TYPE YGHA


HYLUG™

Heavy Duty Irreversible Compression  
Terminals

Heavy duty HYLUG™ irreversible compression terminals designed not only to carry short circuit load, but to also withstand high mechanical stress. Each conductor element has an inspection probe hole to ensure proper cable insertion. UL467 Listed. Acceptable for direct burial in earth or concrete. UL486A Listed. Prefilled with PENETROX™ compound and strip sealed.



Now  
IEEE-837  
2014  
Qualified!



IEEE-837



E-21

| Catalog Number | Copper Conductor Size | Installation Tools, Die Set Catalog Number and (# of Crimps)<br>HYPRESS™ Y35/Y39/Y45①/Y46②/Y750/PAT750 | B    | C    | L    | T    |
|----------------|-----------------------|--|------|------|------|------|
| YGHA2C-2N      | 2 AWG                 | U1CRT (1)  | 0.75 | 0.97 | 4.21 | 0.26 |
| YGHA25-2N      | 1/0 AWG               | U27RT (1)  | 0.83 | 0.91 | 4.60 | 0.19 |
| YGHA26-2N      | 2/0 AWG               | U28RT (1)  | 0.83 | 0.97 | 4.38 | 0.26 |
| YGHA27-2N      | 3/0 AWG               | U29RT (1)  | 1.18 | 1.08 | 4.94 | 0.29 |
| YGHA28-2N      | 4/0 AWG               | U30RT (2)  | 1.18 | 1.22 | 4.94 | 0.30 |
| YGHA29-2N      | 250 kcmil             | U31RT (2)  | 1.18 | 1.28 | 4.94 | 0.34 |
| YGHA31-2N*     | 350 kcmil             | U34RT (2)  | 1.18 | 1.62 | 5.00 | 0.43 |
| YGHA34-2N      | 500 kcmil             | U36RT (3)  | 1.48 | 1.72 | 5.42 | 0.40 |

① Where a "U" or "PU" die is recommended with the Y45 HYPRESS™, a PT6515 adapter must be used

② Where a "U" or "PU" die is recommended with the Y46 HYPRESS™, a PUADP-1 adapter must be used

\* IEEE837 2002 Qualified