

# HARDWARE THREADED ROD 50


## All Thread Rod

- Size Range: 1/4" thru 7/8"
- Surface Finish: Plain and Electro-zinc Plated
- Attaches hangers to structural attachments without threading the rod, UNC Thread Form

**NOTE:** Low carbon: tensile: 58,000 psi; yield: 36,000 psi, available in Stainless Steel for 3/8" and 1/2" rod size



Part Number	RS	L	Max. Rec. Load (lbs)*
Plain Finish			
0502506PL	1/4"	6'	240
0502510PL	1/4"	10'	240
0502512PL	1/4"	12'	240
0503706PL	3/8"	6'	610
0503710PL	3/8"	10'	610
0503712PL	3/8"	12'	610
0505006PL	1/2"	6'	1130
0505010PL	1/2"	10'	1130
0505012PL	1/2"	12'	1130
0506206PL	5/8"	6'	1810
0506210PL	5/8"	10'	1810
0506212PL	5/8"	12'	1810
0507506PL	3/4"	6'	2710
0507510PL	3/4"	10'	2710
0507512PL	3/4"	12'	2710
0508706PL	7/8"	6'	3770
0508710PL	7/8"	10'	3770
0508712PL	7/8"	12'	3770
Electro-zinc Plated Finish			
0502506EG	1/4"	6'	240
0502510EG	1/4"	10'	240
0502512EG	1/4"	12'	240
0503706EG	3/8"	6'	610
0503710EG	3/8"	10'	610
0503712EG	3/8"	12'	610
0505006EG	1/2"	6'	1130
0505010EG	1/2"	10'	1130
0505012EG	1/2"	12'	1130
0506206EG	5/8"	6'	1810
0506210EG	5/8"	10'	1810
0506212EG	5/8"	12'	1810
0507506EG	3/4"	6'	2710
0507510EG	3/4"	10'	2710
0507512EG	3/4"	12'	2710
0508706EG	7/8"	6'	3770
0508710EG	7/8"	10'	3770
0508712EG	7/8"	12'	3770



\*Load based on Max. 650° F

# HARDWARE THREADED STUD 51

## Threaded Studs

- Size Range: 3/8" and 1/2" rod sizes
- Surface Finish: Plain
- Attaches hangers to structural attachments without threading or cutting the rod, UNC Thread Form

**NOTE:** Low carbon: tensile: 58,000 psi; yield: 36,000 psi



Part Number	RS	L	Max. Rec. Load (lbs)*
0513702PL	3/8"	2"	610
0513703PL	3/8"	3"	610
0513704PL	3/8"	4"	610
0513705PL	3/8"	5"	610
0513706PL	3/8"	6"	610
0515004PL	1/2"	4"	1130
0515005PL	1/2"	5"	1130
0515006PL	1/2"	6"	1130
0515010PL	1/2"	10"	1130
0515012PL	1/2"	12"	1130

\*Load based on Max. 650° F

