

### Features

- One-piece die-cast aluminum housing and lens frame. Lens frame fully gasketed, internally hinged and secured with four captive stainless steel hex-head screws for weatherproofing and leaves both hands free for service. Standard finish is Duraplex II™ bronze electrostatic powder coat, optional colours available.
- Lens is a clear, tempered, shock and heat resistant soda lime glass, permanently sealed with silicone to the lens frame.
- Porcelain, 4kV pulse rated, grip-type Mogul base socket prevents lamp loosening.
- HID ballast, class H insulation, high power factor, CWA.
- HID lamps are ED28, Metal Halide & Pulse Start MH, ED23-1/2 & E18 for High Pressure Sodium.
- Reflectors come in three distribution options:
  - Square (Standard)
  - Wide x Narrow (V/N)
  - Cutoff (C)
- Available in two mounting configurations:
  - **Adjustable Tenon Mount:** Die-cast aluminum construction, powder finished same as fixture, with 180° of adjustability. For 2" (2-3/8" OD) pipe or tenon. Includes fully enclosed wiring compartment with access plate.
  - **Yoke Mount:** Heavy gauge steel, powder finished same as fixture. Supplied standard with 3ft. SOW 16/3 cable.
- EPA: Effective Projected Area: 1.0 ft² [0.093m²]
- 3 year limited warranty.

Available up to 400W Metal Halide, Pulse Start Metal Halide & High Pressure Sodium



CSA Approved for Wet Locations  
Yoke Mount IP65 Tested & Certified

### Job Information

### Type:


**Job Name:**

**Cat. No.:**


**Lamp(s):**

**Notes:**

### Dimensions



### Yoke Mounting Pattern



### Ordering information

Explanation of catalog number: Example: PF3Y400WNLXLTRP-6W

<div>PF</div>	<div>3</div>	<div></div>	<div></div>	<div></div>	<div></div>	<div></div>	-	<div></div>	<div></div>
<b>Series:</b> <b>PF:</b> Pentaflood	<b>Size:</b> 3	<b>Mounting:</b> <b>A</b> = Adjustable Tenon <b>Y</b> = Yoke <sup>2</sup>	<b>Wattage<sup>1</sup>:</b> <b>070</b> = 70W <b>100</b> = 100W <b>150</b> = 150W <b>175</b> = 175W <b>250</b> = 250W <b>320</b> = 320W <b>350</b> = 350W <b>400</b> = 400W	<b>Reflector Type:</b> <b>Blank</b> = Square <b>WN</b> = Wide x Narrow <b>C</b> = Cutoff	<b>Source:</b> <b>MA</b> = Metal Halide <b>LX</b> = High Pressure Sodium <b>PS</b> = Pulse Start Metal Halide	<b>Options:</b> <b>L</b> = Lamp Included <b>AM</b> = Automatic Quartz Socket & Relay (Lamp not supplied) <b>EM</b> = Emergency Auxiliary Quartz Socket only (150W max.) <b>FS</b> = Single Line Fusing (120, 277, 347V only) <b>TLR</b> = Twist lock photocontrol receptacle <b>TRP</b> = Twist lock receptacle & photocontrol <b>PCB</b> = Button Photocontrol (for 120 or 277V only)		<b>Voltage:</b> <b>1</b> = 120V <b>2</b> = 208V <b>3</b> = 240V <b>4</b> = 277V <b>5</b> = 480V <sup>3</sup> <b>6</b> = 347V <b>7</b> = 600V <sup>3</sup> <b>T</b> = Tri-Tap (120/277/347V)	<b>Finish:</b> <b>Blank</b> = Bronze <b>W</b> = White <b>B</b> = Black <b>G</b> = Grey

<sup>1</sup> MA (175, 250, 400W); LX (70, 100, 150, 250, 400W); PS (200, 250, 320, 350, 400W)

<sup>2</sup> Supplied with 3' SOW 16/3 cable.

<sup>3</sup> 480V & 600V are available up to 250W max. Not available in 400W



Canlyte  
 3015 Louis-Amos, Lachine, Québec H8T 1C4  
 canlyte-info@philips.com • (514) 636-0670 • www.canlyte.com  
 SD0826 June 30, 2011.  
 Specifications are subject to change without notice.  
 © Koninklijke Philips Electronics N.V., 2011. All rights reserved.

### Job Information

### Type: