

EYS 25% * Fill Vertical Sealing Fittings for Close Turning Radius

Explosionproof, Dust-Ignitionproof, Raintight









UNILETS™ for Use with Threaded Rigid Metal Conduit and IMC.


NEC/CEC:

Class I, Division 1 and 2, Groups A◇, B, C, D

Class II, Division 1 and 2, Groups E, F, G

Class III

| | | Trade Size (Inches) | Millimeters (Inches) | | | Kwiko™ A Cement Required Grams (Ounces) | Catalog Number Grayloy™-Iron |
|---|------|-------------------------------------|----------------------|------------------|--|---|--|
| | | A (Length) | B (Width) | Turning Radius ① | | | |
| EYS Vertical Sealing Fittings (25% fill) | | | | | | | |
| | | Female | | | | | |
|  | 1/2 | 83.3 (3.28) | 31.7 (1.25) | 41.4 (1.63) | | 28.4 (1.00) | EYS-1  |
| | 3/4 | 93.7 (3.69) | 38.1 (1.50) | 48.5 (1.91) | | 56.8 (2.00) | EYS-2  |
| | 1 | 109.4 (4.31) | 44.4 (1.75) | 60.4 (2.38) | | 85.1 (3.00) | EYS-3  |
| | | Male/Female (Removable Male Nipple) | | | | | |
|  | 1/2 | 83.3 (3.28) | 31.7 (1.25) | 41.4 (1.63) | | 28.4 (1.00) | EYS-16  |
| | 3/4 | 93.7 (3.69) | 38.1 (1.50) | 48.5 (1.91) | | 56.8 (2.00) | EYS-26  |
| | 1 | 109.4 (4.31) | 44.4 (1.75) | 60.4 (2.38) | | 85.1 (3.00) | EYS-36  |
| Female | Male | | | | | | |



* Per NEC 501.15(C)(6), seals in Class I, Division 1 and 2 must be limited to conductor fill of 25% of cross sectional area of a rigid metal conduit of the same trade size unless approved for higher percentage fill. See 40% fill sealing fittings.

① Turning radius with cover or plug removed.

◇ Indicates items in the shaded area which are UL Listed for Class I, Groups A, B, C, D; Class II, Groups E, F, G; and Class III.