



OVWP LED LED Wall Sconce



Catalog
Number

Notes

Type


Hit the Tab key or mouse over the page to see all interactive elements.

Introduction

The OVWP luminaire is compact and energy efficient, great for replacing up to 70W MH while saving 85% in energy costs. A photocell built into this luminaire makes the OVWP great for Dusk to Dawn operation, in residential single and multi-family applications.

Specifications

Width:	2-3/8" (6 cm)
Height:	8-7/8" (22.5 cm)
Depth:	5-5/16" (13.5 cm)
Weight:	1.5 lbs (0.68 kg)



All dimensions are inches (centimeters) unless otherwise indicated.

Ordering Information

EXAMPLE: OVWP LED 40K 120 PE DDB

Series	Color Temperature	Voltage	Control Options	Finish
OVWP LED	40K 4000K ¹	120 120V	PE Photoelectric cell, button type	DDB HP17 Bronze WH HP17 White

NOTES

- Corrected color temperature (CCT) shown is nominal per ANSI C78, 377-2008.

FEATURES & SPECIFICATIONS

INTENDED USE

The OVWP provides years of maintenance-free general illumination for commercial or residential outdoor applications such as driveways, patios, loading areas and warehouses.

CONSTRUCTION

Rugged cast-aluminum, corrosion-resistant rear mounting plate. Impact resistant polycarbonate front cover/diffuser resists fading and cracking. Driver operates at 120V. Operating temperature -40°C to 40°C. Lenses are engineered for uniform light distribution, uniformity and fixture spacing. See Lighting Facts Labels for specific fixture performance.

FINISH

Available in dark bronze and white.

ELECTRICAL

Light engine consists of long-life, high-efficacy LEDs mounted on an internal aluminum heat sink to maximize heat dissipation and promote long life (L95/100,000 hours at 40°C). Driver and integral photocell operate at 120V and are fully enclosed in the upper housing. There are no user serviceable parts. LEDs maintain 70% of light output at 35,000 hours of service. (LED lifespan based on IESNA LM-80-08 results and calculated per IESNA TM-21-11 methodology.)

INSTALLATION

Designed for wall mount applications more than 4' above the ground. Mounts to a recessed junction box (by others).

LISTINGS

ETL Listed to US and Canadian safety standards for wet locations.

WARRANTY

1-year limited warranty. Complete warranty terms located at: www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx

Note: Actual performance may differ as a result of end-user environment and application. All values are design or typical values, measured under laboratory conditions at 25 °C. Specifications are subject to change without notice.




Photometric Diagrams

To see complete photometric reports or download .ies files for this product, visit the OVWP home page on www.Lithonia.com. Tested in accordance with IESNA LM-79 and LM-80 standards.

LEGEND

- 0.2 fc
- 0.5 fc
- 1.0 fc
- 2.0 fc

OVWP LED 40K 120 PE DDB



Lighting Facts Labels

Lithonia Lighting

LED A Program of the U.S. DOE

lighting facts[®]

Light Output (Lumens) **1242**

Watts **14.1**

Lumens per Watt (Efficacy) **88.09**

Color Accuracy **80**

Color Rendering Index (CRI)

Light Color **4000 (Bright White)**

Correlated Color Temperature (CCT)

2700K 3000K 4500K 6500K

Warm White Bright White Daylight

All results are according to IESNA LM-79-2008: *Approved Method for the Electrical and Photometric Testing of Solid-State Lighting*. The U.S. Department of Energy (DOE) verifies product test data and results.

Visit www.lightingfacts.com for the *Label Reference Guide*.

Registration Number: NJSM-ATIXBP (4/21/2016)
 Model Number: OVWP LED 40K 120 PE XX
 Type: Luminaire - Other