

# ML10/13.SF

[Print View..](#)  
[Print to Pdf..](#)

## General Information

<b>Extended Product Type:</b>	ML10/13.SF
<b>Product ID:</b>	1SNA199095R1300
<b>EAN:</b>	3472591990959
<b>Catalog Description:</b>	ML10/13.SF Screw Clamp Terminal Blocks - For 6.3 x 25 and 6.3 x 32 fuses - Black
<b>Long Description:</b>	ML10/13.SF Screw Clamp Terminal Blocks Fuse



## Categories

Products » Low Voltage Products and Systems » Connection Devices »  
Terminal Blocks » Screw Clamp Terminal Blocks

## Ordering

<b>EAN:</b>	3472591990959
<b>Minimum Order Quantity:</b>	20 piece
<b>Customs Tariff Number:</b>	85361050

## Dimensions

<b>Product Net Width:</b>	13.0 mm
<b>Product Net Height:</b>	85.0 mm
<b>Product Net Depth:</b>	58.0 mm
<b>Product Net Weight:</b>	51.00 g

## Container Information

<b>Package Level 1 Units:</b>	20 piece
<b>Package Level 1 Width:</b>	172 mm
<b>Package Level 1 Height:</b>	71 mm
<b>Package Level 1 Length:</b>	155 mm
<b>Package Level 1 Gross Weight:</b>	1.02000 kg
<b>Package Level 1 EAN:</b>	3472591990959
<b>Package Level 2 Units:</b>	200 piece
<b>Package Level 2 Width:</b>	300 mm
<b>Package Level 2 Height:</b>	300 mm
<b>Package Level 2 Length:</b>	500 mm
<b>Package Level 2 Gross Weight:</b>	10.700 kg
<b>Package Level 3 Units:</b>	4800 piece
<b>Product Packing Type:</b>	Box

## Environmental

<b>RoHS Status:</b>	Following EU Directive 2002/95/EC August 18, 2005 and amendment
---------------------	-----------------------------------------------------------------

## Technical UL/CSA

<b>Maximum Operating Voltage UL/CSA:</b>	Main Circuit 600 V
<b>Connecting Capacity-Main Circuit UL/CSA:</b>	Screw Clamp / Rigid 1x 22-10 AWG
<b>Connecting Capacity UL/CSA:</b>	Screw Clamp / Rigid 22-10 AWG

Flammability According to UL94: V0

---

### Additional Information

---

<b>Color:</b>	Black
<b>Connecting Capacity-Main Circuit:</b>	Screw Clamp / Flexible 1x 0.5-10 mm <sup>2</sup> Screw Clamp / Rigid 1x 0.5-16 mm <sup>2</sup>
<b>Connection Type:</b>	Screw clamp
<b>Function:</b>	Fuse
<b>Gauge Type:</b>	A6
<b>IIT Publishing Status:</b>	Level 0 - Information enabled
<b>Mounting on DIN Rail:</b>	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
<b>Number of Levels:</b>	1
<b>Pollution Degree:</b>	3
<b>Product Main Type:</b>	ML10/13.SF
<b>Product Name:</b>	Terminal block
<b>Rated Cross-Section:</b>	10 mm <sup>2</sup>
<b>Rated Current (I<sub>n</sub>):</b>	Main Circuit 16 A
<b>Rated Impulse Withstand Voltage (U<sub>imp</sub>):</b>	8000 V
<b>Rated Voltage (U<sub>r</sub>):</b>	800 V
<b>Recommended Screw Driver:</b>	5.5 mm
<b>RoHS Date:</b>	20050818
<b>Spacing:</b>	13 mm
<b>Sub-Function:</b>	For 6.3x25 and 6.3x32 Fuses
<b>Wire Stripping Length:</b>	12.0 mm

---

### Certificates and Declarations (Document Number)

---

<b>CSA Certificate:</b>	TBD - OK in Ag.Base
<b>cUL Certificate:</b>	1SND161000A0202
<b>Declaration of Conformity - CE:</b>	1SND225007C1006
<b>GOST Certificate:</b>	1SND161005A1104
<b>RoHS Information:</b>	1SND230023F0206

---

### Classifications

---

<b>ETIM 4.0:</b>	EC000899 - Fuse terminal block
<b>ETIM 5.0:</b>	EC000899 - Fuse terminal block
<b>Object Classification Code:</b>	X

---