


# Datacom/Low Voltage



Datacom/Low Voltage

Cable Capacity			CAT 5e	CAT 6	CAT 6A	CAT 7 (SFTP)	Fibre Optic (plenum)
			(5.2 mm 0.21")	(5.9 mm 0.23")	(7.5 mm 0.30")	(7.4 mm 0.29")	(5.1 mm 0.20")
			Bend Radius Requirement*				
			4xØ	4xØ	4xØ	4xØ	10 - 15xØ
Part Number	Area (in <sup>2</sup> )	Area (mm <sup>2</sup> )	Cable Capacity				
CAT12	0.60	387	16	10	–	–	–
CAT16HP	1.07	690	20	15	10	10	20
CAT21HP	2.29	1,477	50	40	25	25	50
CAT32HP	3.97	2,561	90	60	35	35	90
CAT48HP	9.26	5,974	200	150	80	80	200
CAT64HP	15.48	9,987	330	220	140	140	330
CAT100CM	2 x 1.58	2 x 1,019	70	50	30	30	70
CAT200CM	21	13,548	450	350	215	215	450
CAT300CM	32	20,645	700	525	325	325	700
CAT425	20.43	13,181	425	325	210	210	425
CAT600	3.14	2,026	70	50	30	30	70
CATCR50	2.67	1,723	50	36	–	–	–

\* Verify bend radius requirements with cable manufacturer.

Non-continuous supports may not exceed spacing of 5' (1.5 m) per TIA 569-C.9.7.

Cable capacity is calculated based on a 70% fill rate.

# Datacom/Low Voltage

## Cable Support Systems – CADDY® CABLECAT Cable Support System

### CADDY® CABLECAT J-Hook with Rod/Wire Clip


- Threaded rod attachment with attached CADDY® CABLECAT J-Hook
- Supports low voltage cables



Patent No: 5,740,994

Material: Steel, Spring Steel  
Finish: Pregalvanized, CADDY® ARMOUR



Part Number	Description	
CAT124Z34	3/4" dia, 1/8"–3/8" Flange, 1/4" Rod, #12–#8 Wire	40 pc
CAT126Z34	3/4" dia, 3/8"–7/16" Flange, 3/8" Rod	60 pc

Datacom/Low Voltage

### CADDY® CABLECAT J-Hook with T-Grid Clip


- T-Grid attachment with attached CADDY® CABLECAT J-Hook
- Supports low voltage cables



Patent No: 5,740,994

Material: Steel, Spring Steel  
Finish: Pregalvanized, CADDY® ARMOUR



Part Number	Description	
CAT12TS	3/4" dia	60 pc

