

**Fiber Patch Cords**

**Order Information**



SC Duplex to SC Duplex MM

**SC to SC Patch Cords**

Replace 'X' with standard lengths of **1, 2, 3, 5** or **10** meters

Duplex/Multimode	Catalog No.	Duplex/Singlemode	Catalog No.
SC to SC, 62.5/125	<b>DFPCSCSCXMM</b>	SC to SC Singlemode	<b>DFPCSCSCSXSM</b>
SC to SC, 50/125	<b>DFPCSCSCDXMM</b>		
SC to SC, 50/125, 10GbE	<b>DFPCSCSCEXMM*</b>		

\* 10GbE cords are not available in 10m lengths.

**ST-style to ST-style Patch Cords**

Replace 'X' with standard lengths of **1, 2, 3, 5** or **10** meters.

Duplex/Multimode	Catalog No.	Duplex/Singlemode	Catalog No.
ST to ST-style, 62.5/125	<b>DFPCSTSTCXMM</b>	ST to ST-style Singlemode	<b>DFPCSTSTXSMM</b>
ST to ST-style, 50/125	<b>DFPCSTSTDMM</b>		

**ST-style to SC Patch Cords**

Replace 'X' with standard lengths of **1, 2, 3, 5** or **10** meters.

Duplex/Multimode	Catalog No.	Duplex/Singlemode	Catalog No.
ST-style to SC, 62.5/125	<b>DFPCSTSCXMM</b>	ST-style to SC, Singlemode	<b>DFPCSTSCSXSM</b>
ST-style to SC, 50/125	<b>DFPCSTSCDXMM</b>		

**MT-RJ Patch Cords**


Replace 'X' with standard lengths of **1, 2, 3** or **5** meters.

Duplex/Multimode	Catalog No.	Duplex/Singlemode	Catalog No.
MT-RJ to MT-RJ, 62.5/125	<b>DFPCRJRJCXMM</b>		
MT-RJ to ST-style, 62.5/125	<b>DFPCRJSTCXMM</b>		
MT-RJ to SC 62.5/125	<b>DFPCRJSCCXMM</b>		

**LC Patch Cords**

Replace 'X' with standard lengths of **1, 2, 3** or **5** meters.

Duplex/Multimode	Catalog No.	Duplex/Singlemode	Catalog No.
LC to LC, 62.5/125	<b>DFPCLCLCCXMM</b>	LC to LC, Singlemode	<b>DFPCLCLCCXSM</b>
LC to ST-style, 62.5/125	<b>DFPCLCSTCXMM</b>	LC to ST-style, Singlemode	<b>DFPCLCSTCXSM</b>
LC to SC, 62.5/125	<b>DFPCLCSCCXMM</b>	LC to SC, Singlemode	<b>DFPCLCSCCXSM</b>
LC to LC, 50/125, 10GbE	<b>DFPCLCLCEXMM</b>		
LC to SC, 50/125, 10GbE	<b>DFPCLCSCEXMM</b>		



ST to ST-style Duplex MM

SC Duplex to ST-style Duplex MM



MT-RJ Duplex to SC Duplex MM



LC Duplex to LC Duplex MM



**Hubbell Premise Wiring**

HUBBELL INCORPORATED (Delaware)  
 14 Lord's Hill Road • Stonington, CT 06378-0901 • (860) 535-8326 • 800-626-0005  
 Fax: (860) 535-8328 • Internet site: <http://www.hubbell-premise.com>

**Worldwide Locations**

Hubbell Premise Wiring, Asia Pacific  
 Hubbell Canada Inc.  
 Hubbell Premise Wiring, Central America  
 Hubbell Premise Wiring, China  
 Hubbell Premise Wiring, Colombia  
 Hubbell Premise Wiring, Europe  
 Hubbell Int'l. Inc., Korea Branch

852-2836-7131 Fax: 852-2836-7132  
 905-839-1138 Fax: 905-839-9108  
 506-309-4158 Fax: 506-260-1616  
 8621-6309-0119 Fax: 8621-6309-0122  
 571-245-8940 Fax: 571-340-0925  
 44-01283 500500 Fax: 44-01283 500400  
 82-2-(0)2607-1363 Fax: 82-2-(0)2603-7386

Hubbell Premise Wiring, Latin America  
 Hubbell de Mexico, S.A. de C.V.  
 Hubbell Premise Wiring, Middle East  
 Hubbell-Taian Co., Ltd., Taiwan  
 Hubbell Premise Wiring, Turkey  
 Hubbell Premise Wiring, Venezuela

305-408-4501 Fax: 305-408-8201  
 (5255) 9151-9999 Fax: (5255) 9151-9989  
 971-4-393-4192 Fax: 971-4-393-4194  
 886-2-2522-1862 Fax: 886-2-2522-1872  
 90-216-313-5016 Fax: 90-216-414-8148  
 58-416-680-7453 Fax: 58-281-274-7900



## HUBBELL OptiChannel Patch Cords

50/125MM Laser Optimized  
Fiber Cords Available for  
10GbE Applications.

100% Insertion Loss Tested for  
Optical Performance.



### FEATURES

- SC, ST-style, LC and MT-RJ versions available.
- High quality zirconia ferrules for high performance and superior durability.
- Low mated pair insertion loss - minimum impact on signal budget.
- Wide temperature operating range for environmental stability.
- Precision engineered plastic SC housings for consistent repeatable mating.

### SPECIFICATIONS

- ◆ Mated pair insertion loss:  
MM: <0.35 dB (0.15dB typical).  
SM: <0.35 dB (0.15dB typical).
- ◆ Typical SM mated pair return loss: <-55 dB.
- ◆ Operating/Storage Temperature: 0°C to +75°C.

### STANDARDS/LISTINGS/VERIFICATIONS

- Mating Durability: 500 matings per FOTP-21.
- Cable Retention: >10 lbs. per FOTP-6.
- Optical, mechanical and environmental performance: Meets TIA/EIA-568-B.3 specifications.

Fiber patch cords provide connections from the work area to the wall outlet, or from active equipment to the patch panel. These applications include connecting to network interface cards (NIC), or to a fiber hub, router or switch.

Cords are available as duplex or simplex 62.5/125, 50/125 MM, 50/125 Laser Optimized or SM fibers. We offer ST-style, SC, MT-RJ or LC connectors. All patch cords are factory polished and 100% optically tested for superior performance.

### APPLICATIONS SUPPORTED

- ▲ Intra-building Backbone LAN cross connects.
- ▲ 10Gigabit fiber links (300m 10GbE 50mm fiber).
- ▲ Local and Wide Area Networks.
- ▲ Data transmission.
- ▲ Video systems.
- ▲ Remote optical communications.
- ▲ Process control.