







## SIRIUS 3SE5 Mechanical Position Switches

3SE5, metal enclosures  
Enclosure width 56 mm

Version	Diameter	DT	Modular system	PU (UNIT, SET, M)	PS*	PG	
	mm		Article No.	Price per PU			
<b>Twist actuators</b>							
	<b>Twist actuators</b> , metal (without lever)						
	<ul style="list-style-type: none"> <li>For twist levers and rod actuators, switching right and/or left, adjustable</li> <li>For fork levers, latching</li> </ul>						
		⊕ A	<b>3SE5000-0AH00</b>	1	1 unit	41K	
		⊕ B	<b>3SE5000-0AT10</b>	1	1 unit	41K	
<b>Levers</b>							
	<b>Twist levers 27 mm, offset, type A according to EN 50041</b>						
	Metal lever, plastic roller	19	⊕ A	<b>3SE5000-0AA01</b>	1	1 unit	41K
	Metal lever, high-grade steel roller	19	⊕ A	<b>3SE5000-0AA02</b>	1	1 unit	41K
	Metal lever, high-grade steel roller with ball bearing	19	⊕ B	<b>3SE5000-0AA03</b>	1	1 unit	41K
	Metal lever, 2 plastic rollers	19	⊕ B	<b>3SE5000-0AA04</b>	1	1 unit	41K
	Metal lever, plastic roller	30	⊕ B	<b>3SE5000-0AA05</b>	1	1 unit	41K
	Metal lever, plastic roller	50	⊕ B	<b>3SE5000-0AA07</b>	1	1 unit	41K
	Metal lever, rubber roller	50	⊕ B	<b>3SE5000-0AA08</b>	1	1 unit	41K
	High-grade steel lever, plastic roller	19	⊕ B	<b>3SE5000-0AA11</b>	1	1 unit	41K
	High-grade steel lever, high-grade steel roller	19	⊕ B	<b>3SE5000-0AA12</b>	1	1 unit	41K
	<b>Twist levers 35 mm, offset</b>						
	Metal lever, plastic roller	19	⊕ B	<b>3SE5000-0AA15</b>	1	1 unit	41K
High-grade steel lever, plastic roller	19	⊕ B	<b>3SE5000-0AA16</b>	1	1 unit	41K	
<b>Twist levers 30 mm, straight<sup>1)</sup></b>							
Metal lever, plastic roller	19	⊕ B	<b>3SE5000-0AA24</b>	1	1 unit	41K	
Metal lever, plastic roller	30	⊕ B	<b>3SE5000-0AA26</b>	1	1 unit	41K	
	<b>Twist levers, adjustable length, with grid hole</b>						
	Metal lever, plastic roller	19	⊕ B	<b>3SE5000-0AA60</b>	1	1 unit	41K
	Metal lever, high-grade steel roller	19	⊕ B	<b>3SE5000-0AA61</b>	1	1 unit	41K
	Metal lever, plastic roller	50	⊕ B	<b>3SE5000-0AA67</b>	1	1 unit	41K
	Metal lever, rubber roller	50	⊕ B	<b>3SE5000-0AA68</b>	1	1 unit	41K
	High-grade steel lever, plastic roller	19	⊕ B	<b>3SE5000-0AA62</b>	1	1 unit	41K
	High-grade steel lever, high-grade steel roller	19	⊕ B	<b>3SE5000-0AA63</b>	1	1 unit	41K
	<b>Twist lever, adjustable length</b>						
	Metal lever, plastic roller	19	A	<b>3SE5000-0AA50</b>	1	1 unit	41K
	Metal lever, high-grade steel roller	19	B	<b>3SE5000-0AA51</b>	1	1 unit	41K
	Metal lever, plastic roller	30	B	<b>3SE5000-0AA55</b>	1	1 unit	41K
	Metal lever, plastic roller	50	B	<b>3SE5000-0AA57</b>	1	1 unit	41K
	Metal lever, rubber roller	50	B	<b>3SE5000-0AA58</b>	1	1 unit	41K
	High-grade steel lever, plastic roller	19	B	<b>3SE5000-0AA52</b>	1	1 unit	41K
	High-grade steel lever, high-grade steel roller	19	B	<b>3SE5000-0AA53</b>	1	1 unit	41K
	<b>Fork levers</b> (for switches with snap-action contacts only)						
	2 metal levers, 2 plastic rollers	19	⊕ B	<b>3SE5000-0AT01</b>	1	1 unit	41K
	2 metal levers, 2 high-grade steel rollers	19	⊕ B	<b>3SE5000-0AT02</b>	1	1 unit	41K
	2 high-grade steel levers, 2 plastic rollers	19	⊕ B	<b>3SE5000-0AT03</b>	1	1 unit	41K
	2 high-grade steel levers, 2 high-grade steel rollers	19	⊕ B	<b>3SE5000-0AT04</b>	1	1 unit	41K
	<b>Rod actuators, type D according to EN 50041</b>						
	Aluminum rod, length 200 mm	6	B	<b>3SE5000-0AA80</b>	1	1 unit	41K
	Spring rod, length 200 mm	6	B	<b>3SE5000-0AA81</b>	1	1 unit	41K
	Plastic rod, length 200 mm	6	B	<b>3SE5000-0AA82</b>	1	1 unit	41K

⊕ Positively driven actuator, necessary in safety circuits.

<sup>1)</sup> Can be clinch mounted (turned through 180°, rear of lever).