
8-WAY VERTICAL COAX SPLITTER (2 GHZ)

VM0208 |



FEATURES & BENEFITS

This splitter is designed to be specified into an EN0800 enclosure for basic structured wiring applications, such as multi-dwelling units and small homes.



- Package includes one 8-way 2 GHz coax splitter

SPECIFICATIONS

GENERAL INFO

Finish: Nickel-Plated with Tin Sealed
Number Of Ports: 8
Size: 3.43" x 2.39" x 1.15"
Connection Type: F-Connector
Type: Low Voltage Coax Splitter, Single-Bay
Special Features: 8-Way Vertical Coax Splitter, 2 GHz
Style: Single-Bay Module

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

DIMENSIONS

Depth (US): 1.15"
Height (US): 3.43"
Width (US): 2.39"
Rack Units: Custom MDU enclosure mountable

TECHNICAL INFORMATION

Frequency: Bandwidth: 5~2300 MHz

Material: Cast Alloy

Supported Standards: RoHS

Typical Insertion Loss: Insertion Loss: 16.5~21 dB max

Typical Return Loss: Return Loss, Input: 7~8 dB min; Return Loss, Output: 3.5~10 dB min