














SIRIUS 3SE5 Mechanical Position Switches

3SE5, metal enclosures
Enclosure width 40 mm according to EN 50041

Version	Diameter	DT	Modular system	PU (UNIT, SET, M)	PS*	PG	
	mm		Article No.	Price per PU			
Operating mechanisms							
	Plain plunger						
	High-grade steel plunger	10	⊕ A	3SE5000-0AB01	1	1 unit	41K
	Rounded plungers, type B according to EN 50041						
	High-grade steel plungers, with 3 mm overtravel	10	⊕ B	3SE5000-0AC02	1	1 unit	41K
	Roller plungers, type C acc. to EN 50041						
	High-grade steel roller, with 3 mm overtravel	13	⊕ B	3SE5000-0AD02	1	1 unit	41K
	Roller lever						
	Metal lever, plastic roller	22	⊕ A	3SE5000-0AE01	1	1 unit	41K
	Metal lever, high-grade steel roller	22	⊕ B	3SE5000-0AE02	1	1 unit	41K
	High-grade steel lever, plastic roller	22	⊕ B	3SE5000-0AE03	1	1 unit	41K
	Angular roller lever						
	Metal lever, plastic roller	22	⊕ A	3SE5000-0AF01	1	1 unit	41K
	Metal lever, high-grade steel roller	22	⊕ B	3SE5000-0AF02	1	1 unit	41K
	High-grade steel lever, plastic roller	22	⊕ B	3SE5000-0AF03	1	1 unit	41K
	Spring rods (for switches with snap-action contacts only)						
	Plunger made of plastic, spring of high-grade steel:	7					
	• Length 142.5 mm (spring 50 mm, plunger 50 mm)		B	3SE5000-0AR01	1	1 unit	41K
	• Length 76 mm (spring 23.5 mm, plunger 10 mm)		B	3SE5000-0AR03	1	1 unit	41K
	Twist actuators, metal (without lever)						
	• For twist levers and rod actuators, switching right and/or left, adjustable		⊕ A	3SE5000-0AH00	1	1 unit	41K
	• For fork levers, latching		⊕ B	3SE5000-0AT10	1	1 unit	41K
	Levers						
	Twist levers, offset, type A according to EN 50041						
	Metal lever 27 mm, plastic roller	19	⊕ A	3SE5000-0AA01	1	1 unit	41K
	Metal lever 27 mm, high-grade steel roller	19	⊕ A	3SE5000-0AA02	1	1 unit	41K
	Metal lever 27 mm, high-gr. steel roller with ball bearing	19	⊕ B	3SE5000-0AA03	1	1 unit	41K
	Metal lever 27 mm, 2 plastic rollers	19	⊕ B	3SE5000-0AA04	1	1 unit	41K
	Metal lever 27 mm, plastic roller	30	⊕ B	3SE5000-0AA05	1	1 unit	41K
	Metal lever 27 mm, rubber roller	50	⊕ B	3SE5000-0AA08	1	1 unit	41K
	High-grade steel lever 27 mm, plastic roller	19	⊕ B	3SE5000-0AA11	1	1 unit	41K
	High-grade steel lever 27 mm, high-grade steel roller	19	⊕ B	3SE5000-0AA12	1	1 unit	41K
	Metal lever 35 mm, plastic roller	19	⊕ B	3SE5000-0AA15	1	1 unit	41K
	High-grade steel lever 35 mm, plastic roller	19	⊕ B	3SE5000-0AA16	1	1 unit	41K
		Twist levers 30 mm, straight¹⁾					
Metal lever, plastic roller		19	⊕ B	3SE5000-0AA24	1	1 unit	41K
	Metal lever, plastic roller	30	⊕ B	3SE5000-0AA26	1	1 unit	41K
	Twist levers, adjustable length, with grid hole						
	Metal lever, plastic roller	19	⊕ B	3SE5000-0AA60	1	1 unit	41K
	Metal lever, high-grade steel roller	19	⊕ B	3SE5000-0AA61	1	1 unit	41K
	Metal lever, rubber roller	50	⊕ B	3SE5000-0AA68	1	1 unit	41K
	High-grade steel lever, plastic roller	19	⊕ B	3SE5000-0AA62	1	1 unit	41K
	Twist lever, adjustable length						
	Metal lever, plastic roller	19	A	3SE5000-0AA50	1	1 unit	41K
	Metal lever, high-grade steel roller	19	B	3SE5000-0AA51	1	1 unit	41K
	Metal lever, plastic roller	30	B	3SE5000-0AA55	1	1 unit	41K
	Metal lever, rubber roller	50	B	3SE5000-0AA58	1	1 unit	41K
	High-grade steel lever, plastic roller	19	B	3SE5000-0AA52	1	1 unit	41K
	Twist lever, adjustable length						
	High-grade steel lever, high-grade steel roller	19	⊕ B	3SE5000-0AA63	1	1 unit	41K
	Twist lever, adjustable length						
	Metal lever, plastic roller	19	A	3SE5000-0AA50	1	1 unit	41K
	Metal lever, high-grade steel roller	19	B	3SE5000-0AA51	1	1 unit	41K
	Metal lever, plastic roller	30	B	3SE5000-0AA55	1	1 unit	41K
	Twist lever, adjustable length						
	Metal lever, rubber roller	50	B	3SE5000-0AA58	1	1 unit	41K
	High-grade steel lever, plastic roller	19	B	3SE5000-0AA52	1	1 unit	41K
	High-grade steel lever, high-grade steel roller	19	B	3SE5000-0AA53	1	1 unit	41K
	Fork levers (for switches with snap-action contacts only)						
	2 metal levers, 2 plastic rollers	19	⊕ B	3SE5000-0AT01	1	1 unit	41K
2 metal levers, 2 high-grade steel rollers	19	⊕ B	3SE5000-0AT02	1	1 unit	41K	
2 high-grade steel levers, 2 plastic rollers	19	⊕ B	3SE5000-0AT03	1	1 unit	41K	
	Rod actuators, type D according to EN 50041						
	Aluminum rod, length 200 mm	6	B	3SE5000-0AA80	1	1 unit	41K
	Spring rod, length 200 mm	6	B	3SE5000-0AA81	1	1 unit	41K
	Plastic rod, length 200 mm	6	B	3SE5000-0AA82	1	1 unit	41K

⊕ Positively driven actuator, necessary in safety circuits.

¹⁾ Can be clinch mounted (turned through 180°, rear of lever).

* You can order this quantity or a multiple thereof.
Illustrations are approximate