



Copper H-Tap Connectors for Copper Conductors

Copper H-Taps – Certified to 600 V

Material: High-Conductivity Extruded Copper

Finish: Electro-Tin Plated



Cat. No.	Fig. No.	Colour Code	Dimensions in. (mm)				Crimping Information						
			Main	Branch 1	Branch 2	Branch 3	Hydraulic Head	Installing Die	# of Crimps	Colour Code	Die Code	Strip Length (in.)	Insulating Covers
CHT750350-1F	1	White	(750-500) (750) Flex Only	(750-500) (350) Flex Only	-	-	TBM151	15620CHF	1	White	F	1-1/8	HTC
CHT750350-2	2	Yellow	750-500 (550-500)	750-500 (550-500)	-	-		15620CH		Yellow	Z	1-3/8	
CHT75010-3	9	Brown	500-250 (350-4/0)	500-4/0 (350-4/0)	-	-		15612CH	2	Brown	N	1-1/8	
CHT50040-4	2			500-4/0 (350-4/0)	250-1/0 (4/0-1/0)	1 Str. 2-6 AWG (1-8)							8-14 (8-14)
CHT50010-5	3	500-4/0 (350-4/0)	250-1/0 (4/0-1/0)	1 Str. 2-6 AWG (1-8)	8-14 (8-14)								
CHT2502-6	2	Purple	250-2 (4/0-2)	250-2 (4/0-2)	-	-	•TBM151 TBM14M	15CA80RCH	1	Purple	80R	13/16	HTC40
CHT25014-7	4			2-6 Str./Sol. (2-8)	-	-						1-1/8	
CHT250214-8	5			8-14 (8-14)	-	-						-	
CHT214-9	6	Brown	2-6 Str./Sol. (2-8)	2-6 Str./Sol. (2-8)	8-14 (8-14)	8-14 (8-14)	•TBM151 TBM14M 13100A	15CA71RCH	3	Brown	71R	7/8	HTC2C
CHT814-10	7	Green	8-14 (8-14)	8-14 (8-14)	-			15CA37RCH				1	
CHT75040-11	8	Yellow	750 Str. (750-500)	350-4/0 Str. Cu and Flex	-		-	TBM151	15620CH	1	Yellow	Z	1-1/8

* Requires adaptor Cat. No. 15500-TB when used with hydraulic head TBM151.
Material: Copper per ASTM designation B-124-55 Alloy 12.
Tooling: pp. E4-E62
Die Selector Chart: pp. E35-E50

Copper H-Tap Connectors for Copper Conductors

Copper H-Taps – Certified to 600 V 90°C Applications

- H-type compression taps
- For aluminum-to-aluminum, aluminum-to-copper and copper-to-copper stranded-conductor applications
- Concentric and compact code strandings

Exclusive FILLERLOK tab design.

Material: High-Conductivity
Wrought Aluminum



Cat. No.	Combinations			Length (in.)	Die Code Cat. No.				Colour Code	
	Main	Branch	Side Tap		TBM6-TBM6S TBM6ORS	Hydraulic TBM14M 13100A	TBM12 12-TON HEAD	TBM15I 15-TON HEAD		
63105†	2-6	8-14	-	3/4	13474 upper 13477 lower	15530	TBM12D-4	15530*	Orange	
63110	4-6	4-6		1-1/2	13470	15501A	TBM12D-H	15001A*	Green	
63118	2/0-2	8-14		3/4						
63125	2/0-2	1/0-6		1-1/2						
63140	4/0-2/0	2-10			13471	15502	15502*	Blue		
63148•	4/0-2/0	3/0-1		8-14	3	-	-	-	15502	Red
63160	500-4/0	4/0-2		2-6	2-3/4				15612	
63169	750-4/0	750-4/0	-	3	15620				Black	
63170	1000-500	1000-1/0	-	6						
63180	750-350	350-1/0	1-6	3						

* Use with adaptor Cat.No.15500-TB.

† 63105 also installed by TBM5/TBM5S with 13455 die or TBM8/TBM8S with 13462 die.

• 63148 – #1 CU or AL - wire bent double (hairpin).

For Smart™ Tools Installation

63110,63118,63125: Use TBM8-750HG

63140,63148:Use TBM8-750BH

Tooling: pp. E4-E62

Die Selector Chart: pp. E35-E50