

SMT402AD | MAESTRO™

SMART THERMOSTAT

4000 W



MAESTRO™



ORCHESTRATING COMFORT

Use the Maestro thermostat with the Maestro controller•thermostat to turn your house into a smart home in a snap! Indeed, the Maestro thermostat reveals its full potential when it's paired with the Maestro controller•thermostat. It can also be linked to an existing Zigbee network controlled by any Zigbee-compatible controller. Maestro is the smart home comfort solution!



COMPATIBLE WITH MAESTRO CONTROLLER OR ZIGBEE HUB
CONTROL AT YOUR FINGERTIPS WITH YOUR SMARTPHONE OR MOBILE DEVICE



RELATIVE ROOM HUMIDITY DISPLAY



ENERGY CONSUMPTION REPORTS†
FOR OPTIMAL ENERGY EFFICIENCY



ELECTRICITY SAVINGS
ENERGY SAVINGS UP TO 25%
DEPENDING ON USE*

COMPATIBILITY

- Maestro controller•thermostat or Zigbee hub required
- Zigbee 3.0

COLOUR

- white

FINISH

- molded plastic

WATTAGE AND VOLTAGE

- 150 W to 2000 W @ 120 V
- 260 W to 3400 W @ 208 V
- 300 W to 4000 W @ 240 V

CONTROL

- Maestro environment options include:
 - outdoor temperature or relative room humidity display
 - energy consumption reports

- lock screen capability
- screen backlighting
- radical temperature decrease detection (open-window feature)
- motion-activated screen
- Zigbee home automation environment compatibility

ACCURACY

- accurate ambient temperature control of ± 0.5 °C (1 °F)
- CSA C828-13
- temperature sensing with thermistor

TEMPERATURE RANGE

- 5 to 30 °C (41 to 86 °F)

WARRANTY

- three years

† with Maestro ecosystem

* study carried out by an independent university team

ACCESSORIES

PRODUCT	DESCRIPTION	PRICE
SMAMPLIZB	Zigbee signal amplifier	96.00
SMREPETZB	Zigbee signal repeater	65.00

COMPATIBLE WITH



FOR HOME AUTOMATED SYSTEM COMPATIBILITIES AND INSTRUCTIONS ON CONNECTING TO YOUR MAESTRO THERMOSTAT, VISIT WWW.STELPRO.COM/MAESTRO.

TECHNICAL SPECIFICATIONS

PRODUCT	WATTS		VOLTAGE	AMPERAGE	FREQUENCY	COLOUR	PACKAGING	UNIT PRICE
CODE	MINIMUM	MAXIMUM	VOLTS	AMPERES	HZ			
SMT402AD	150/260/300	2000/3400/4000	120/208/240	16.7	60	WHITE	BOX	107.00

Dimensions: 5 3/8 in. (137 mm) wide, 5 3/8 in. (137 mm) high and 1 1/4 in. (32 mm) deep

°STELPRO

Stelpro reserves the right to modify descriptions, manufacturing specifications or prices without prior notice. No returns accepted on optional-colour products. For all the latest models and prices, please refer to our website at www.stelpro.com.



FC_SMT402AD_EN_280420