

---

## FEATURES

- Surface-mounted luminaire suitable for industrial, commercial and residential applications.
- Flat bottom, pattern 12 acrylic prismatic diffuser.
- Sturdy one piece construction.
- Low profile design minimizes ceiling shadows and sharp contrast.
- For surface or stem mounting.
- High-gloss, baked white enamel finish.
- Guaranteed for one year against mechanical defects in manufacture.

## SPECIFICATIONS

**BALLAST** — Thermally protected, resetting, Class P, HPF, non-PCB, UL listed, CSA-certified ballast is standard. Energy saving and electronic ballasts are sound rated A.

**WIRING & ELECTRICAL** — Fixture is suitable for damp locations. AWM, TFN or THHN wire used throughout, rated for required temperatures.

**MATERIALS** — Housing formed from code-gauge steel. Diffuser is 100% virgin acrylic. No asbestos is used in this product.

**FINISH** — Five-stage iron-phosphate pretreatment ensures superior paint adhesion and rust resistance. Painted parts finished with high-gloss, baked white enamel.

**LISTING** — Listed and labeled to comply with Canadian Standards.


Specifications subject to change without notice.

Catalog Number	Type

## Commercial Wraparound

# BWX

4' length  
2 lamps



---


## PHOTOMETRICS

Full photometric data on these and other configurations available upon request.


# BWX Commercial Wraparound

## DIMENSIONS

Inches (centimeters). Subject to change without notice.



C = 7/8 (2.22) Dia.K.O.



## ORDERING INFORMATION

Example: **BWX 2 40 120 ES**

**BWX**

Series	Number of lamps	Lamp Type	Voltage	Options
<b>BWX</b> Commercial Wraparound	<b>2</b> Not included	<b>32</b> 32W T8 (48") <b>40</b> 40W T12 (48")	<b>120, 347</b> Others available	<b>ES</b> Energy-saving ballasts (40W lamps only). <b>GEB</b> Electronic ballasts, ≤ 20% THD. <b>GEB10</b> Electronic ballast, ≤ 10% THD. <b>GLR</b> Internal fast-blow fuse. <b>GMF</b> Internal slow-blow fuse.

**BWX**

©1998 Lithonia Lighting, 10/98  
BWX.P65

**LITHONIA LIGHTING**  
 COMMERCIAL & INDUSTRIAL FLUORESCENT LIGHTING  
 P.O. BOX A, CONYERS, GEORGIA 30012, TELEPHONE 770-922-9000, FAX 770-929-8789  
 www.lithonia.com • IN CANADA: 1100 50TH AVE., LACHINE, QUEBEC H8T 2V3