

Model 300GCX

SelecTone® Hazardous Location Amplified Speaker



Federal Signal's Model 300GCX SelecTone® Amplified Speaker is designed to produce tones, digital voice messages and live public address in harsh environments with high ambient noise levels.

The rugged speaker cone and projector are constructed of spun aluminum. The amplification circuitry, tone module, and gain control are contained in a housing constructed of die-cast aluminum. All surfaces are sealed with powder-coat paint. Dust- and moisture-proof gaskets provide protection from the elements.

SelecTone Amplified Speakers are used individually or as part of a plant-wide emergency notification system. The Model UTM Universal Tone Module, with 32 tones, or the TM33 Custom Tone Module is plugged into a single SelecTone Amplified Speaker for stand-alone use or into a SelecTone Command Unit for plant-wide signaling.

For plant-wide signaling, a Connector Kit is installed into each SelecTone Amplified Speaker and wired to a central controller, SelecTone Command Unit or CommCenter® Digital Message Center. Command Units and CommCenters broadcast tones, voice messages, melodies and live public address to an unlimited number of SelecTone Amplified Speakers

Applications for SelecTone include emergency warning, evacuation, start/dismissal, public address, and process control signaling.

FEATURES

- Available in 24VAC/DC, 120VAC and 240VAC
- Reliable, solid-state circuitry
- Digital signal amplification
- Fused input and output
- Built-in gain control, adjustable between 0 dBa to 110 dBa @ 10' (0 dBa to 120 dBa @ 1m)
- Cast copper free aluminum housing, spun aluminum projector
- Type 4X enclosure
- Indoor/outdoor use
- UL 1480 and CSFM Approved
- UL and cUL Listed


MODEL	V O L T A G E	0	S T A N D B Y C U R R E N T *	D E C I I 1 0 '	BELS 1 M
300GCX-024	24VDC 24VAC 50/60Hz	0.67 amps 0.90 amps	50 mA 100 mA	110 110	120 120
300GCX-120	120VAC 50/60Hz	0.20 amps	30 mA	110	120
300GCX-240	240VAC 50/60Hz	0.10 amps	15 mA	110	120

^{*}When used as a powered loud speaker

HAZARDOUS LOCATION RATING: 300GCX


T-CODE AT MAXIMUM AMBIENT TEMPERATURE, °C				
Hazardous Location	40°C	66°C		
Class I, Division 2, Groups A, B, C, D	T3	T2C		
Class II, Division 2, Groups F, G	T6	T6		
Class III	T6	T6		

Hazardous Location Amplified Speaker (300GCX)



Operating Temperature:	-67°F to 150°F	-55°C to 66°C
Rated Power		15 watt
Net Weight: 24VAC/DC 120/240VAC	5.5 lbs 5.5 lbs	2.5 kg 2.5 kg
Shipping Weight: 24VAC/DC 120/240VAC	6.7 lbs 6.7 lbs	3.0 kg 3.0 kg
Height: Width: Depth:	12.4" 7.9" 8.5"	314.0 mm 200.0 mm 216.0 mm

Description	Part Number	
Amplifier Assembly, 24VAC/DC	K2005502A-04	
Transformer, 120VAC	K120857A	
Transformer, 240VAC	K120858A	
Voice Coil, Series C	K8593035A	
Speaker Assembly	K8593082A	



Specify Tone Module:

For stand alone operation **UTM** – Universal Tone Module (Reference page 199 for list of tones) TM33 - Custom Tone Module (Reference page 201 for list of tones)

Specify Connector Kit:

(sold separately) for use in systems Call factory for system design assistance. (Reference page 202 for Connector Kits)

AM25CK – 25 Vrms, 1 Vrms **AM70CK** – 70 Vrms, 1 Vrms **300CK** – 10 Vrms, 1 Vrms **T-300CK** – 2.7 Vrms, 1 Vrms **E-300CK** – 1 Vrms, 1 Vrms