


PHILIPS
Day-Brite
CFI

Industrial

FBD high bay

T8 or T5HO



Project: _____
 Location: _____
 Cat.No: _____
 Type: _____
 Lamps: _____ Qty: _____
 Notes: _____

The Philips Day-Brite / Philips CFI FBD fluorescent high bay is a flexible luminaire designed to meet the needs of today's industrial environment. This luminaire is available with T5HO or T8 lamps. The 95% reflective specular aluminum reflectors and solid body design result in a sturdy and efficient luminaire. A variety of mounting methods and accessories allow the luminaire to be used in many different types of applications.

Ordering guide

Example: FBD654HO-UNV-1/42-EB

Family	Lamp Quantity	Lamp Type/ Wattage	Voltage	Ballast	Options
FBD					
FBD	2 3 4 6 8	32 32WT8 (48") 54HO 54WT5HO (46")	UNV (108-305V) 120 277 347 480	1/2-EB One 2 lamp electronic ballast 1/2-EBH One 2 lamp electronic ballast, high ballast factor (32W T8 only) 1/3-EB One 3 lamp electronic ballast 1/3-EBH One 3 lamp electronic ballast, high ballast factor (32W T8 only) 1/4-EB-2LS One 4 lamp electronic ballast with 2 level switching (54W T5HO only) 1/4-EBH One 4 lamp electronic ballast, high ballast factor (32W T8 only) 2/2-EB Two 2 lamp electronic ballasts 2/2-EBH Two 2 lamp electronic ballasts, high ballast factor (32W T8 only) 2/3-EBH Two 3 lamp electronic ballasts, high ballast factor (32W T8 only) 3/2-EB Three 2 lamp electronic ballasts 3/2-EBH Three 2 lamp electronic ballasts, high ballast factor (32W T8 only) 1/42-EBH One 4 lamp and one 2 lamp electronic ballasts, high ballast factor 1/42-EB One 4 lamp and one 2 lamp electronic ballasts 2/4-EB Two 4 lamp electronic ballasts 2/4-EBH Two 4 lamp electronic ballasts, high ballast factor (32W T8 only)	GLR Fusing, fast blow WC3 Wired 3' Cord WP3 Wired 3' Cord and Plug Assembly (Specify voltage) CMP Center Mount for 3/4" Conduit CMH Center Mount with Hook WT Optional White Reflector E7LP LP550 emerg. ballast T8/T5/T5HO, 430-700 lumens, 120/277V E6LP LP600 emerg. ballast U.S. or Canada market, T8/T5/T5HO, 750-1325 lumens, 120/277V E5LP B50LP emerg. ballast T8, 1375-1400 lumens, 120/277V MD360 Installed motion detector

Accessories (order separately)

- WG-FBD4 4 Lamp Wire Guard
- WG-FBD6 6 or 8 Lamp Wire Guard
- MD360 Motion Detector (120V/277V)
- MD360-480 Motion Detector (480V)
- FBD-4E-1W Single Gasketed Door with Clear Acrylic Lens - 4 lamp units
- FBD-4E-1W-DB21 Single Gasketed Door Frame with Prismatic Lens - 4 lamp units
- FBD-6E-1W Single Gasketed Door with Clear Acrylic Lens - 6 or 8 lamp units
- FBD-6E-1W-DB21 Single Gasketed Door Frame with Prismatic Lens - 6 or 8 lamp units
- FBF/FBE CHAIN KIT 54" chains & V brackets
- FBF/FBE-GRIP5 5' cables & V brackets
- FBD4-GL-DB21 Single Gasketed Door Frame with Prismatic Lens, with Wire Guard and Safety Tether, 4 lamp units
- FBD4-GL Single Gasketed Door Frame with Clear Lens, with Wire Guard and Safety Tether, 4 lamp units
- FBD6-GL-DB21 Single Gasketed Door Frame with Prismatic Lens, with Wire Guard and Safety Tether, 6 or 8 lamp units
- FBD6-GL Single Gasketed Door Frame with Clear Lens, with Wire Guard and Safety Tether, 6 or 8 lamp units
- FBD-CMP Pendant Box and Hook

General Notes

- All options factory installed.
- All accessories are field installed.
- "EBH" for T8 lamps is 1.15-1.2 BF.
- "EB" for T5HO lamps is 1.0 BF.
- Order "FBD4-GL" or "FBD6-GL" if wire guard and door are both required.



FBD fluorescent high bay

T8 or T5HO

Application

- An efficient alternative in industrial lighting applications.

Construction/Finish

- Heavy duty mounting chains or cables with hangers (order separately).
- 95% reflective specular aluminum reflectors maximize luminaire efficiency and control light distribution.
- Steel housing with white polyester powder finish.
- Electronic ballast(s).
- Rotating ring, locking type lampholders for T5HO lamps, locking type for T8 lamps.
- Quarter turn fasteners allow reflector to swing down for easy access to ballasts.

Electrical

- cULus listed suitable for damp locations.
- Open 4 and 6 lamp units are rated for use in 55°C ambient. Open 8 lamp units are rated for use in 50°C ambient. Enclosed units are rated for use in 40°C ambient.

Energy Data

Lamp Watts	Ballast Type	Input Watts
32	1/2-EBH	74
	1/3-EBH	110
	1/4-EBH	146
	2/2-EBH	148
	2/3-EBH	222
	3/2-EBH	222
54	1/2-EB	120
	1/3-EB	182
	1/4-EB	240
	2/2-EB	240
	1/42-EB	360
	3/2-EB	360



FBF/FBE Chain Kits



FBF/FBE-Grip5



Center Mount with 3/4" Conduit ("CMP" option)







Center Mount with Hook ("CMH" option)






MD360

Dimensions

6 Lamp (shown) and 8 lamp



4 Lamp



FBD fluorescent high bay

T8 or T5HO

Photometry

6 Lamp F54T5HO

Efficiency – 91.2%

LER – 73

TER – 37

Catalog No.	FBD654HO-UNV-1/42-EB
Test No.	29065
Medium Spread S/MH	1.3
Lamp Type	F54T5HO
Lumens/Lamp	4400
Ballast Factor	1.0
Input Watts	331

Candlepower

Angle	End	45	Cross
0	10428	10428	10428
5	10522	10309	10283
10	10372	10157	10156
15	10119	9895	9869
20	9785	9534	9242
25	9356	8947	8208
30	8835	8090	7240
35	8240	7090	6452
40	7574	6153	5673
45	6833	5368	4653
50	6049	4541	3680
55	5210	3574	3139
60	4341	2648	2902
65	3446	2213	2408
70	2538	1864	1664
75	1664	1203	995
80	875	603	426
85	270	136	107

Light Distribution

Degrees Luminaire	Lumens	% Lamp	%
0-30	7812	29.6	32.4
0-40	12346	46.8	51.3
0-60	20068	76.0	83.3
0-90	24084	91.2	100.0

Average Brightness

Zone	End	45	Cross
45	16867	13251	11486
55	15855	10876	9553
65	14233	9140	9946
75	11222	8113	6710
85	5407	2724	2143

Comparative yearly lighting energy cost per 1000 lumens – **\$3.38** based on 3000 hrs. and \$.08 pwr KWH.

The photometric results were obtained in the Philips Day-Brite laboratory which is NVLAP accredited by the National Institute of Standards and Technology.

Coefficients of Utilization

EFFECTIVE FLOOR CAVITY REFLECTANCE 20 PER (pfc=0.20)

Ceil	80				70				50				30				10			
Wall	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10			
RCR																				
0	109	109	109	109	106	106	106	106	101	101	101	97	97	97	93	93	93			
1	100	96	93	89	98	94	91	88	90	88	85	87	84	82	83	82	80			
2	92	85	79	74	89	83	78	73	80	75	71	77	73	70	74	71	68			
3	84	75	68	62	82	74	67	62	71	65	61	68	64	60	66	62	59			
4	77	67	59	54	75	66	59	53	63	57	52	61	56	52	59	55	51			
5	71	60	52	47	69	59	52	46	57	51	46	56	50	45	54	49	45			
6	66	54	47	41	64	54	46	41	52	45	41	51	45	40	49	44	40			
7	61	50	42	37	60	49	42	36	48	41	36	46	40	36	45	40	36			
8	57	45	38	33	56	45	38	33	44	37	33	43	37	32	42	36	32			
9	54	42	35	30	52	41	34	30	40	34	30	39	34	29	38	33	29			
10	50	39	32	27	49	38	32	27	37	31	27	37	31	27	36	31	27			

4 Lamp F54T5HO

Efficiency – 92.9%

LER – 71

TER – 37

Catalog No.	FBD454HO-UNV-1/4-EB
Test No.	29068
Medium Spread S/MH	1.3
Lamp Type	F54T5HO
Lumens/Lamp	4400
Ballast Factor	1.0
Input Watts	230

Candlepower

Angle	End	45	Cross
0	6971	6971	6971
5	7153	6819	7106
10	7054	6813	7043
15	6893	6701	6865
20	6653	6411	6340
25	6369	6013	5630
30	6020	5421	4947
35	5612	4789	4395
40	5148	4136	3918
45	4651	3566	3321
50	4110	3070	2614
55	3529	2563	2224
60	2942	1885	2030
65	2329	1494	1616
70	1730	1241	1059
75	1134	780	613
80	609	362	251
85	179	75	69

Light Distribution

Degrees Luminaire	Lumens	% Lamp	%
0-30	5298	30.1	32.4
0-40	8375	47.6	51.2
0-60	13681	77.7	83.6
0-90	16359	93.0	100.0

Average Brightness

Zone	End	45	Cross
45	16992	13028	12133
55	15894	11544	10017
65	14236	9132	9878
75	11319	7785	6119
85	5306	2223	2045

Comparative yearly lighting energy cost per 1000 lumens – **\$3.20** based on 3000 hrs. and \$.08 pwr KWH.

The photometric results were obtained in the Philips Day-Brite laboratory which is NVLAP accredited by the National Institute of Standards and Technology.

Coefficients of Utilization

EFFECTIVE FLOOR CAVITY REFLECTANCE 20 PER (pfc=0.20)

Ceil	80				70				50				30				10			
Wall	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10			
RCR																				
0	111	111	111	111	108	108	108	108	103	103	103	99	99	99	95	95	95			
1	102	98	94	91	100	96	93	90	92	89	87	88	86	84	85	83	82			
2	93	86	80	75	91	85	79	75	81	77	73	78	75	71	76	72	70			
3	86	76	69	64	83	75	68	63	72	67	62	70	65	61	67	63	60			
4	79	68	61	55	77	67	60	54	65	58	54	63	57	53	61	56	52			
5	73	61	53	48	71	60	53	47	58	52	47	57	51	46	55	50	46			
6	67	56	48	42	66	55	47	42	53	46	41	51	46	41	50	45	41			
7	63	51	43	37	61	50	42	37	48	42	37	47	41	37	46	40	36			
8	58	46	39	33	57	46	38	33	45	38	33	43	37	33	42	37	33			
9	55	43	35	30	53	42	35	30	41	35	30	40	34	30	39	34	30			
10	51	39	32	28	50	39	32	28	38	32	27	37	31	27	36	31	27			



Some luminaires use fluorescent or high intensity discharge (HID) lamps that contain small amounts of mercury. Such lamps are labeled, "Contain Mercury" and/or the symbol "HG". Lamps that contain mercury must be disposed of in accordance with local requirements. Information regarding lamp recycling and disposal can be found at www.lamprecycle.org

© 2015 Koninklijke Philips N.V. All rights reserved.
Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.
philips.com/luminaires



Philips Lighting, North America Corporation
200 Franklin Square Drive, Somerset, NJ 08873
Tel. 855-486-2216

Philips Lighting Canada Ltd.
A division of Philips Electronics Ltd.
281 Hillmount Rd, Markham, ON, Canada L6C 2S3
Tel. 800-668-9008