




Loadcentres

EQL & SEQ Single Phase Main Lug & Main Breaker Loadcentres



Selection and Ordering Data

 <p>SEQ24125SM</p>	Factory Modifications[®]												
	Type	Description	Catalogue Number			Example			Delivery				
	EQL	White door and trim Beige door and trim	add suffix... W add suffix... B			EQL24125DW EQL24125DB			2 weeks				
	SEQ	Grey door installed White door and trim Beige door and trim	add suffix... D add suffix... DW add suffix... DB			SEQ24125SMD SEQ24125SMDW SEQ24125SMDB							
	Door Kit	White Door kit Beige Door kit	add suffix... W add suffix... B			DK24SM-1W DK24SM-1B							
Note: All door kits are available in Grey, White and Beige colours.													
EQL	Copper Bus	add suffix... C			EQL24125DC			4 weeks					
 <p>SEQ24100SMCR</p>	SEQ Type 3R Weatherproof Loadcentre with Factory installed main breaker 1 phase 3 wire 240V AC max.												
	Number of Circuits	Catalogue Number	Skid Qty.	Main Amps	Dimensions - Inches (mm)			Lug Data	Mounting Trim	Factory Mod.	Hubs (sold seperately)		
					H	W	D				Conduit size (")	Catalogue Number	
	16/32	SEQ16100SMCR	35	100	21 5/8 (549)	13.6 (345)	5 (127)	6-2/0	surface only	N/A	3/4 1 1 1/4 1 1/2 2 2 1/2	ECHS075 ECHS100 ECHS125 ECHS150 ECHS200 ECHS250	
	24/48	SEQ24100SMCR	28	100	24 5/8 (625)	13.6 (345)	5 (127)	6-2/0	surface only	N/A			
	24/48	SEQ24125SMCR	28	125	24 5/8 (625)	13.6 (345)	5 (127)	6-2/0	surface only	N/A			
	24/48	SEQ24200CR	21	200	27 1/2 (699)	15 (381)	5 (127)	6-250 MCM	surface only	N/A			
	32/64	SEQ32100SMCR	21	100	28 5/8 (726)	13.6 (345)	5 (127)	6-2/0	surface only	N/A			
	32/64	SEQ32125SMCR	21	125	28 5/8 (726)	13.6 (345)	5 (127)	6-2/0	surface only	N/A			
	32/64	SEQ32150CR	21	150	33 1/2 (851)	15 (381)	5 (127)	6-250 MCM	surface only	N/A			
	32/64	SEQ32200CR	21	200	33 1/2 (851)	15 (381)	5 (127)	6-250 MCM	surface only	N/A			
	40/80	SEQ40150CR	21	150	36 1/2 (927)	15 (381)	5 (127)	6-250 MCM	surface only	N/A			
	40/80	SEQ40200CR	21	200	36 1/2 (927)	15 (381)	5 (127)	6-250 MCM	surface only	N/A			
Note: The SEQ Weatherproof panels are stocked complete with gasketed hinged door for improved weatherproof protection. All SEQ Type 3R panels come standard with copper bus.													
 <p>SEQ38200U</p>	Dual Listed/cULus Loadcentres 120/240V 1 phase 3 Wire												
	Number of Circuits	Catalogue Number	Skid Qty.	Main Amps	Dimensions - Inches (mm)			Lug Data	Mounting Trim	Door Kit Catalogue Number			
					H	W	D						
	38	SEQ38100U SEQ38125U	27 27	100 125	36 (362)	14 1/4 (362)	4 (102)	6-250MCM	comb.	DKS38-1A			
SEQ38150U SEQ38200U		27 27	150 200	DKS38-2A									
Branch breakers: Only 1" full module breakers that are both UL & CSA certified are allowed to be installed in this loadcentre; 1/2" twin and quad branch breakers must not be used as per NEC 384-14(a) and NEC-384-15. Consult Siemens Sales Rep. for details.													
Application benefit: Allows modular home builders who have businesses in both US & Canada to carry only one line of inventory.													





Loadcentres

SPA panel and Mini Panel/Enclosed Breaker

Selection

Selection and Ordering Data



 <p>W0408ML1125</p>  <p>2-POLE GFCI</p>	SPA panel package, 3R enclosure 120/240V 1 Phase 3 Wire																																							
	Number of Circuits	Package Catalogue Number	Main Amps.	GFCI Included	Enclosure Dimensions - Inches (mm)			Hubs (sold separately)																																
					H	W	D	Conduit Size (")	Catalogue Number																															
	4/8	W0408ML1125-20	125	QF220	12 ^{1/4} (312)	6 (153)	4 ^{1/4} (108)	Cover 3/4 1 1 ^{1/4} 1 ^{1/2} 2 2 ^{1/2}	ECHS000 ECHS075 ECHS100 ECHS125 ECHS150 ECHS200 ECHS250																															
		W0408ML1125-30		QF230																																				
		W0408ML1125-40		QF240																																				
W0408ML1125-50		QF250																																						
W0408ML1125-60		QF260																																						
Each package also includes a 4-point ground bar and French instructions.																																								
 <p>EQS260</p>	Circuit Breaker Enclosures for Service Entrance and Commercial Use																																							
	EEMAC 1 Enclosure (Indoor) 1 phase 3 wire 240V AC Max.																																							
	Breaker Range	Catalogue Number	Main Amps.	Number of Poles	Dimensions - Inches (mm)			Lug Data																																
					H	W	D																																	
	15-60A	EQS260* ^①	60	1,2	7 ^{3/4} (197)	5 (127)	2 ^{3/4}	14-4 (70)																																
15-125A	EQS2125* ^①	125	1,2	13 (330)	6 ^{5/8} (168)	3 ^{3/8}	14-2/0 (86)																																	
*Does not accept quad type breaker.																																								
 <p>WEQ60-4</p>	EEMAC 3R Weatherproof Enclosure, 1 phase 3 wire 240V AC Max.																																							
	Full Module Circuits	Catalogue Number	Main Amps.	Dimensions - Inches (mm)			Weight lbs.	Hub ^② Type																																
				H	W	D																																		
	3	WEQ60-4 ^③	60	10 ^{1/4} (260)	9 ^{1/2} (241)	5 ^{5/8} (143)	8	HR																																
	2/4	W0204ML1060 ^③	60	8 (204)	5 (127)	4 ^{1/4} (108)	4	HA																																
4/8	W0408ML1125 ^③	125	12 ^{1/4} (312)	6 (153)	4 ^{1/4} (108)	7	HS																																	
Key Features: Outdoor EEMAC 3R enclosure <ul style="list-style-type: none"> • Accepts plug-in Q type breakers • One piece bus bar construction • Combination trim flush/surface 				Hubs <table border="1"> <thead> <tr> <th>Catalogue Number</th> <th>Conduit size (")</th> <th>Catalogue Number</th> <th>Conduit size (")</th> </tr> </thead> <tbody> <tr> <td>ECHA075</td> <td>3/4</td> <td>ECHS075</td> <td>3/4</td> </tr> <tr> <td>ECHA100</td> <td>1</td> <td>ECHS100</td> <td>1</td> </tr> <tr> <td>ECHA125</td> <td>1 1/4</td> <td>ECHS125</td> <td>1 1/4</td> </tr> <tr> <td>ECHR075</td> <td>3/4</td> <td>ECHS150</td> <td>1 1/2</td> </tr> <tr> <td>ECHR100</td> <td>1</td> <td>ECHS200</td> <td>2</td> </tr> <tr> <td>ECHR125</td> <td>1 1/4</td> <td>ECHS250</td> <td>2.5</td> </tr> <tr> <td>ECHR150</td> <td>1 1/2</td> <td></td> <td></td> </tr> </tbody> </table>					Catalogue Number	Conduit size (")	Catalogue Number	Conduit size (")	ECHA075	3/4	ECHS075	3/4	ECHA100	1	ECHS100	1	ECHA125	1 1/4	ECHS125	1 1/4	ECHR075	3/4	ECHS150	1 1/2	ECHR100	1	ECHS200	2	ECHR125	1 1/4	ECHS250	2.5	ECHR150	1 1/2		
Catalogue Number	Conduit size (")	Catalogue Number	Conduit size (")																																					
ECHA075	3/4	ECHS075	3/4																																					
ECHA100	1	ECHS100	1																																					
ECHA125	1 1/4	ECHS125	1 1/4																																					
ECHR075	3/4	ECHS150	1 1/2																																					
ECHR100	1	ECHS200	2																																					
ECHR125	1 1/4	ECHS250	2.5																																					
ECHR150	1 1/2																																							
Remark: ① The panels will not accommodate a 2 pole ground fault breaker (GFCI) or breaker with shunt trip. ② Hubs sold separately ③ Not to be used as service entrance.																																								

4 LOADCENTRES