



Slug-Buster® Knockout Punches 0.492" to 2.520"



Unique Slug-Buster® punch design creates slug as the punch is drawn into the die.



Slug is split in half as punching operation is completed.




Split slugs fall free from the die and stud.

- The contractor's choice – worldwide.
- Unique punch profile also splits slugs for easier slug removal.
- Use with battery-powered, hydraulic, ratchet or manual drivers.
- Uses standard Greenlee dies and draw studs.
- Slug Buster® punches available in sizes up thru 2.52" (64.0 mm).
- U.S. Patent #4,543,722 for Slug-Buster®.



SPECIFICATIONS

| | |
|--------------------|--|
| Capacity | Mild steel up through 10 gauge (3.5 mm). |
| Application | Punch mild steel, aluminum, fiberglass and plastic. |
| Hole Sizes | Conduit Sizes- Hole size is outside diameter of US conduit sizes. i.e 1/2" conduit actually 7/8". Pg Sizes-European standard pipe sizes. ISO Sizes- International Standards Organization pipe sizes. |
| Operation | Battery, hydraulic, ratchet or manual drivers. When used with ratchet, hydraulic or battery drivers, buy the punch and die only; the draw stud is part of the driver kit. |

PUNCH UNIT



REPLACEMENT PARTS



| PUNCH UNIT INCLUDES PUNCH, DIE AND DRAW STUD | | CONDUIT & PIPE SIZE | HOLE SIZE ACTUAL | | | CAPACITY MILD STEEL | | | WEIGHT | | REPLACEMENT PUNCH | | REPLACEMENT DIE | | REPLACEMENT MANUAL DRAW STUD | | |
|--|---------|---------------------|------------------|-------|------|---------------------|-----|-----|--------|------|-------------------|------------|-----------------|---------|------------------------------|----------|-------|
| CAT. NO. | UPC NO. | | Ø INCH | Ø mm | PG | ISO | GA. | mm | LBS. | g | CAT. NO. | UPC NO. | CAT. NO. | UPC NO. | CAT. NO. | UPC NO. | |
| 06727 | 06727 | — | 0.492 | 12.5 | 7 | 12 | 16 | 1.5 | 0.3 | 137 | 06728 | 06728 | 06729 | 06729 | 1675AV | 04218 | |
| NI 12356 | 12356 | — | 1/2 | 12.7 | 7 | — | 16 | 1.5 | 0.15 | 69 | 12360 | 12360 | 12358 | 12358 | 1675AV | 04218 | |
| NI 12357 | 12357 | — | 9/16 | 14.3 | — | — | 16 | 1.5 | 0.16 | 73.5 | 12357 | 12357 | 12361 | 12361 | 1675AV | 04218 | |
| 7211EBB-15.2 | 31989 | — | 0.598 | 15.2 | 9 | — | 14 | 2.0 | 0.3 | 137 | 31969 | 31969 | 32002 | 32002 | 00042 | 00042 | |
| 35177 | 35177 | — | 0.638 | 16.2 | — | 16 | 14 | 2.0 | 0.3 | 137 | 35163 | 35163 | 35162 | 35162 | 00042 | 00042 | |
| NI 12335 | 12335 | — | 11/16 | 17.5 | — | — | 14 | 2.0 | 0.3 | 177 | 12337 | 12337 | 12336 | 12336 | 00042 | 00042 | |
| 7211EBB-18.6 | 31990 | — | 0.732 | 18.6 | 11 | — | 14 | 2.0 | 0.3 | 137 | 31970 | 31970 | 32003 | 32003 | 00042 | 00042 | |
| NI 12307 | 12307 | — | 3/4 | 19.1 | — | — | 14 | 2.0 | 0.4 | 183 | 12306 | 12306 | 12305 | 12305 | 00042 | 00042 | |
| 7211EBB-20.4 | 31991 | — | 0.803 | 20.4 | 13 | 20 | 14 | 2.0 | 0.3 | 137 | 31971 | 31971 | 32004 | 32004 | 00042 | 00042 | |
| 7211BB-1/2 | 31962 | 1/2" | 7/8 | 0.885 | 22.5 | 16 | — | 10 | 3.5 | 0.3 | 137 | 721-1/2 | 31756 | 14722 | 14722 | 00042 | 00042 |
| NI 12338 | 12338 | — | 15/16 | 23.8 | — | — | 14 | 2.0 | 0.5 | 253 | 12340 | 12340 | 12339 | 12339 | 00042 | 00042 | |
| ◇ | ◇ | 1/2" | 7/8 | 0.885 | 22.5 | 16 | — | 10 | 3.5 | — | 721-1/2P | 01980 | 14722P | 01992 | 00042P | 06678 | |
| 35178 | 35178 | — | 1 | 1.000 | 25.4 | — | 25 | 14 | 2.0 | 0.5 | 227 | 35165 | 35165 | 35164 | 35164 | 00042P | 06678 |
| 12341 | 12341 | — | 1-1/16 | 27 | — | — | 14 | 2.0 | 0.6 | 261 | 12343 | 12343 | 12342 | 12342 | 00042 | 00042 | |
| 7211BB-3/4 | 31963 | 3/4" | — | 1.115 | 28.3 | — | — | 10 | 3.5 | 0.8 | 363 | 721-3/4 | 31757 | 124AV | 06972 | 249AVBB | 04040 |
| ◇ | ◇ | 3/4" | — | 1.115 | 28.3 | — | — | 10 | 3.5 | — | 721-3/4P | 01981 | 124AVP | 01993 | 249AVBBP | 01987 | |
| 7211EBB-28.3 | 31993 | — | — | 1.115 | 28.3 | 21 | — | 14 | 2.0 | 0.5 | 227 | 31973 | 31973 | 32006 | 32006 | 00042 | 00042 |
| 60246 | 60246 | — | 1-7/32 | 1.210 | 30.5 | — | — | 10 | 3.5 | 0.6 | 273 | 60237 | 60237 | 36278 | 36278 | 249AVBB | 04040 |
| 36508 | 36508 | — | 1-7/32 | 1.210 | 30.5 | — | — | 14 | 2.0 | 0.6 | 273 | 36284 | 36284 | 36279 | 36279 | 00042 | 00042 |
| NI 12308 | 12308 | — | 1-1/4 | — | 31.8 | — | — | 16 | 1.5 | 0.7 | 326.5 | 12309 | 12309 | 12310 | 12310 | 00042 | 00042 |
| 35179 | 35179 | — | — | 1.280 | 32.5 | — | 32 | 10 | 3.5 | 0.8 | 363 | 35169 | 35169 | 35168 | 35168 | 249AVBB | 04040 |
| NI 12344 | 12344 | — | 1-5/16 | — | 33.4 | — | — | 16 | 1.5 | 0.7 | 345 | 12346 | 12346 | 12345 | 12345 | 00042 | 00042 |
| 7211BB-1 | 31964 | 1" | — | 1.362 | 34.6 | — | — | 10 | 3.5 | 1 | 454 | 721-1 | 31758 | 126AV | 04011 | 249AVBB | 04040 |
| NI 12304 | 12304 | — | 1-3/8 | — | 34.9 | — | — | 10 | 3.0 | 1.1 | 507.5 | 12303 | 12303 | 12302 | 12302 | 04040 | 04040 |
| ◇ | ◇ | 1" | — | 1.362 | 34.6 | 10 | — | 10 | 3.5 | — | — | 721-1P | 01982 | 126AVP | 01994 | 249AVBBP | 01987 |
| 7211EBB-37 | 31995 | — | — | 1.457 | 37.0 | 29 | — | 10 | 3.5 | 1.2 | 545 | 31975 | 31975 | 32008 | 32008 | 249AVBB | 04040 |
| NI 12313 | 12313 | — | 1-1/2 | — | 38.1 | — | — | 10 | 3.0 | 1.2 | 559 | 12312 | 12312 | 12311 | 12311 | 04040 | 04040 |
| 35180 | 35180 | — | — | 1.595 | 40.5 | — | 40 | 10 | 3.5 | 1.2 | 545 | 35158 | 35158 | 35159 | 35159 | 249AVBB | 04040 |
| NI 12347 | 12347 | — | 1-5/8 | — | 41.3 | — | — | 10 | 3.0 | 1.3 | 610.25 | 12349 | 12349 | 12348 | 12348 | 04040 | 04040 |
| 7211BB-1-1/4 | 31965 | 1-1/4" | — | 1.701 | 43.2 | — | — | 10 | 3.5 | 1.3 | 590 | 721-1-1/4 | 31759 | 128AV | 04013 | 249AVBB | 04040 |
| NI 12316 | 12316 | — | 1-3/4 | — | 44.5 | — | — | 10 | 3.0 | 1.4 | 661.5 | 12315 | 12315 | 12314 | 12314 | 04040 | 04040 |
| ◇ | ◇ | 1-1/4" | — | 1.701 | 43.2 | — | — | 10 | 3.5 | — | — | 721-1-1/4P | 01983 | 128AVP | 01995 | 249AVBBP | 01987 |
| 7211EBB-47 | 31996 | — | — | 1.850 | 47.0 | 36 | — | 10 | 3.5 | 1.9 | 862 | 31976 | 31976 | 32009 | 32009 | 304AVBB | 04042 |
| NI 12350 | 12350 | — | 1-7/8 | — | 47.6 | — | — | 10 | 3.0 | 1.8 | 853.5 | 12354 | 12354 | 12352 | 12352 | 04042 | 04042 |
| 7211BB-1-1/2 | 31966 | 1-1/2" | — | 1.951 | 49.6 | — | — | 10 | 3.5 | 2.1 | 953 | 721-1-1/2 | 31760 | 440AV | 04061 | 304AVBB | 04042 |
| ◇ | ◇ | 1-1/2" | — | 1.951 | 49.6 | — | — | 10 | 3.5 | — | — | 721-1-1/2P | 01984 | 440AVP | 01996 | 304AVBBP | 01988 |
| 35181 | 35181 | — | 2 | 2.000 | 50.8 | — | 50 | 10 | 3.5 | 2.3 | 1043 | 35160 | 35160 | 35161 | 35161 | 304AVBB | 04042 |
| 36171 | 36171 | — | 2-1/8 | 2.125 | 54.0 | 42 | — | 10 | 3.5 | 2.5 | 1134 | 36172 | 36172 | 36173 | 36173 | 304AVBB | 04042 |
| NI 12351 | 12351 | — | 2-1/4 | — | 57.2 | — | — | 10 | 3.0 | 2.9 | 1336 | 12355 | 12355 | 12353 | 12353 | 04042 | 04042 |
| 7211EBB-60 | 31998 | — | — | 2.362 | 60.0 | 48 | — | 10 | 3.5 | 2.8 | 1270 | 31978 | 31978 | 32011 | 32011 | 304AVBB | 04042 |
| 7211BB-2 | 31967 | 2" | 2-3/8 | 2.416 | 61.5 | — | — | 10 | 3.5 | 3.2 | 1452 | 721-2 | 31761 | 442AV | 04063 | 304AVBB | 04042 |
| ◇ | ◇ | 2" | 2-3/8 | 2.416 | 61.5 | — | — | 10 | 3.5 | — | — | 721-2P | 01985 | 442AVP | 01997 | 304AVBBP | 01988 |
| 35182 | 35182 | — | — | 2.520 | 64.0 | — | 63 | 10 | 3.5 | 3.4 | 1542 | 35167 | 35167 | 35166 | 35166 | 304AVBB | 04042 |

◇ Individually Packaged in Point of Purchase clamshell for display opportunities

R = REPLACEMENT PART **A** = ACCESSORY **NI** = NEW PRODUCT

International Tel: +1.815.397.7070
Fax: +1.815.397.9247

Canada Tel: 800.435.0786
Fax: 800.524.2853

USA Tel: 800.435.0786
Fax: 800.451.2632