



GSTUD38HY

by Burndy Catalog ID: GSTUD38HY

Prop 65 Notice

Structural Steel Grounding Connector, 3 AWG, 3/8" Rod.

- May be welded to steel surfaces quickly and easily
- No disk grinding needed
- Knurled surface for better gripping
- Copper platedMay be installed during adverse weather conditions

Features: The VERSITAIL May Be Welded To Steel Surfaces Quickly And Easily With Normal Construction Equipment, The VERSITAIL Eliminates Costly Disk Grinding And The Need To Expose Virgin Metal, The Welding Process Burns Through The Oxidation And Scale To Establish Excellent Electrical Grounding Continuity, The VERSITAIL May Be Installed By The Welder In The Field Or At The Steel Fabricator Based On Customer Preference, The VERSITAIL Pure Copper Coating Over Low Carbon, Hot Rolled Steel Is Compatible With Standard Welding Processes, No Toxic Gasses Are Generated, The VERSITAIL Knurled Surface Is Copper Plated And Specifically Designed To Ensure Excellent Mechanical Gripping And Electrical Integrity For BURNDY Compression And Mechanical

Connectors In All Grounding Applications, The VERSITAIL May Be Installed During Adverse Weather Conditions Thus Eliminating Costly Construction Delays, Low Carbon, Hot Rolled Steel, Pure Copper Plated Finish, Compression Connector: YGHP34C26 (250 - 500 KCMIL), YGHP29C26 (1/0 AWG - 250 KCMIL), Ground Rod Size: 3/8 IN

Product Details

General

Application	For Compression Connectors And Mechanical Connectors
Material	Steel
Plated	Y
Plating Type	Nickel
Sub Brand	HYGROUND, VERSITAIL
Trade Name	VERSITAIL™
Туре	GSTUD-HY
UPC	781810220887
UPC 12 Digit	7818102208877

Dimensions

Dimension - B Length fraction	16/41 in
Dimension - B Length inch	0.39 in
Dimension - D inch	1.25 in
Dimension - Ground Rod Size	3/8 in
Dimension - L Length Overall mm	148 mm
Dimension - Length Overall inch	5.81 in
Physical Attribute - Tongue Angle	45 Degree

Conductor Related

Conductor - Copper Str Size	3 AWG

Conductor - Copper Str Size Range	3 AWG
Conductor - Rod Size	3/8 in
Conductor - Rod Size Range	3/8 in
Conductor Type	Rod-SizeCU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No	
Certification - ETL	No	
Certification - UL Listed Direct Burial	No	
Certification - UL Recognized	No	
Certification - cULus	No	
Standards - RoHS Compliance Status	СМ	
UL Listed	No	
Logistics		

Minimum Pack Quantity 1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175 1-603-647-5299 (International)