




PRODUCT SEARCH

[HOME](#)[WHAT'S NEW](#)[SERVICE / SUPPORT](#)[WHERE TO BUY](#)[INSTRUCTION MANUALS](#)[CO](#)**TERMINATION**[Hand Tools](#)[Holemaking](#)[Bending](#)[Fishing](#)[Cable Pulling](#)[Wire & Cable Termination](#)[Voice Data Video](#)[Testing & Measurement](#)[Storage & Material Handling](#)[Hydraulic Pumps & Miscellaneous](#)**Name:**

200' x 1/8" x .060 (61 m x 3.2 mm x 1.5 mm) Stainless Steel Fish Tape with Case

Cat #:

438-20SS

UPC #:

06410

Spec:

Capacity 1/8" (3.2 mm) tape width - 400 lbs. (1.7 kN) maximum design strength. Weight 438-10SS - 5 lbs. (2.3 kg) 438-20SS - 7 lbs. (3.2 kg)

Description:

SILVER STREAK® comes with either 100' (30.5 m) or 200' (61 m) of stainless steel fish tape. It's rust and corrosion-resistant so it lasts longer and rewinds easier than ordinary tape. It won't leave a nasty residue, either.

- Equipped with SPEED FLEX™ leader, silver-soldered onto the fish tape. Streamlined fish tape/leader connection and lightweight, flexible leader design combine to enable user to fish farther, faster.
- High-impact nylon, one-piece handle for maximum durability, long life, and easy, comfortable use.
- Large handle grip for greater user control.
- Self-tensioning case for easy tape winding. (No tension trigger.)
-

