

# AF26-30-00-11

## General Information

<b>Extended Product Type:</b>	AF26-30-00-11
<b>Product ID:</b>	1SBL237001R1100
<b>EAN:</b>	3471523110915
<b>Catalog Description:</b>	AF26-30-00-11 24-60V50/60HZ 20-60VDC Contactor
<b>Long Description:</b>	<p>AF26 contactors are used for controlling power circuits up to 690 V AC and 220 V DC. They are mainly used for controlling 3-phase motors, non-inductive or slightly inductive loads. AF... contactors include an electronic coil interface accepting a wide control voltage <math>U_c \text{ min. } \dots U_c \text{ max.}</math> Only four coils cover control voltages between 24...500 V 50/60 Hz or 20...500 V DC. AF contactors can manage large control voltage variations. One coil can be used for different control voltages used worldwide without any coil change. AF contactors have built-in surge protection and do not require additional surge suppressors. The AF... series 1-stack 3-pole contactors are of the block type design. - Main poles and auxiliary contact blocks: 3 main poles, front and side-mounted add-on auxiliary contact blocks (mechanically-linked auxiliary contacts compliant with Annex L of IEC 60947-5-1. N.C. mirror contacts compliant with Annex F of IEC 60947-4-1) - Control circuit: AC or DC operated - Accessories: a wide range of accessories is available. Note: AF...-30-...-11 not suitable for a direct control by PLC-output. AF...-30-...-11 contactor type available in some countries: please consult your ABB representative.</p>



## Categories

Products » Low Voltage Products and Systems » Control Products » Contactors » Block Contactors

## Ordering

<b>EAN:</b>	3471523110915
<b>Minimum Order Quantity:</b>	1 piece
<b>Customs Tariff Number:</b>	85369085

## Dimensions

<b>Product Net Width:</b>	45.0 mm
<b>Product Net Depth:</b>	86.0 mm
<b>Product Net Height:</b>	86.0 mm
<b>Product Net Weight:</b>	0.310 kg

## Container Information

---

<b>Package Level 1 Units:</b>	1 piece
<b>Package Level 1 Width:</b>	87 mm
<b>Package Level 1 Length:</b>	87 mm
<b>Package Level 1 Height:</b>	47 mm
<b>Package Level 1 Gross Weight:</b>	0.31000 kg
<b>Package Level 1 EAN:</b>	3471523110915
<b>Package Level 2 Units:</b>	45 piece
<b>Package Level 3 Units:</b>	1080 piece

---

## Environmental

---

<b>Ambient Air Temperature:</b>	Close to Contactor for Storage -60...+80 °C Close to Contactor Fitted with Thermal O/L Relay -25...+60 °C Close to Contactor without Thermal O/L Relay -40...+70 °C
<b>Maximum Operating Altitude Permissible:</b>	3000 m
<b>Resistance to Shock acc. to IEC 60068-2-27:</b>	Closed, Shock Direction: B1 25 g Open, Shock Direction: B1 5 g Shock Direction: A 30 g Shock Direction: B2 15 g Shock Direction: C1 25 g Shock Direction: C2 25 g
<b>Resistance to Vibrations acc. to IEC 60068-2-6:</b>	5...300 Hz 4 g closed position / 2 g open position
<b>RoHS Status:</b>	Following EU Directive 2011/65/EC

---

## Technical

---

<b>Rated Operational Power AC-3 (<math>P_e</math>):</b>	(220 / 230 / 240V) 6.5 kW (380 / 400V) 11 kW (415V) 11 kW (440V) 15 kW (500V) 15 kW (690V) 15 kW
<b>Rated Operational Current AC-1 (<math>I_e</math>):</b>	(690V) 40°C 45 A (690V) 60°C 40 A (690V) 70°C 32 A
<b>Number of Main Contacts NO:</b>	3
<b>Number of Main Contacts NC:</b>	0
<b>Number of Auxiliary Contacts NO:</b>	0
<b>Number of Auxiliary Contacts NC:</b>	0
<b>Rated Control Circuit Voltage (<math>U_c</math>):</b>	50 Hz 24...60 V 60 Hz 24...60 V DC Operation 20...60 V
<b>Terminal Type:</b>	Screw Terminals

---

## Technical UL/CSA

---

<b>Tightening Torque UL/CSA:</b>	Control Circuit 11 in·lb Main Circuit 22 in·lb
----------------------------------	---

---

## Certificates and Declarations (Document Number)

---

<b>CB Certificate:</b>	CB_SE_70856M1
<b>CCC Certificate:</b>	CCC_2010010304445623

<b>cUL Certificate:</b>	UL_20091124-E312527-7-1
<b>Declaration of Conformity - CE:</b>	1SBD250165C1000
<b>DNV Certificate:</b>	DNV_E12810
<b>EAC Certificate:</b>	EAC_RU C-FR ME77 B01010
<b>GL Certificate:</b>	GL_3786512HH
<b>GOST Certificate:</b>	GOST_POCCFR.ME77.B07175.pdf
<b>LR Certificate:</b>	LRS_1300087
<b>RINA Certificate:</b>	RINA_ELE084013XG
<b>RoHS Information:</b>	1SBD251012E1001

---

## Classifications

---

<b>E-nummer:</b>	3211344
------------------	---------

---