

FEATURES & SPECIFICATIONS

INTENDED USE

For use with housings L7X, L7XR, LC6, L7XF and L7XFR.

CONSTRUCTION

Aluminum one piece reflector.

Polyester powder coat paint.

Baffles available in black or white.

White and black baffles have integral flange.

INSTALLATION

Socket to trim interface.

Retaining clips pull and snap onto top of reflector to hold trim inside housing.

LISTING


U.L. Listed to U.S. and Canadian safety standards.

Damp location listed.

Pull on clip Patent # (U.S.) 5707143, (Canada) 2193902.

Note: Specifications subject to change without notice.


Catalog Number
Notes
Type



6" Full Reflector Trim

7B5

BAFFLE DEEP
Narrow Flange



Specifications

Height:	7-1/4 (18.4)
Lamp opening:	5-3/4 (14.6)
Diameter:	7-5/8 (19.4) white 8 (20.3) others

All dimensions are inches (centimeters).

ORDERING INFORMATION

For shortest lead times, configure products using **bolded options**.

Example: 7B5

7B5		
Series/ Finish		Options
Series 7B5	Finish (blank) Black baffle W White baffle	PF Integral white plastic flange (separate flange)

HOUSING COMPATIBILITY

Housing and trim ordered separately.

Application	Source	Maximum Wattage	Housing
IC	Fluorescent	13DTT	L7XF
		26TRT	L7XF
Non-IC	Incandescent	120 PAR38	L7X, L7XR, LC6
		120 BR40*	L7X, L7XR, LC6
	Fluorescent	18DTT	L7XF, L7XFR

* 150 BR40 maximum wattage for 7B5W.

