



These dimmable LED downlight kits provide exceptional light output in a sophisticated, sleek design that replicates the look of a traditional downlight but at a fraction of the energy and maintenance costs.

- ▶ Easily convert most 4", 5" and 6" recessed downlights or can be surface mounted directly to a J-Box<sup>4</sup>
- ▶ Quick and easy installation – all mounting hardware included for retrofit or new construction
- ▶ IC rated when used in an approved IC rated recessed housing



# Downlights



Order code	Description	Watts (W)	Base	Volts (VAC)	Colour temp. (K)	CRI	Average life <sup>1</sup> (hrs)	Initial lumens <sup>2</sup> (lm)	Traditional equivalent (W)	Dimmable <sup>3</sup> (Yes/No)	Case qty
<b>4" Downlight</b>											
MOL : 2 7/32 in. (53.5 mm)    Dia. : 5 1/2 in. (139.5 mm)											
62947	LED/DL4/9W/27K/RETRO/E26/D/STD	9	E26	120	2 700	80	40 000	525	50	Y	4
62948	LED/DL4/9W/30K/RETRO/E26/D/STD	9	E26	120	3 000	80	40 000	550	50	Y	4
<b>6" Downlight</b>											
MOL : 2 1/4 in. (54 mm)    Dia. : 7 1/2 in. (186.5 mm)											
63151	LED/DL6/11W/27K/RETRO/E26/D/STD	11	E26	120	2 700	85	50 000	800	65	Y	6
63150	LED/DL6/11W/30K/RETRO/E26/D/STD	11	E26	120	3 000	85	50 000	850	65	Y	6
62550	LED/DL6/13W/27K/RETRO/E26/D/STD	13	E26	120	2 700	80	50 000	750	65	Y	6
62427	LED/DL6/13W/30K/RETRO/E26/D/STD	13	E26	120	3 000	80	50 000	756	65	Y	6

### 4" Downlight

Retrofit Installation



J-Box Installation



### 6" Downlight

Retrofit Installation



J-Box Installation



<sup>1</sup> Life rating based on L70 lumen depreciation design criteria. Average life of lamps that have been approved for ENERGY STAR early submission or complete submission can vary. ENERGY STAR early submission dictates that manufacturers can only claim 35 000 hour life with 3 000 hour actual life test data, 6 000 hour LM-80 data and in-situ temperature measurements. Once a product has been fully qualified, manufacturers may increase the lifetime of a product by demonstrating full compliance with the ENERGY STAR criteria at the new lifetime with Lumen Maintenance at the minimum required test period.

<sup>2</sup> Typical Lumens +/- 5 %  
<sup>3</sup> For a complete list of compatible dimmers, housings and ENERGY STAR qualified products, please visit [www.standardpro.com](http://www.standardpro.com)  
<sup>4</sup> Both the 4" and 6" fit into 4x4 J-box. Minimum depth required for 4" is 1 1/2" and 2 1/4" for 6".