



# Metal Halide

| Lamp watts<br>(W) | ANSI code    | Input volts<br>(V)            | Order code   | Description                     | Type          | Circuit type       | Input power ANSI (W) | Max. input current<br>(A)        |
|-------------------|--------------|-------------------------------|--------------|---------------------------------|---------------|--------------------|----------------------|----------------------------------|
| 175               | M57          | 120 / 208 / 240               | <b>10059</b> | BMH0175/120/208/240/C/CWI/H/K/  | Core and coil | CWI                | 215                  | 0.82 / 0.48 / 0.41               |
|                   |              | 120 / 277 / 347               | <b>62933</b> | BMH0175/TRITAP/C/CWA/H/K/STD    | Core and coil | CWA                | 210                  | 1.10 / 0.45 / 0.35               |
|                   |              | 120 / 277 / 347               | <b>10071</b> | BMH0175/TRITAP/F/CWA/H/STD      | F-Can         | CWA                | 205                  | 1.15 / 0.50 / 0.40               |
|                   |              | 120 / 277 / 347               | <b>31166</b> | BMH0175/TRITAP/REM/CWA/H/STD    | Remote        | CWA                | 210                  | 1.10 / 0.50 / 0.40               |
|                   |              | 120 / 208 / 240 / 277         | <b>62920</b> | BMH0175/QUADTAP/C/CWA/H/K/STD   | Core and coil | CWA                | 213                  | 1.30 / 0.75 / 0.65 / 0.57        |
|                   |              | 120 / 208 / 240 / 277 / 480   | <b>61690</b> | BMH0175/5TAP/C/CWA/H/K/STD      | Core and coil | CWA                | 210                  | 1.80 / 1.04 / 0.90 / 0.78 / 0.45 |
|                   |              | 347 / 480 / 600               | <b>10060</b> | BMH0175/347/480/600/C/CWI/H/K/  | Core and coil | CWI                | 215                  | 0.30 / 0.22 / 0.17               |
|                   |              | 347 / 480 / 600               | <b>31200</b> | BMH0175/347/480/600/REM/CWI/H   | Remote        | CWI                | 215                  | 0.30 / 0.22 / 0.17               |
| 250               | M58          | 120 / 208 / 240               | <b>10061</b> | BMH0250/120/208/240/C/CWI/H/K/  | Core and coil | CWI                | 292                  | 0.90 / 0.52 / 0.45               |
|                   |              | 120 / 208 / 240               | <b>16611</b> | BMH0250/120/208/240/REM/C/CWI/H | Remote        | CWI                | 215                  | 0.82 / 0.48 / 0.41               |
|                   |              | 120 / 277 / 347               | <b>62934</b> | BMH0250/TRITAP/C/CWA/H/K/STD    | Core and coil | CWA                | 290                  | 2.10 / 0.90 / 0.70               |
|                   |              | 120 / 277 / 347               | <b>10072</b> | BMH0250/TRITAP/F/CWA/H/STD      | F-Can         | CWA                | 295                  | 1.85 / 0.80 / 0.65               |
|                   |              | 120 / 277 / 347               | <b>31360</b> | BMH0250/TRITAP/REM/CWA/H/STD    | Remote        | CWA                | 290                  | 1.10 / 0.50 / 0.40               |
|                   |              | 120 / 208 / 240 / 277         | <b>10118</b> | BMH0250/QUADTAP/C/CWA/H/K/STD   | Core and coil | CWA                | 290                  | 1.75 / 1.05 / 0.90 / 0.77        |
|                   |              | 120 / 208 / 240 / 277 / 480   | <b>61691</b> | BMH0250/5TAP/C/CWA/H/K/STD      | Core and coil | CWA                | 290                  | 2.50 / 1.45 / 1.25 / 1.10 / 0.63 |
|                   |              | 347 / 480 / 600               | <b>10062</b> | BMH0250/347/480/600/C/CWI/H/K/  | Core and coil | CWI                | 292                  | 0.30 / 0.22 / 0.17               |
| 347 / 480 / 600   | <b>16610</b> | BMH0250/347/480/600/REM/CWI/H | Remote       | CWI                             | 292           | 0.30 / 0.22 / 0.17 |                      |                                  |
| 400               | M59          | 120 / 208 / 240               | <b>10063</b> | BMH0400/120/208/240/C/CWI/H/K/  | Core and coil | CWI                | 462                  | 0.98 / 0.70 / 0.49               |
|                   |              | 120 / 208 / 240               | <b>31361</b> | BMH0400/120/208/240/REM/CWI/H   | Remote        | CWI                | 462                  | 0.98 / 0.70 / 0.49               |
|                   |              | 120 / 277 / 347               | <b>10054</b> | BMH0400/TRITAP/C/CWA/H/K/STD    | Core and coil | CWA                | 458                  | 3.10 / 1.40 / 1.10               |
|                   |              | 120 / 277 / 347               | <b>10073</b> | BMH0400/TRITAP/F/CWA/H/STD      | F-Can         | CWA                | 460                  | 3.15 / 1.35 / 1.10               |
|                   |              | 120 / 277 / 347               | <b>31177</b> | BMH0400/TRITAP/REM/CWA/H/STD    | Remote        | CWA                | 458                  | 3.10 / 1.40 / 1.10               |
|                   |              | 120 / 208 / 240 / 277         | <b>10055</b> | BMH0400/QUADTAP/C/CWA/H/K/STD   | Core and coil | CWA                | 458                  | 3.00 / 1.75 / 1.50 / 1.30        |
|                   |              | 120 / 208 / 240 / 277 / 480   | <b>61692</b> | BMH0400/5TAP/C/CWA/H/K/STD      | Core and coil | CWA                | 458                  | 4.00 / 2.30 / 2.00 / 1.70 / 1.00 |
|                   |              | 347 / 480 / 600               | <b>10064</b> | BMH0400/347/480/600/C/CWI/H/K/  | Core and coil | CWI                | 462                  | 0.33 / 0.23 / 0.19               |
| 347 / 480 / 600   | <b>31183</b> | BMH0400/347/480/600/REM/CWI/H | Remote       | CWI                             | 462           | 0.33 / 0.23 / 0.19 |                      |                                  |
| 1000              | M47          | 120 / 208 / 240               | <b>10065</b> | BMH1000/120/208/240/C/CWI/H/K/  | Core and coil | CWI                | 1 080                | 4.37 / 2.55 / 2.20               |
|                   |              | 120 / 208 / 240               | <b>31191</b> | BMH1000/120/208/240/REM/CWI/H   | Remote        | CWI                | 80                   | 4.37 / 2.55 / 2.20               |
|                   |              | 120 / 277 / 347               | <b>62935</b> | BMH1000/TRITAP/C/CWA/H/K/STD    | Core and coil | CWA                | 1 100                | 5.10 / 2.15 / 1.70               |
|                   |              | 120 / 277 / 347               | <b>31184</b> | BMH1000/TRITAP/REM/CWA/H/STD    | Remote        | CWA                | 80                   | 5.90 / 3.25 / 2.60               |
|                   |              | 120 / 208 / 240 / 277         | <b>10057</b> | BMH1000/QUADTAP/C/CWA/H/K/STD   | Core and coil | CWA                | 1 080                | 7.30 / 4.30 / 3.70 / 3.20        |
|                   |              | 120 / 208 / 240 / 277 / 480   | <b>61693</b> | BMH1000/5TAP/C/CWA/H/K/STD      | Core and coil | CWA                | 1 080                | 9.20 / 5.30 / 4.60 / 4.00 / 2.30 |
|                   |              | 347 / 480 / 600               | <b>10066</b> | BMH1000/347/480/600/C/CWI/H/K/  | Core and coil | CWI                | 1 100                | 1.52 / 1.10 / 0.90               |
|                   |              | 347 / 480 / 600               | <b>31190</b> | BMH1000/347/480/600/REM/CWI/H   | Remote        | CWI                | 100                  | 1.52 / 1.10 / 0.90               |
| 1500              | M48          | 120 / 277 / 347               | <b>10058</b> | BMH1500/TRITAP/C/CWA/H/K/STD    | Core and coil | CWA                | 1 605                | 10.70 / 4.70 / 3.65              |
|                   |              | 120 / 208 / 240 / 277         | <b>16607</b> | BMH1500/QUADTAP/C/CWA/H         | Core and coil | CWA                | 1 605                | 12.10 / 7.05 / 6.05 / 5.30       |