


ORDERING INFORMATION

Order code: 63069
 Description: LED/P30S/10W/30K/40/STD
 UPC: 069549630697
 Case quantity: 6



PERFORMANCE DATA

Shape: PAR30SN
 Wattage (W): 10
 Base: E26
 Lamp voltage (VAC): 120
 Colour temperature (K)**: 3 000
 Average life (L70 hours): 40 000
 Initial lumens (lm)*: 820
 Initial lumens per watt (lm/W): 82
 CBCP: 1 581
 CRI: 90
 Beam angle: 40
 Power factor: ≥ 0.9
 Operating temperature range: $-40^{\circ}\text{C}/-40^{\circ}\text{F}$ to $40^{\circ}\text{C}/104^{\circ}\text{F}$

*Initial lumens range: +/- 5 %

**Typical colour temperature range: +/- 5 %



For a complete list of ENERGY STAR qualified products, please visit www.standardpro.com

COMPATIBLE DIMMER LIST

LUTRON: DVCL-153P, CTCL-153P, MACL-153P, DVCL-253P, AYCL-253P, DVELV-300P, SELV-300P, NTELV-600
 LEGRAND: HCL453P, H703PTUW
 COOPER: SAL06P, SLC03P, AAL06
 LEVITON: IPL06, 6674

Dimmer compatibility list indicates those dimmers that have been tested and operated properly under normal conditions. Each application is unique and various factors such as load, common neutrals or electrical products on the circuit can, in certain instances, cause variance in the system performance. Consult dimming system manufacturer for additional support in operation.

CAUTIONS

- Turn power off before inspection, installation, or removal.
- Risk of electric shock – do not use where directly exposed to water or weather.
- Suitable for use in open fixtures.
- Suitable for use in wet locations.
- Do not open – no user serviceable parts inside.
- Added weight of the device may cause instability of a freestanding portable luminaire. Use in portable table lamps in which the distance from the bottom of the base to the top of the lampholder does not exceed three (3) times the minimum base diameter.
- Use only on 120 VAC, 60 Hz circuits.
- This device is not intended for use with emergency exit fixtures or emergency exit lights.
- Five year limited warranty.
- For complete dimmer compatibility and warranty information visit www.standardpro.com.
- Operating temperature: $-40^{\circ}\text{C}/-40^{\circ}\text{F}$ to $40^{\circ}\text{C}/104^{\circ}\text{F}$.

NOTES: This device complies with Part 15 of the FCC rules and has been tested and found to comply with the limits for a Class B digital device. This product may cause interference with other devices. If interference occurs, change the location of the product. Any changes or modifications not expressly approved by the manufacturer could void the user's authority to operate the equipment. This RFLD device complies with Canadian ICES-003. LED lamps must be stored, operated under suitable environmental conditions and in accordance with, but not limited to, the latest National Electrical Code, cETLus, cULus, CSA and ANSI specifications.