

Date: _____
 In hands date of project: _____
 Project name/Number: _____
 Name of distributor: _____
 Client #: _____
 Name of end user: _____

ORDERING INFORMATION

Order code: 65772
 Description: LED/ST19/S2/4W/22K/A/V/FIL/STD
 UPC: 69549657724
 Case quantity: 10/50

PERFORMANCE DATA


Type: LED Filament Victorian Style
 Shape: ST19
 Wattage (W): 4
 Base: E26
 Lamp voltage (VAC): 120
 Finish: Amber
 Colour temperature (K): 2 700
 Life (hrs): 15 000
 Lumen Output-LM79 (lm)*: 400
 Lumens per watt (lm/W): 100
 Traditional equivalent: 60
 CRI: 80
 Beam angle: 360°
 Power factor: >0.5
 Operating temperature range: -20°C/68°F to 40°C/104°F
 Burning position: Universal
 Dimmer Type: Forward and Reverse Phase
 Energy Star approved: No
 Suitable for Enclosed Fixture: Yes

*Initial lumens range: +/- 5 %

**Typical colour temperature range: +/- 5 %



Diameter



Dia. : 2 3/8 in. (60 mm)
 MOL : 4 31/32 in. (126 mm)



¹ Based on an average daily usage of 3 hours.

CAN ICES-005 (B) - This lighting equipment complies with Canadian standard ICES-005 for use in residential applications.

Data is based upon tests performed in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

July 13, 2017



ORDERING INFORMATION

Order code: 65772
 Description: LED/ST19/S2/4W/22K/A/V/FIL/STD
 UPC: 69549657724
 Case quantity: 10/50

COMPATIBLE DIMMER LIST

Legrand HCL453P
Cooper DAL06P, SLC03P, AAL06
Leviton 6615, IPL06, 6674, DSL06-1LZ, DSM10-1LZ, IPE04-1LZ
Lutron DVCL-153P, CTCL-153P, AYCL-253P, DVELV-300P, SELV-300P, NTELV-600

CAUTIONS

- Turn power off before inspection, installation, or removal.
- Risk of electrical shock – do not use where directly exposed to water or weather.
- Suitable for use in damp locations.
- Do not open – no user serviceable parts inside.
- Use only on 120 VAC, 60Hz circuits.
- This device is not intended for use with emergency exit fixtures or emergency exit lights.
- Compatible with most dimmers.
- For complete dimmer and warranty information visit www.standardpro.com.
- Operating temperature: - 20 °C / 68 °F to 40 °C / 104 °F.

Qty	Description	Price

I accept the specifications of the lamp configuration mentioned above.

Name: _____
 Company: _____
 Signature: _____

Date: _____