

AF26Z-40-00-21

General Information

Extended Product Type:	AF26Z-40-00-21
Product ID:	1SBL236201R2100
EAN:	3471523116016
Catalog Description:	AF26Z-40-00-21 24-60V50/60HZ 20-60VDC Contactor
Long Description:	<p>AF26Z 4-pole contactors are used for controlling power circuits up to 690 V AC and 440 V DC. They are mainly used for controlling non-inductive or slightly inductive loads (i.e. resistance furnaces...).</p> <p>AF..Z contactors include an electronic coil interface accepting a wide control voltage $U_c \text{ min.} \dots U_c \text{ max.}$ Only four coils cover control voltages between 24...250 V 50/60 Hz or 12...250 V DC. AF..Z contactors can manage large control voltage variations. One coil can be used for different control voltages used worldwide without any coil change. AF..Z contactors allow direct control by PLC-output $\geq 24 \text{ V DC } 500 \text{ mA}$ and obtain a reduced holding coil consumption. AF..Z contactors withstand short voltage dips and voltage sags (SEMI F47-0706 compliance) between 24...250 V 50/60 Hz AF..Z contactors have built-in surge protection and do not require additional surge suppressors The AF... series 4-pole contactors are of the block type design. - Main poles and auxiliary contact blocks: 4 N.O. main poles, front and side-mounted add-on auxiliary contact blocks. (mechanically-linked auxiliary contacts compliant with Annex L of IEC 60947-5-1. N.C. mirror contacts compliant with Annex F of IEC 60947-4-1) - Control circuit: AC or DC operated - Accessories: a wide range of accessories is available.</p>



Categories

Products » Low Voltage Products and Systems » Control Products » Contactors » Block Contactors

Ordering

EAN:	3471523116016
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85369085

Dimensions

Product Net Width:	45.0 mm
Product Net Depth:	101.0 mm
Product Net Height:	86.0 mm

Product Net Weight: 0.400 kg

Container Information

Package Level 1 Units: 1 piece
Package Level 1 Width: 87 mm
Package Level 1 Length: 103 mm
Package Level 1 Height: 47 mm
Package Level 1 Gross Weight: 0.40000 kg
Package Level 1 EAN: 3471523116016
Package Level 2 Units: 36 piece
Package Level 3 Units: 864 piece

Environmental

Ambient Air Temperature: Close to Contactor for Storage -60...+80 °C
Near Contactor for Operation in Free Air -40...+70 °C

Maximum Operating Altitude Permissible: 3000 m

Resistance to Shock acc. to IEC 60068-2-27: Closed, Shock Direction: B1 25 g
Open, Shock Direction: B1 5 g
Shock Direction: A 30 g
Shock Direction: B2 15 g
Shock Direction: C1 25 g
Shock Direction: C2 25 g

Resistance to Vibrations acc. to IEC 60068-2-6: 5...300 Hz 4 g closed position / 2 g open position

RoHS Status: Following EU Directive 2011/65/EC

Technical

Rated Operational Power AC-3 (P_e): (220 / 230 / 240V) 5.5 kW
(415V) 11 kW
(440V) 11 kW
(500V) 11 kW
(690V) 9 kW
(400V) 11 kW

Rated Operational Current AC-1 (I_e): (690V) 40°C 45 A
(690V) 60°C 40 A
(690V) 70°C 32 A

Number of Main Contacts NO: 4
Number of Main Contacts NC: 0
Number of Auxiliary Contacts NO: 0
Number of Auxiliary Contacts NC: 0

Rated Control Circuit Voltage (U_c): 50 Hz 24...60 V
60 Hz 24...60 V
DC Operation 20...60 V

Terminal Type: Screw Terminals

Technical UL/CSA

Tightening Torque UL/CSA: Control Circuit 11 in·lb
Main Circuit 22 in·lb

Certificates and Declarations (Document Number)

CB Certificate: CB_SE_70858M1

CCC Certificate:	CCC_2010010304445623
cUL Certificate:	UL_20100802-E319322-3-1
Declaration of Conformity - CE:	1SBD250169C1000
DNV Certificate:	DNV_E12810
EAC Certificate:	EAC_RU C-FR ME77 B01010
GL Certificate:	GL_3786512HH
GOST Certificate:	GOST_POCCFR.ME77.B07175.pdf
LR Certificate:	LRS_1300087
RINA Certificate:	RINA_ELE084013XG
RoHS Information:	1SBD251015E1001

Classifications

E-nummer:	3211526
------------------	---------
