



The perfect replacement for traditional lamps, E-LUME LED lamps offer good value with great performance while providing bright clean light and consistent colour from lamp to lamp.

Features and Benefits

- Energy efficient
- Consistent lamp to lamp colour and light
- Dimmable
- Suitable for use in damp locations
- Long life
- No UV emissions



Applications

- Track, recessed and accent light

MR16 - 7 W



MOL = 1 7/8 in. (47 mm)
Dia. = 1 31/32 in. (50 mm)

MR16-E26 - 7 W



MOL = 2 1/2 in. (53 mm)
Dia. = 1 31/32 in. (50 mm)

MR16-GU10 - 6 W



MOL = 2 1/4 in. (57 mm)
Dia. = 1 31/32 in. (50 mm)

MR16-GU10 - 6 W



MOL = 2 1/4 in. (57 mm)
Dia. = 1 31/32 in. (50 mm)

MR16-GU10 - 7 W



MOL = 2 1/8 in. (55 mm)
Dia. = 1 31/32 in. (50 mm)

MR16-GU10 - 7 W



MOL = 2 1/4 in. (57 mm)
Dia. = 1 31/32 in. (50 mm)

Order code	Description	Watts (W)	Base	Volts (VAC)	Colour temp. (K)	CRI	Average life (hrs)	Initial lumens* (lm)	Beam angle (°)	CBCP (cd)	Traditional equivalent (W)	Dimmable (Yes/No)	Case qty
MR16													
63605	LED/MR16/7W/30K/25/ELUME	7	GU5.3	12	3 000	80	40 000	520	25	2 000	50	Y	48
63606	LED/MR16/7W/30K/40/ELUME	7	GU5.3	12	3 000	80	40 000	520	40	1 100	50	Y	48
MR16-E26													
63854	LED/MR16E26/7W/30K/38/ELUME	7	E26	120	3 000	80	30 000	500	38	1 106	50	Y	48
MR16-GU10													
62430	LED/GU10/6W/NFL/30K/25/D/ELUME	6	GU10	120	3 000	82	25 000	340	25	1 100	35	Y	48
62776	LED/GU10/6W/NFL/30K/25/D/ELUME/GRY	6	GU10	120	3 000	82	25 000	340	25	1 100	35	Y	48
62434	LED/GU10HO/7W/NFL/30K/25/D/ELUME	7	GU10	120	3 000	82	25 000	400	25	1 350	50	Y	48
63607	LED/GU10/7W/30K/25/ELUME	7	GU10	120	3 000	80	40 000	520	25	2 000	50	Y	48
63609	LED/GU10/7W/30K/25/GRY/ELUME	7	GU10	120	3 000	80	40 000	520	25	2 000	50	Y	48
63608	LED/GU10/7W/30K/40/ELUME	7	GU10	120	3 000	80	40 000	520	40	1 100	50	Y	48

* Typical lumens +/- 5%

LED Lamps



P20 - 7.6 W



MOL = 3 11/16 in. (85 mm)
Dia. = 2 15/16 in. (63 mm)

P30S - 9 W



MOL = 3 1/4 in. (86 mm)
Dia. = 3 1/4 in. (95 mm)

P30L - 9 W



MOL = 4 7/16 in. (113 mm)
Dia. = 3 1/4 in. (95 mm)

P38 - 14 W



MOL = 5 1/8 in. (130 mm)
Dia. = 4 1/2 in. (120 mm)

Order code	Description	Watts (W)	Base	Volts (VAC)	Colour temp. (K)	CRI	Average life (hrs)	Initial lumens* (lm)	Beam angle (°)	CBCP (cd)	Traditional equivalent (W)	Dimmable (Yes/No)	Case qty
PAR20													
63610	LED/P20/7.6W/30K/25/ELUME	7.6	E26	120	3 000	80	40 000	534	25	1 179	50	Y	20
63611	LED/P20/7.6W/30K/40/ELUME	7.6	E26	120	3 000	80	40 000	534	40	1 179	50	Y	20
PAR30S													
63612	LED/P30S/9W/30K/25/ELUME	9	E26	120	3 000	80	40 000	800	25	2 910	75	Y	20
63613	LED/P30S/9W/30K/40/ELUME	9	E26	120	3 000	80	40 000	800	40	2 910	75	Y	20
PAR30L													
63614	LED/P30L/9W/30K/25/ELUME	9	E26	120	3 000	80	40 000	800	25	2 910	75	Y	20
63615	LED/P30L/9W/30K/40/ELUME	9	E26	120	3 000	80	40 000	800	40	2 910	75	Y	20
PAR38													
63616	LED/P38/14W/30K/40/ELUME	14	E26	120	3 000	80	40 000	1 000	40	4 241	100	Y	10
63617	LED/P38/14W/40K/40/ELUME	14	E26	120	4 000	80	40 000	1 000	40	4 241	100	Y	10

¹ Life rating based on L70 lumen depreciation design criteria. Average life of lamps that have been approved for ENERGY STAR early submission or complete submission can vary. ENERGY STAR early submission dictates that manufacturers can only claim 25 000 hour life with 3 000 hour actual life test data, 6 000 hour LM-80 data and in-situ temperature measurements. Once a product has been fully qualified, manufacturers may increase the lifetime of a product by demonstrating full compliance with the ENERGY STAR criteria at the new lifetime with Lumen Maintenance at the minimum required test period.

² Typical lumens +/- 5 %

³ For a complete list of compatible dimmers and ENERGY STAR qualified products, please visit www.standardpro.com