

## Pushbutton, flush, without button plate, momentary

Part no. M22-D-X
Article no. 216602
Catalog No. M22-D-X0





## **Delivery programme**

| Product range              | RMQ-Titan (drilling dimensions 22.5 mm) |
|----------------------------|---|
| Basic function             | Pushbutton actuators                    |
| Single unit/Complete unit  | Single unit                             |
| Description                | Flush                                   |
| Function                   | momentary                               |
|                            | Without                                 |
| Front ring                 | Front ring: titanium                    |
| Connection to SmartWire-DT | yes                                     |
| Function                   | momentary                               |

#### **Approvals**

| Approvais                   |  |
|-----------------------------|--|
| Product Standards           | IEC/EN 60947-5; UL 508; CSA-C22.2 No. 14-05; CSA-C22.2 No. 94-91; CE marking |
| UL File No.                 | E29184   |
| UL Category Control No.     | NKCR   |
| CSA File No.                | 012528   |
| CSA Class No.               | 3211-03  |
| North America Certification | UL listed, CSA certified   |
| Degree of Protection        | UL/CSA Type 3R, 4X, 12, 13   |

#### General

| Standards                                 |              |                   | IEC/EN 60947<br>VDE 0660   |
|---|--------------|-------------------|--|
| Lifespan, mechanical                      | Operations   | x 10 <sup>6</sup> | > 5  |
| Operating frequency                       | Operations/h |                   | ≦ <sub>3600</sub>  |
| Actuating force                           |              | n                 | ≦ <sub>5</sub>   |
| Degree of Protection                      |              |                   | IP67, IP69K  |
| Climatic proofing                         |              |                   | Damp heat, constant, to IEC 60068-2-78<br>Damp heat, cyclic, to IEC 60068-2-30 |
| Ambient temperature                       |              | °C                |  |
| Open                                      |              | °C                | - 25 - + 70  |
| Storage                                   |              | °C                | - 40 - + 80  |
| Mounting position                         |              |                   | As required  |
| Mechanical shock resistance               |              | g                 | 30<br>Shock duration 11 ms<br>Sinusoidal<br>according to IEC 60068-2-27        |
| Indoor and protected outdoor installation |              |                   |  |

# Data for design verification according to IEC/EN 61439

| Technical data for design verification                                     |                   |   |  |
|--|-------------------|---|--|
| Rated operational current for specified heat dissipation                   | In                | Α | 0  |
| Heat dissipation per pole, current-dependent                               | P <sub>vid</sub>  | W | 0  |
| Equipment heat dissipation, current-dependent                              | $P_{vid}$         | W | 0  |
| Static heat dissipation, non-current-dependent                             | $P_{vs}$          | W | 0  |
| Heat dissipation capacity  | P <sub>diss</sub> | W | 0  |
| IEC/EN 61439 design verification   |                   |   |  |
| 10.2 Strength of materials and parts                                       |                   |   |  |
| 10.2.2 Corrosion resistance  |                   |   | Meets the product standard's requirements. |
| 10.2.3.1 Verification of thermal stability of enclosures                   |                   |   | Meets the product standard's requirements. |
| 10.2.3.2 Verification of resistance of insulating materials to normal heat |                   |   | Meets the product standard's requirements. |

| 10.2.3.3 Verification of resistance of insulating materials to abnormal heat and fire due to internal electric effects | Meets the product standard's requirements.   |
|--|--|
| 10.2.4 Resistance to ultra-violet (UV) radiation   | Please enquire   |
| 10.2.5 Lifting   | Does not apply, since the entire switchgear needs to be evaluated.                                       |
| 10.2.6 Mechanical impact   | Does not apply, since the entire switchgear needs to be evaluated.                                       |
| 10.2.7 Inscriptions  | Meets the product standard's requirements.   |
| 10.3 Degree of protection of ASSEMBLIES  | Does not apply, since the entire switchgear needs to be evaluated.                                       |
| 10.4 Clearances and creepage distances   | Meets the product standard's requirements.   |
| 10.5 Protection against electric shock   | Does not apply, since the entire switchgear needs to be evaluated.                                       |
| 10.6 Incorporation of switching devices and components   | Does not apply, since the entire switchgear needs to be evaluated.                                       |
| 10.7 Internal electrical circuits and connections  | Is the panel builder's responsibility.   |
| 10.8 Connections for external conductors   | Is the panel builder's responsibility.   |
| 10.9 Insulation properties   |  |
| 10.9.2 Power-frequency electric strength   | Is the panel builder's responsibility.   |
| 10.9.3 Impulse withstand voltage   | Is the panel builder's responsibility.   |
| 10.9.4 Testing of enclosures made of insulating material   | Is the panel builder's responsibility.   |
| 10.10 Temperature rise   | Not applicable.  |
| 10.11 Short-circuit rating   | Is the panel builder's responsibility. The specifications for the switchgear must be observed.           |
| 10.12 Electromagnetic compatibility  | Is the panel builder's responsibility. The specifications for the switchgear must be observed.           |
| 10.13 Mechanical function  | The device meets the requirements, provided the information in the instruction leaflet (IL) is observed. |


## **Technical data ETIM 5.0**


Low-voltage industrial components (EG000017) / Front element for push button (EC000221)


Electric engineering, automation, process control engineering / Low-voltage switch technology / Command and alarm device / Front element for push-button actuators (ecl@ss8-27-37-12-10 [AKF028010])

| Colour button                         |    | Without button plate |
|---------------------------------------|----|----------------------|
| Number of command positions           |    | 1                    |
| Construction type lens                |    | Round                |
| Hole diameter                         | mm | 22                   |
| Width opening                         | mm | 22                   |
| Height meter opening                  | mm | 6                    |
| Degree of protection (IP), front side |    | IP67                 |
| Type of button                        |    | Flat                 |
| Suitable for illumination             |    | No                   |
| Switching function latching           |    | No                   |
| Spring-return                         |    | Yes                  |
| With front ring                       |    | Yes                  |
| Material front ring                   |    | Plastic              |
| Colour front ring                     |    | Chrome               |

# **Dimensions**







Actuating and indicator elements Base fixing

## **Additional product information (links)**

## IL04716002Z (AWA1160-1745) RMQ-Titan System

IL04716002Z (AWA1160-1745) RMQ-Titan System

ftp://ftp.moeller.net/DOCUMENTATION/AWA\_INSTRUCTIONS/IL04716002Z2013\_08.pdf