## Carflex<sup>®</sup> Liquidtight Flexible Conduit and Accessories

**Product Overview** 

Liquidtight Flexible Nonmetallic Conduit provides superior wire protection in harsh, damp environments. Carflex® Conduit is non-conductive, non-corrosive and resistant to oil, acid, ozone and alkaline. Carflex® Conduit is strong and lightweight and because it weighs 50% less than metallic systems, it's easy to handle, transport and install. Carflex® is ideal for industrial, air conditioning, heating and outdoor lighting applications.

## **Features**

- Non-conductive and non-corrosive
- · Lightweight for easy handling, transportation and installation
- Crush, abrasion and strain resistant
- Provides superior wire protection
- · Smooth interior ideal for pulling cable
- No jagged edges
- Maintains internal I.D. even in tight radius bends
- Type LFNC-B
- Resistant to oil, acid, ozone and alkaline
- CSA Certified as per Section 12-1300 of the Canadian Electrical Code, Part 1
- Sequentially marked footage
- Suitable for use at conduit temperatures of 80°C dry, 60°C wet and 60°C oil

Note: Liquidtight flexible conduits, metallic and nonmetallic, in contrast to rigid PVC conduit and electrical nonmetallic tubing, do not have wire temperature limitations. Any temperature rated wire (for example, 90° wire) can be used as long as the temperature conditions marked on the conduit are not exceeded.



## **Applications**

- Control and motor
- Air conditioning and heating
- Computer power distribution
- Machine tools
- Console wiring
- Transformer connections
- Outdoor lighting





Coils								
Cat. No.	Nom. Size (in.)	Avg. O.D. (in.)	Avg. I.D. (in.)	Length Coil (ft.)	Std. Coil Wt. (lb.)			
15004-100	3/8	0.700	0.4890	100	11.70			
15005C-025	1/2	0.830	0.6270	25	3.25			
15007-100	3/4	1.040	0.8250	100	18.00			
15007C-025	3/4	1.040	0.8250	25	4.25			
15008-100	1	1.302	1.046	100	28.00			
15009-100	1-1/4	1.645	1.385	100	37.60			
15010-50	1-1/2	1.882	1.580	50	22.55			
15010-100	1-1/2	1.882	1.580	100	47.80			
15011-050	2	2.357	2.025	50	34.10			

Standard colou
----------------

Reels								
Cat. No.	Nom. Size (in.)	Avg. O.D. (in.)	Avg. I.D. (in.)	Length Reels (ft.)	Std. Reel Wt. (lb.)			
15004-001	3/8	0.700	0.4890	1000	145.0			
15005-001	1/2	0.830	0.6270	1000	157.0			
15007-001	3/4	1.040	0.8250	1000	212.0			
15008-500	1	1.302	1.046	500	155.0			
15009-200	1-1/4	1.645	1.385	200	100.0			
15010-150	1-1/2	1.882	1.580	150	95.7			
15011-100	2	2.357	2.025	100	94.6			