


## Grounding

### Ground Rod Clamps



Cat. No.	Water Pipe Size (in.)	Dimensions (in.)		Galv. Steel (in.)	Copper Clad (in.)
		Min.	Max.		
<b>Ground Clamps (Zinc alloy body / Steel screws)</b>					
<b>CI3106</b>	1/2 to 1	10 sol.	2 str.	5/8 to 1 *	N/A
<b>Ground Clamps (Zinc / Steel)</b>					
<b>CI3108</b>	1/2 to 1	10 sol.	2 str.	5/8 to 1 *	N/A
For connecting grounding conductor to either galvanized steel rod or water pipe.					
<b>Ground Clamps (Brass body / brass screws)</b>					
<b>CI3110U</b>	1/2 to 1	10 sol.	2 str.	5/8 to 1 *	5/8 to 1
For connecting grounding conductor to either galvanized steel rod, copper clad rod or water pipe. CSA certified for wet locations and for direct burial.					
<b>Ground Clamps (Brass body / brass screws)</b>					
<b>CI3112U</b>	1-1/4 to 2	10 sol.	2 str.	—	—
For connecting grounding conductor to water pipe. CSA certified for wet locations and for direct burial * Reversible					



CI3108



CI3106



CI3110U



CI3112U

## Grounding

### Ground Rod Clamps

CIGRC-58



Cat. No.	Water Pipe Size	Dimensions (in.)		Galv. Steel (in.)	Copper Clad (in.)
		Min.	Max.		
<b>Ground Rod Clamps (Bronze body / brass screws)</b>					
CIGRC58	N/A	8 sol.	1/0 str.	5/8	5/8
CIGRC34				3/4	3/4

For connecting grounding conductor to either galvanized steel rod or copper clad rod  
CSA certified for wet locations and for direct burial

JAB12



Cat. No.	Dimensions (in.)		Dimensions (in.)				Thread Size UNC-2A
	in.	mm	Min.	Max.	Min. (mm <sup>2</sup> )	Max. (mm <sup>2</sup> )	
<b>Ground Rod Clamps</b>							
<b>Socket Type</b>							
JAB12	1/2	12.7	10 sol.	2 str.	5.2	33.6	7/16-14
JAB34C	3/4+5/8	15.8	8 sol.	3/0 str.	8.3	95.0	7/16-14
JAB1	1	25.0	8 sol.	4/0 str.	8.3	107.1	7/16-14
<b>Hex Head Bolt</b>							
JAB12H	1/2	12.7	10 sol.	2 str.	5.2	33.6	7/16-14
JAB58H	5/8	15.8	8 sol.	1/0 str.	8.3	53.4	7/16-14
JAB34H	3/4	19.0	8 sol.	1/0 str.	8.3	53.4	7/16-14
JAB1H	1	25.0	8 sol.	4/0 str.	8.3	107.1	7/16-14

Cast of high strength corrosion-resistant copper alloy. Both hex head and socket set screw available. Long bearing surface of clamp on ground wire secures ground connection UL listed for direct burial.

G3



Cat. No.	Dimensions (in.)		Dimensions (in.)				Thread Size UNC-2A
	in.	mm	Min.	Max.	Min. (mm <sup>2</sup> )	Max. (mm <sup>2</sup> )	
<b>Type G - Budget Line Ground Rod Clamps</b>							
G3*	3/8	9.5	10 sol.	4 str.	5.2	21.1	5/16-18
G4	1/2	12.7	10 sol.	2 str.	5.2	33.6	3/8-16
G5	5/8	15.8	10 sol.	2 str.	5.2	33.6	3/8-16
G6	3/4	19.0	10 sol.	2 str.	5.2	33.6	3/8-16


A dependable ground connection offered at a substantial saving. Cast of high strength corrosion-resistant copper alloy. Hex head bolts. Simplified compact design will make a lasting trouble free connection UL listed for direct burial. \* Not CSA certified

## Grounding

### Ground Bushings and Accessories



CI2604



Cat. No.	Trade Size (in.)	Ground Wire Size (AWG)
<b>Insulated Grounding Bushings</b>		
CI2604	1/2	14-6
CI2606	3/4	14-6
CI2608	1	14-6
CI2610	1-1/4	14-4
CI2612	1-1/2	14-4
CI2616	2	6-1/0
CI2620	2-1/2	6-1/0
CI2624	3	2-4/0
CI2628	3-1/2	2-4/0
CI2632	4	2-4/0

With solid copper lug

## Grounding

### Ground Electrode Plates, Boxes and Wedge Clamps

51628



Cat. No.	Description
<b>Ground Electrode Boxes</b>	
51628	Pregalvanized steel
51629	Hot dip galvanized steel
51628-ALTA	Ground electrode box for Alberta only

14 gauge steel 10 in. diameter, 12 in. depth.


W20-1



Cat. No.	Conductor Range			Typical Tensile Values	
	ACSR	AL	AAAC	Conductor	Value (lb.)
<b>Type W - Aluminum Service Wedge Clamps for use with ACSR, AL, AAAC Conductor</b>					
W20-1	1/0	2/0 str.-2 sol.	1/0-4	1/0-6 x 1 ACSR	1800
W20-1-AN	1/0	2/0 str.-2 sol.	1/0-4	1/0-6 x 1 ACSR	1800
W40-1	4/0-2/0	4/0 str.-2/0 sol.	4/0-2/0	4/0-6 x 1 ACSR	1900
W40-1B	4/0-2/0	4/0 str.-2/0 sol.	4/0-2/0	4/0-6 x 1 ACSR	1900

W40 series clamps rated 850 lb. ultimate tension for 1/0 ACSR, AL or AAAC.

1016TB



- 1/4 in. hot dipped galvanized
- As efficient as two ground rods
- Must be buried at least 24 in. below finished grade level according to CEC rule 10-700

Cat. No.	Description	Wire Range
<b>Ground Electrode Steel Plates</b>		
1016TB	Galvanized grounding plate	8 sol. to 1/0 str.
1016BTB	Galvanized grounding plate (Complete with ground rod clamp)	8 sol. to 1/0 str.
1016TB-NG *	Grounding plate (Not galvanized)	8 sol. to 1/0 str.
1016BTB-NG *	Grounding plate (Not galvanized) (Complete with ground rod clamp)	8 sol. to 1/0 str.

10 in. x 16 in. x 1/4 in. thick. \* Not CSA certified

