

# CADDY® ROD LOCK Threaded Rod Mounting System



## CADDY® ROD LOCK Strut, Perforated

- CADDY® ROD LOCK technology allows for the quick creation, installation, and adjustment of multi-level trapeze assemblies
- Ready to use out of the box and eliminates the need for cutting and preparing sections of strut
- Easy “push-to-install” design allows installers to simply push the threaded rod through the mounting hole, instantly holding it in position
- Integrated adjustment nut enables fine tuning the system height up or down
- Lock nut can be finger tightened, locking the rod in place
- Works with all accessories that fit standard A or C type strut channels



Patent No.: 8,132,767  
8,434,725  
Patent Pending

Material: Steel  
Finish: Pregalvanized, Electrogalvanized

Part Number	Description		
Strut Type: A			
CRLP237L14	A Strut, 3/8" Rod, 16"	2,668 lb	5 pc
CRLP237L18	A Strut, 3/8" Rod, 20"	2,075 lb	5 pc
CRLP237L22	A Strut, 3/8" Rod, 24"	1,698 lb	5 pc
CRLP237L26	A Strut, 3/8" Rod, 28"	1,437 lb	5 pc
CRLP237L38	A Strut, 3/8" Rod, 40"	983 lb	5 pc
CRLP237L50	A Strut, 3/8" Rod, 52"	642 lb	5 pc
Strut Type: C			
CRLP137L14	C Strut, 3/8" Rod, 16"	789 lb	5 pc
CRLP137L18	C Strut, 3/8" Rod, 20"	613 lb	5 pc
CRLP137L22	C Strut, 3/8" Rod, 24"	494 lb	5 pc
CRLP137L26	C Strut, 3/8" Rod, 28"	354 lb	5 pc
CRLP137L38	C Strut, 3/8" Rod, 40"	166 lb	5 pc

Static loads are assumed to be uniformly distributed and include a hole factor of 0.92.  
The load applied to CADDY ROD LOCK Strut should include a factor of safety appropriate for the application in which the strut is being used.  
CADDY ROD LOCK Strut must be installed with the open side of the channel facing up.  
For indoor applications only.

