



H-Tap Connectors
T&B Catalog Number:

WR279

UPC Number:

78378610007

Status:

Active

Description:

Aluminum Wide Range H-Type Compression Connector Main: 2/0-1 AC-SR, 3/0-1/0 Str., 4/0-2/0 Sol. Tap: 2/0-1 ACSR, 3/0-1/0 Str., 3/0-2/0 Sol. Die: D, D3


Features

Made of 1350 Aluminum alloy to provide high strength and conductivity. Prefilled with oxide inhibitor held captive in the rib/connection area.

Enables excellent connector contact without distorting the conductor's shape.

Fold-in tabs provide positive tab interlock as tool closes.

RUS accepted and complies with ANSI C119.4



General

Style	Type WR - Supplemental O and D Die Connectors
Material	Aluminum
Standard Conductor Main - ACSR	2/0, 1/0, 1
Standard Conductor Main - Stranded	3/0, 2/0, 1/0
Standard Conductor Main - Solid	4/0, 3/0, 2/0
Standard Conductor Tap - ACSR	2, 4, 6
Standard Conductor Tap - Stranded	1, 2, 3, 4, 6
Standard Conductor Tap - Solid	1/0, 1, 2, 4, 6
Compact Conductor Main - ACSR	3/0, 2/0
Compact Conductor Main - Stranded	3/0
Compact Conductor Tap - ACSR	2, 4, 6
Compact Conductor Tap - Stranded	2, 3, 4, 6

Dimension Information

Length (inches)	1 13/16"
Conductor Diameter Main Max.	0.470
Conductor Diameter Main Min.	0.336
Conductor Diameter Tap Max.	0.470
Conductor Diameter Tap Min.	0.336

Tooling

Application Tools	JB12A, JB12B, 12A, Y-35
Connector Die	D
No. Indents Mechanical Tool	5
No. Indents Hydraulic Tool	2

Packaging

T&B Inner Pack	25
Package in Units	250
T&B Sold in UOM	Each
T&B Weight Per UOM	15.63 lbs. per 100

Certifications

RoHS Compliance	Yes
-----------------	-----

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com