BE1, BE2 SERIES D9

BE2 Series


200 A (main lugs) 600 V; multiple position – 100 A per position stud type



NOTE: Supply from an underground network often requires use of stud type connector. Consult your local utility.

Product specifications

- Conductor range: line: 6 AWG-250 kcmil, load: 6-1/0 AWG
- Aluminum tunnel type connectors for both line and load sides
- Factory prebussed from main lugs to each position
- Combination overhead-underground supplied with hub opening closure plate for underground service
- Hubs to be ordered separately (refer to pages D57–D58)
- Supplied with screw type rings
- Weatherproof Type 3R enclosure
- · Primarily used in: All provinces




Dimensions (in.) Weight each Meter position Н W D lb Cat. no. kg 4 Jaw Left-hand entry Right-hand entry BE2-V BE2-VH 14% 161/2 8.1 2 position 5**¾16** 18 BE3-V BE3-VH 3 position 14% 2413/16 53/16 26 11.8 BE4-V BE4-VH 4 position 14% 331/8 53/16 34 15.4 BE5-V BE5-VH 5 position 14% 411/16 5³⁄16 42 19.0

BE6-V BE6-VH 6 position 14% 49% 5% 50 22.7

Factory-installed accessories

Include: -5 5th jaw, standard capacity, 9 o'clock position

Diagrams



BEC Series

200 A (main lugs) 600V; multiple position – 100 A per position stud type



Product specifications

- Conductor range: line: ½ in. studs supplied, load: 6-1/0 AWG
- · Aluminum tunnel type connectors load side; stud ½ in. line side
- · For underground service only
- Factory prebussed from main lugs to each position

- Supplied with screw type rings
- Weatherproof Type 3R enclosure
- Primarily used in: B.C., *Sask. (extended enclosure), Man., Ont., Que.



Approved for copper or aluminum

		Meter position		Dimensions (in.)		Weight each	
Cat. no.			Н	W	D	lb	kg
4 Jaw							
Left-hand entry	Right-hand entry						
BEC2-V	BEC2-VH	2 position	15 1/8	243/16	5	27	12.2
BEC2-VA*	BEC2-VAH	2 position comes with connector (tunnel type)	15½	243/16	5	27	12.2
BEC2-VE*	BEC2-VEH	2 position extended enclosure	20 1/ 16	243/16	5	27	12.2
BEC3-V	BEC3-VH	3 position	15½	33 ½	5	35	15.9
BEC3-VA*	BEC3-VAH	3 position comes with connector (tunnel type)	15½	33 ½	5	35	15.9
BEC3-VE*	-	3 position extended enclosure	20 1/ 16	331/8	5	35	15.9
BEC4-V	BEC4-VH	4 position	15½	417⁄16	5	43	19.5
BEC4-VA*	BEC4-VAH	4 position comes with connector (tunnel type)	15½	411⁄16	5	43	19.5
BEC4-VE*	-	4 position extended enclosure	201/16	417⁄16	5	43	19.5
BEC5-V	BEC5-VH	5 position	15½	49%	5	51	23.1
BEC6-V	BEC6-VH	6 position	15½	57 5 /8	5	59	26.8
Factory installed acc	cessories						
Include: -5	5 th jaw, standard capacity, 9 o'clock position						

* Note: Models with suffix -VA and -VAH = tunnel type connectors on line side provided instead of studs (required by B.C. Hydro). Conductor range: line: 1–1/0 AWG, load: 6–1/0 AWG.

Cross reference

Underground meter required by BC Hydro standard

Not accepted by BC Hydro for underground application	Required by BC Hydro for underground applications		
BE2-V	BEC2-VA		
BE3-V	BEC3-VA		
BE4-V	BEC4-VA		
BEC2-VH	BEC2-VAH		
BEC3-VH	BEC3-VAH		
BEC4-VH	BEC4-VAH		
BEC2-V	BEC2-VA		
BEC3-V	BEC3-VA		
BEC4-V	BEC4-VA		
BEC2-VH	BEC2-VAH		
BEC3-VH	BEC3-VAH		
BEC4-VH	BEC4-VAH		

