



Centium T5HO

CENTIUM ELE BALLAST (2) F39T5/HO 120-277V

No matter what the conditions require, operating at a variety of line voltages between 120V to 480V, whether located in high ambient temperature environments (requiring a 90° C rating) or not, our family of Philips Advance Centium ballasts are ideal for a wide variety of applications.

Product data

• General Characteristics

Lamp Type	F39T5/HO
Number of Lamps	1/2 piece
Input Voltage	120-277 V
Line Frequency	50/60 Hz
Ballast Type	Electronic Fluorescent
Base Model	ICN2S39T
Housing	T
Housing Dimensions	14.17" x 1.18" x 1.06"
Housing Material	Metal
Suitable for Outdoor use?	Yes
Starting Method	Programmed Start
Family Name	Centium

• Operating Characteristics

Automatic restart	Yes
Ignition time	1.5 s
Input Power Gear	87-85 W
Ballast factor	1 -
Ballast Efficacy Factor	1.15 -
Power Factor	0.98
Lamp Current Crest Factor	1.7 -
Sound Rating	A
Max THD	10 %

• Wiring Characteristics

Color input terminals	BLK & WHT
Color output terminals	RED, YEL & BLU
Connector type	Poke-In
Wire Striplength	0.375 mm
Lamp Connection	Series
Wire Gauge	18AWG

Wire Length by Color	No wires
Wire Type	Solid
Allowed Wiring Config(Remote)	Yes
Allowed Wiring Config(Tandem)	Yes
Allowed Wiring Config(Through)	Yes
Max Dist. Ball to Lamp(Remote)	20'
Max Dist. Ball to Lamp(Tandem)	Blue = 20'
Max Dist. Ball to Lamp(Through)	Blue = 20'

• System Chars on driver level

Rated Lamp Watts	39W
------------------	-----

• Temperature Characteristics

T-case maximum	70 C
----------------	------

• Product Dimensions

Length A1	14.17 in
Length A2	13.78 in
Width B1	1.18 in
Height C1	1.06 in

• Approval & Application Chars


EMC Immunity	FCC Non-Consumer
Approbation Marks	UL, CSA, RoHS
UL Listed	Yes
CSA certificate	Yes

CEC Listing	No
CEE Rated	No
Circle E logo	No
CSA E	No
cUL certificate	No
DOE	No
Energy Star	No
FIDE Certificate	No
NEMA Premium	No
NOM certificate	No
RoHS Compliant	Yes
SASO Certificate	No
UL Recognized	No

• Product Data


Product number	ICN2S39T35M
Full product name	ELE BALLAST (2) F39T5/HO 120-277V
Short product name	ELE BALLAST (2) F39T5/HO 120-277V
Pieces per Sku	1
Skus/Case	18
Bar code on pack	781087131756
Bar code on case	50781087131768
Logistics code(s)	913701253202
eop_net_weight_pp	0.441 kg

Dimensional drawing



CENTIUM ELE BALLAST (2) F39T5/HO 120-277V

Product	A1 (Norm)	A2 (Norm)	A3 (Norm)	B1 (Norm)	C1 (Norm)
ELE BALLAST (2) F39T5/HO 120-277V	14.17	13.78	-	1.18	1.06



For 1 lamp operation, do not use yellow leads



© 2015 Koninklijke Philips N.V. (Royal Philips)
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2015, August 29
data subject to change