


Nonmetallic Core

Type LNM-P – Type A



Trade Size (in.)	Cat. No.	Reel Content (m)	Cat. No.	Reel Content (m)	Cat. No.	Reel Content (m)	Inside Dia.		Outer Dia.		Inside Bend Radius		Wt. kg/30m
							Min.	Max.	Min.	Max.	in.	(mm)	
							in. (mm)	in. (mm)	in. (mm)	in. (mm)	in.	(mm)	
3/8	LNMP038-75	75	LNMP038-150	150	LNMP038-300	300	0.485(12.32)	0.505(12.83)	0.755(19.18)	0.775(19.69)	2.5	(63.5)	7
1/2	LNMP050-60	60	LNMP050-150	150	LNMP050-300	300	0.620(5.08)	0.640(16.26)	0.910(23.11)	0.930(23.62)	3.0	(76.2)	10
3/4	LNMP075-50	50	LNMP075-150	150	-	-	0.815(20.70)	0.835(21.21)	1.150(29.21)	1.170(29.72)	4.0	(101.6)	14
1	LNMP100-30	30	LNMP100-120	120	-	-	1.030(26.16)	1.055(26.80)	1.415(35.94)	1.440(36.58)	6.0	(152.4)	19
1-1/4	LNMP125-30	30	LNMP125-60	60	-	-	1.370(34.80)	1.395(35.43)	1.800(45.72)	1.825(46.36)	7.0	(177.8)	28
1-1/2	LNMP150-15	15	LNMP150-45	45	-	-	1.585(40.26)	1.620(41.15)	2.045(51.94)	2.080(52.83)	8.0	(203.2)	36
2	LNMP200-15	15	LNMP200-30	30	-	-	2.075(52.71)	2.100(53.34)	2.555(64.90)	2.590(65.79)	9.0	(228.6)	54

Type LNM-P

This nonmetallic liquidtight conduit is ideally suited for continuous flexing situations. It is often specified in "Power Track" or cable carrier installations and on industrial robots. It does not contain a metal core which could fatigue from repeated flexing or vibration.

Construction

LNM-P is of the Layered, Type-A construction which incorporates a smooth seamless inner core of flexible PVC that is bonded to a covering of flexible PVC. Between these layers is a woven nylon mesh for added reinforcement. The PVC material is a high quality flame-retardant compound which resists oils, mild acids and exposure to sunlight.

Applications

General Use:

In accordance with CEC Rule 12-1002 (1) the flexible metal conduit is permitted in or on buildings of either combustible or non-combustible constructions.

Restriction and Exception:

CEC Rule 12-1004 (a): "12 (3/8) trade size flexible metal conduit shall be permitted to be used for runs of not more than 1.5 m (5 ft.) for the connection of equipment." and CEC Rule 12-1004 (b): "12 (3/8) trade size liquidtight flexible conduit may be used as permitted by this code."

Securements with straps:

CEC Rule 12-1010 (3): "When flexible metal conduit is installed, it shall be secured at intervals not exceeding 1.5 m (5 ft.) and within 300 mm (12 in.) on each side of every outlet box or fitting except where flexible metal conduit is fished and except for lengths of not over 900 mm (3 ft.) at terminals where flexibility is necessary."

Conductor fill:

CEC Rule 12-1014 defines the maximum number of conductor, the CEC Tables 6 provides the maximum number of conductors of one size in trade sizes of conduit, CEC Table 8 provides the maximum allowable per cent conduit fill, and CEC Table 9 provides the cross-sectional areas of conduit.

Specific Use and applications:

Elevators, Hoistways, in accordance with CEC Rules 38-021 (1) (a) (1) and 38-0221 (1) (a) (iv)

Elevators, Cars, in accordance with CEC Rules 38-021 (1) (b) (v)

Elevators, Within Machine Rooms, Control Rooms and Machinery Spaces and Control Spaces, in accordance with CEC Rule 38-021 (1) (c) (1)

Elevators, Counterweights, in accordance with CEC

Rule 38-021 (1) (d)

Escalators, in accordance with CEC Rule 38-021 (2)

Lifts for persons with physical disabilities, in accordance with CEC Rule 38-021 (3)

Theater installation, in accordance with CEC Rule 44-102 (1)

Working temperatures

-20°C to 60°C

Listing / Certification

Listed. Conforms to UL Standard ANSI/UL 1660 type A

Certified. Conforms to CSA 22.2 No. 227.2 type A

Standard Colour


Safety Orange. Also available in Black and Grey. Part numbers listed designate Orange jacket.

Fittings

Fittings for Layered Conduit are for that conduit only and are so identified by the marking "FNMC-A".

Recommendation:

"Suitable for use with 3700 Series, Type A, Metal Fittings from Thomas & Betts". Refer to pages B101 to B103.



LNM-P TYPE A

Nonmetallic Core

Type NMC – Type B



Recommended industrial applications:

- Machine tools
- Motor hookups
- Food processing equipment
- Extensions from wireways
- Sensor and microswitch wiring found in control consoles

Type NMC

A general purpose nonmetallic liquidtight conduit offers excellent protection to wiring from abrasion, sunlight, mild acids, alkaline and oils. Often used for air conditioning hook-ups and other outdoor applications.

Construction Type B

NMC is of the helically wound integral Type B construction. It contains a spiral of rigid PVC reinforcement imbedded within the flexible PVC wall.

Cat. No.	Trade Size (in.)	Inside Bend Radius (in.)	Weight (lb/100ft)	Coil Footage Length	I.D. (in.)		O.D. (in.)	
					Min.	Max.	Min.	Max.
NMC038TB	3/8	2.00	10	100	0.484	0.504	0.690	0.710
NMC050TB	1/2	3.25	11	100	0.622	0.642	0.820	0.840
NMC075TB	3/4	4.25	15	100	0.820	0.840	1.030	1.050
NMC100TB	1	6.50	25	100	1.041	1.066	1.290	1.315
NMC125TB	1-1/4	8.00	34	100	1.380	1.410	1.630	1.660
NMC150TB	1-1/2	9.00	42	50	1.575	1.600	1.865	1.900
NMC200TB	2	11.00	60	50	2.020	2.045	2.340	2.375
NMC050-1000TB	1/2	3.25	11	1000	0.622	0.642	0.820	0.840
NMC075-500TB	3/4	4.25	15	500	0.820	0.840	1.030	1.050

Use with Bullet® Liquidtight Fittings

Available in other colours. Consult your Regional Sales Office for details

Type NMC Specifications

Type NMC is intended for installation in accordance with CEC Rule 12-1300 to 12-1306 for Liquidtight Flexible Conduit.

-For containment of 600 volt and lower potential circuits.

Working Temperature

-20°C to 80°C/Dry 60°C/Wet 70°C/Oil

Listing / Certification



Listed. Conforms to Underwriters Laboratories Standard ANSI/UL 1660 type B



Certified. Conforms to CSA 22.2 No. 227.2 type B. The 3/8 through 1-1/4 in. trade sizes are listed and marked for direct burial and in poured concrete.

Standard Colour

Black

Type NMT – Tubing



Recommended industrial applications:

- Protection of fiber optic cable
- Installation of instrumentation and control cable
- Indoor/outdoor lighting
- Packaging equipment
- Marine and shipboard wiring
- Flexing—component wiring protection on robots, graphic arts equipment, etc.

Cat. No.	Trade Size (in.)	Inside Bend Radius (in.)	Weight (lb/100ft)	Coil Footage Length	I.D. (in.)		O.D. (in.)	
					Min.	Max.	Min.	Max.
NMT038TB	3/8	0.7	6	100	0.484	0.504	0.690	0.710
NMT050TB	1/2	0.9	8	100	0.622	0.642	0.820	0.840
NMT075TB	3/4	1.1	10	100	0.820	0.840	1.030	1.050
NMT100TB	1	1.3	15	100	1.041	1.066	1.290	1.315
NMT125TB	1-1/4	1.7	20	100	1.380	1.410	1.630	1.660
NMT150TB	1-1/2	1.9	26	50	1.575	1.600	1.865	1.900
NMT200TB	2	2.4	36	50	2.020	2.045	2.340	2.375

Available in other colours, consult your Regional Sales Office for details

Type NMT

Type NMT is an Extra Flexible Liquidtight Non-metallic Tubing. This lightweight tubing cuts easily and installs quickly. It is ideal for wiring protection in tight quarters and for tight bends. The thin flexible PVC skin allows greater movement for many OEM applications. Used for wiring harnesses, laboratory, equipment, fiber optics, etc.

Construction

Co-extruded from both flexible and rigid PVC. The rigid spiral PVC reinforcement is imbedded within the wall of the tubing.

Working Temperature

-20°C to 70°C

UL Recognized

Standard Colour

Black