



Steel Strand Automatic Splices

T&B Catalog Number:

ATSG516

UPC Number:

78378643282

Status:


Active

Description:

Automatic Tension Deadend Splice for Steel Strand Diameter 5/16 (7.94) for use on Utilites, Common, Siemens-Martin, High-Strength, Strand Rating 5/16 (6M)

Features

Built tough. The connectors can handle tensile loads in excess of 90 percent of the rated strength of the recommended strands. They also exceed 90 percent of the strand rated breaking strength (RBS). Pilot Cap and Jaw eliminate incorrect insertions. Aluminum cartridge and internal components are lubricated for long-term continuous performance and corrosion resistance.



General

Style	ATSG Splices
Material	Aluminum
Strand Rating	5/16 (6M)
Strand RBS LBS. (KN)	11,200 (49.82)

Dimension Information

Length (inches)	7.2
B (inches)	1.1
Strand Nominal Diameter Inches (MM)	5/16 (7.94)

Packaging

T&B Order Multiple	12
Package in Units	12
T&B Sold in UOM	Each
T&B Weight Per UOM	0.56 lbs. Each

Notes

Recommended for use on: Common grade, Siemens-Martin, High-strength utility grade, EHS, Galvanized, Bethalume, Aluminized steel strand (per ASTM A 474, A 475)

RBS rating listed is for 7 wire EHS strand.

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com