

Project: _____

Fixture Type: _____

Location: _____

Contact/Phone: _____

COMPACT FLUORESCENT STEP/NIGHT LIGHT

7W or 9W COMPACT
FLUORESCENT LAMP

ICPL813

PRODUCT DESCRIPTION

ICPL Housing is designed for use in insulated or non-insulated areas.

PRODUCT SPECIFICATIONS

Lamp One 7W or 9W twin tube CFL lamp.

Socket Horizontal mounted in housing.

Ballast 120V normal power factor magnetic • UL listed/CSA certified.

Trims Available in white baked enamel on steel • Fastens to housing with two torsion springs.

Labels UL listed for damp locations and IP • Union made
• UL Listed/CSA certified.

Testing All reports are based on published industry procedures; field performance may differ from laboratory performance.

Specifications subject to change without notice.


INSTALLATION

Real Nail 3 Bar Hangers Telescoping, Patented (US Patent D552,969) Real Nail® 3 system permits quick placement of housing anywhere within 24" O.C. joists or suspended ceilings • Integral T-bar notch and clip secures housing in suspended ceiling grid – no accessory clips required • 24" expansion stop allows quick placement of fixture in standard grid spacing • Bars scored in two locations for fast, clean breaking, allowing housing installation in tight applications • Bars captive to mounting frame • Edge-mounted for extra strength • Captive bugle-headed ring shank nail for quick one-step installation and easy removal with claw hammer for fixture relocation • Quick-Loc slot and oversized locking set screw lock fixture in position • Bar hanger foot contoured to align to bottom of construction joist • Alternate mounting holes included.

Junction Box Pre-wired junction compartment provided with (3) ½" knockouts with pryout slots and ground wire • 90° C supply connection.

Housing 22-gauge white painted steel • 8¼" L x 3½" H x 3½" D.

DIMENSIONS






8 3/4" X 3 3/4" WALL CUTOUT

ORDERING INFORMATION: Housing and trim can be ordered together or separate, but will always ship separately.

Example (Housing): **ICPL813 120**

Example (Trim): **840 WH**

Example (Together): **ICPL813 120 104 WH**

Series		Voltage		Trims		Trim Finish	
<input type="text" value="ICPL813"/>		<input type="text" value="120 120V"/>		<input type="text" value="104 Diffuse Glass Lens Step Light Trim"/>		<input type="text" value="WH White"/>	
							
							

Trim Size: 9 5/8" L x 4 7/8" H

Lamp Rating: 7W or 9W Twin Tube CFL.