


## Specification Guide


### Cable Fittings




L-16




CI70 / CI72




CI804 / CI816




CI2060 / CI2061




CI2104 / CI2116




CI2163




CI2166 / CI2172



CI2173 / CI2174



CI2175



Cat. No.	Trade Size (in.)	Clamping Range (in.)		Dimensions (in.)		
		Min.	Max.	A	B	C
<b>One Screw Connectors (Zinc Alloy)</b>						
CI70	3/8	0.13	0.70	1	1-1/8	1/2
L-16	3/8	0.12	0.63	1	—	—
CI71	1/2	0.33	0.95	1-3/8	1-1/2	1/2
CI72	3/4	0.60	1.15	1-1/2	1-13/16	1/2
<b>Two Screw Connectors (Zinc Alloy)</b>						
CI804	3/8	0.18	0.64	7/8	1-1/16	—
CI806	3/4	0.41	0.82	1-3/8	1-3/16	
CI808	1	0.50	1.04	1-1/8	2	
CI810	1-1/4	0.56	1.06	1-5/16	2-3/16	
CI812	1-1/2	0.63	1.60	1-1/2	2-5/8	
CI816	2	0.86	2.06	1-9/16	3	—
<b>Two Screw Connectors (Steel)</b>						
CI2060	3/8	0.11	0.60	1-1/2	5/8	—
CI2061	3/4	0.15	0.90	1-3/4	13/16	
<b>Two Screw Connectors (Cast Aluminum Body and Clamp)</b>						
CI2104	1/2	0.45	0.59	1-3/16	1-3/8	19/32
CI2106	3/4	0.55	0.78	1-3/8	1-11/16	5/8
CI2108	1	0.69	1.01	1-1/2	1-15/16	3/4
CI2110	1-1/4	0.84	1.33	1-1/2	2-3/8	9/16
CI2112	1-1/2	1.06	1.57	1-9/16	2-3/4	5/8
CI2116	2	1.38	2.06	1-3/4	3-1/4	3/4
<b>One Screw Connector (Zinc Alloy)</b>						
CI2163	3/8	0.35	0.61	1	1-5/16	7/16
<b>One Screw Connectors (Aluminum)</b>						
CI2166	1/2	0.50	0.90	1-9/16	1-11/16	7/16
CI2167	3/4	0.71	1.10	1-11/16	1-7/8	7/16
CI2169	1	1.16	1.50	2	2-1/2	1/2
CI2170	1-1/4	1.32	1.77	2-3/8	2-7/8	5/8
CI2171	1-1/2	1.77	2.05	2-1/2	3-1/4	5/8
CI2172	2	2.10	2.54	2-11/16	3-3/4	11/16
<b>Two Screw Connectors (Aluminum)</b>						
CI2173	2-1/2	2.05	3.07	3-1/8	4-9/16	3/4
CI2174	3	2.25	3.57	3-3/8	5-5/16	15/16
<b>Duplex Connectors (Zinc Alloy)</b>						
CI2175	3/8	0.15	0.65	9/16	5/8	3/8


Technical improvements are constantly taking place in the electrical industry. Cable manufacturers are changing their products from time to time. Accordingly, it is strongly suggested that you verify the cable size with the cable manufacturer prior to selecting a fitting.

## Specification Guide


### Cable Connectors




CI2210 / CI2236




CI2238 / CI2240




CI3360




CI4004




CI4000




CI4090



CI4040



CI9049



Cat. No.	Trade Size	Clamping Range		Dimensions		
		Min.	Max.	A	B	C
<b>90° Connectors (Zinc Alloy)</b>						
CI2210	3/8	0.40	0.63	1-3/8	3/4	3/8
CI2211	1/2	0.65	0.97	1-11/16	1-1/16	3/8
CI2214	3/4	0.77	1.12	1-3/4	1-1/8	1/2
CI2216	1	1.10	1.57	2	1-5/8	5/8
CI2218	1-1/4	1.27	1.75	3-3/8	2-1/8	5/8
CI2234	1-1/2	1.70	2.15	5-1/4	3-1/4	3/4
CI2236	2	2.00	2.62	5-3/8	3-1/4	3/4
<b>90° Connectors (Aluminum)</b>						
CI2238	2-1/2	2.50	3.08	6-1/4	5-1/2	3/4
CI2240	3	2.95	3.55	7-1/4	6-5/8	3/4
<b>Nonmetallic Connector</b>						
CI3360	1/2	0.30	0.60	1-5/16	1-1/16	7/16
<b>Two Screw Connector (Aluminum)</b>						
CI4000	4	4.40	4.55	4-7/8	5-3/4	7/8
<b>Nonmetallic Connector</b>						
CI4004	1/2	0.21	0.42	15/16	7/8	3/8
<b>One Screw Connectors (Steel)</b>						
CI4040	3/8	0.19	0.57	15/16	7/8	—
CI9049	3/8	0.13	0.37	1-3/8	5/16	—
<b>90° Connector (Aluminum)</b>						
CI4090	4	4.17	4.62	8-1/4	6	1

Technical improvements are constantly taking place in the electrical industry. Cable manufacturers are changing their products from time to time. Accordingly, it is strongly suggested that you verify the cable size with the cable manufacturer prior to selecting a fitting.