


**Ring Terminal  
T&B Catalog Number:**

G2-516  
78621080368  
Active

**UPC Number:**  
**Status:**  
**Description:**

Non-Insulated - Tubular Ring Terminal For Wire Range 2 Stud Size 5/16, Metallic


**WEB\_USE**

US Cutsheet PDF Catalog Link

<http://www-public.tnb.com/contractor/docs/stakon.pdf>

**Features**

These non-insulated ring terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire).


**General**

|                 |                         |
|-----------------|-------------------------|
| Insulation Type | Non-Insulated - Tubular |
| Terminal Series | G                       |
| Material        | Copper                  |
| Finish          | Electro -Tin Plated     |
| Color           | Metallic                |
| Wire Range      | 2                       |
| Stud Size       | 5/16                    |

**Dimension Information**

|                 |      |
|-----------------|------|
| Stock Thickness | .05  |
| A (inches)      | 1.59 |
| B (inches)      | .69  |
| C (inches)      | .40  |
| M (inches)      | 1.26 |

**Specifications**

|                     |           |
|---------------------|-----------|
| Temperature Rating  | 150°C     |
| Voltage Rating      | 600V      |
| Flammability Rating | UL 94 V-0 |

**Tooling**

|                   |                             |
|-------------------|-----------------------------|
| Tool Charts       | Available on Website        |
| Application Tools | WT115A, TBM6, TBM6S, WT3185 |
| Recommended Tool  | ERG4008, TBM6S              |

**Packaging**

|                    |                   |
|--------------------|-------------------|
| T&B Order Multiple | 10                |
| T&B Inner Pack     | 10                |
| Package in Units   | 100               |
| Package Type       | Standard          |
| T&B Sold in UOM    | Each              |
| T&B Weight Per UOM | 3.69 lbs. per 100 |

**Application Support**

|                    |                      |
|--------------------|----------------------|
| T&B Sales Drawings | wsd-000219           |
| Overview           | Available on Website |
| Wire Guide Tables  | Available on Website |

## Notes

Not available on Mylar Tape.

## Certifications

RoHS Compliance

Yes

## Certifications



File Nbr:

E9809

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)