
BD2 Series

200 A (main lugs) 600 V; multiple position – 200 A per position


Product specifications

- Conductor range: line: 6 AWG-250 kcmil, load: 6 AWG-250 kcmil
- Aluminum tunnel type connectors for both load and line sides
- Factory prebussed from main lugs to each position
- Supplied with hub opening closure plate for underground service
- Combination overhead underground
- Supplied with screw type rings
- Weatherproof Type 3R enclosure
- Primarily used in: All provinces



					Dimensio	ns (in.)	Weig	ht each
	Cat. no.	Cat. no.		н	w	D	lb	kg
BD2-V	4 Jaw							
	Left-hand entry	Right-hand entry						
	BD2-V	BD2-VH	2 position	15 ½	171/2	5 7⁄16	23	10.4
	BD3-V	BD3-VH	3 position	15 ½	26 ¼	5 %16	35	15.9
and the second	BD4-V	BD4-VH	4 position	15 ½	35	5 % 16	47	21.3
	BD2-VBC	BD2-VBCH	2 position for British Columbia	20	171⁄2	5 %	27	12.2

Diagrams



4, 1½, 2 and 2½ in. 4 places


Note: Pattern for bottoms. Left-hand entry is shown. For right-hand entry, unit is manufactured symmetrically with hub openings, knockout and line connections on right side.

BDA2-V Series

200 A (main lugs) 600 V; multiple position with blank compartment 200 A per position


Product specifications


- Conductor range: line: 6 AWG-250 kcmil, load: 6 AWG-250 kcmil
- Aluminum tunnel type connectors for load side
- Combination overhead and underground
- Hub opening closure plate for underground service
- Supplied with screw type rings
- Weatherproof Type 3R enclosure
- Primarily used in: Ontario only



				Dimensions (in.)			Weight each	
	Cat. no.		Meter position	н	w	D	lb	kg
BDA2-V	4 Jaw							
	Left-hand entry	Right-hand entry						
	BDA2-V	BDA2-VH	2 position	15 %	26 ¾	5¼	31	14.6

Diagrams





BDC Series

200 A (main lugs) 600 V; stud type multiple position with blank compartment 200 A per position

Copper

Copper

or aluminum

(SP

BDC2-VII

For u	ıse in	all pr	ovinces
-------	--------	--------	---------

Cat. no.			Dimensions (in.)			Weight each		
Left-hand entry	Right-hand entry	Meter position		w	D	lb	kg	
4 Jaw								
BDC2-V	BDC2-VH	2 position	15%	26¼	5 ¼	30	13.6	
BDC3-V	BDC3-VH	3 position	15%	35	5 ¼	42	19.0	
BDC4-V	BDC4-VH	4 position	15%	43 ¾	5 ¼	54	24.5	

Locking system outside meter section.

Cat. no.		Dimer	nsions	(in.)	Weight each		
Left-hand entry	Right-hand entry	Meter position	н	w	D	lb	kg
4 Jaw							
BDC2-VAILBC	BDC2-VAHILBC	2 position	20 ¾	26¼	5 ¼	30	13.6
BDC3-VAILBC	BDC3-VAHILBC	3 position	20¾	35	5 ¼	42	13.6
BDC4-VAILBC	BDC4-VAHILBC	4 position	20 ¾	43 ¼	5 ½	54	19.0

Product specifications

- Conductor range: line: single ½ in. studs to accommodate compression lugs (supplied by utility), load: 6 AWG-250 kcmil
- · Aluminum tunnel type connectors for load sides
- · For underground service only
- Factory prebussed from main lugs to each position
- Supplied with screw type sealing rings
- Weatherproof Type 3R enclosure
- · Primarily used in: All provinces

For use in Quebec					(5	or alu	iminum	
Cat. no.			Dime	nsions	(in.)	Weight each		
Left-hand entry	Right-hand entry	Meter position	н	w	D	lb	kg	
4 Jaw								
BDC2-VIL	BDC2-VHIL	2 position	15%	26¼	51⁄4	30	13.6	
BDC3-VIL	BDC3-VHIL	3 position	15 %	35	5 ¼	42	19.0	
BDC4-VIL	BDC4-VHIL	4 position	15 %	43 ¾	51⁄4	54	24.5	
Locking system	n incido motor cos	ion						

Locking system inside meter section.


Copper or aluminum

^H23%usin.

Conner

For use in On		e or a	luminum			
Cat. no.			Dimensio	ns (in.)	Weight e	
Left-Hand Entry	Meter Position	н	w	D	lb	kg
5 Jaw						
BDC2-5V	2 position	23%	26 1/4	55⁄16	30	13.6
BDC3-5V	3 position	23%	35	5 5⁄16	42	19.0
BDC4-5V	4 position	23 ¾	43 ¾	55⁄16	54	24.5

Locking system outside meter section.



For right-hand entry, unit is manufactured symmetrically with hub openings, knockouts for line connectors on right side.




BS4 Series

400 A (main lugs) 600 V; multiple position with blank compartment 200 A per position

Product specifications

- Conductor range: line: dual rated connectors for 1 x 4 AWG-600 kcmil or 2 x 1/0 AWG-250 kcmil, load: 6 AWG-250 kcmil
- Aluminum tunnel type connectors for both load and line sides
- Factory prebussed from main lugs to each position

- Combination overhead-underground
- Supplied with hub opening closure plate for underground service
- Larger hub opening requires use of 3 in., 3½ in. or 4 in. hubs unless BS052 adapter plate is used
- Supplied with screw type rings
- Weatherproof Type 3R enclosure
- Primarily used in: All provinces



						Dimensi	isions (in.) W		Weight each	
		Cat. no.		Meter position	н	w	D	lb	kg	
BS42-V		4 Jaw								
		Left-hand entry	Right-hand entry							
	1.121	BS42-V	BS42-VH	2 position	23%	26¼	5 %16	45	20.4	
		BS43-V	BS43-VH	3 position	23 %	35	5 5⁄16	59	26.8	
		BS44-V	BS44-VH	4 position	23 ¾	43 ¾	5 % 16	73	33.1	
V		BS45-V	BS45-VH	5 position	23 %	52 ½	5 % 16	87	39.5	
~		BS46-V	BS46-VH	6 position	23%	61¼	55⁄16	101	45.9	

Diagrams

