



KS90

by Burndy
Catalog ID: KS90

Prop 65 Notice

Copper Split Bolt, Cu: 12-10 AWG (Str) (Run & Tap).

Features: Compact, High Strength, High Copper Alloy SERVIT Split-Bolt Has Free-Running Threads And Easy To Grip Wrench Flats, Highly Resistant To Season Cracking And Corrosion, The SERVIT Provides Maximum Pressure And Assures A Secure Connection On All Combinations Of Run And Tap Conductors, Conductor Type: Run: Solid Copperweld, Commercial Stranded And Solid Copper, Tap: Solid Copperweld, Commercial Stranded And Solid Copper, Installation Torque: 80 IN-LB, Length: 0.85 IN, Cross Flats: 0.5 IN, Width: 0.38 IN

Product Details

General

Application	For Direct Burial Cables
Connector Type	Split Bolt
Installation Torque Recommended in-lb	80 in
Material	Copper
Plated	N
Plating Type	Unplated
Sub Brand	SERVIT
Trade Name	SERVIT®
Type	KS
UPC	781810015254
UPC 12 Digit	7818100152544

Dimensions

Dimension - B Length fraction	9/20 in
Dimension - B Length inch	.45 in
Dimension - Cross Flats inch	.50 in
Dimension - L Length Overall mm	22 mm
Dimension - Length Overall inch	0.85
Dimension - Width fraction	19/50 in
Dimension - Width inch	0.38 in
Dimension - Width mm	10 mm
Width	0.38 in

Conductor Related

Conductor - Copper Solid Run	8 AWG
Conductor - Copper Solid Run Range	10 AWG-12 AWG
Conductor - Copper Solid Tap	8 AWG
Conductor - Copper Solid Tap Range	16 AWG-10 AWG
Conductor - Copper Str Run	12 AWG;10 AWG

Conductor - Copper Str Run Range	12 STR. 10 STR.
Conductor - Copper Str Tap	16 AWG;14 AWG;12 AWG;10 AWG
Conductor - Copper Str Tap Range	16 STR.
Conductor - CopperWeld Solid Run	#10
Conductor - CopperWeld Solid Run Range	#10
Conductor - CopperWeld Solid Tap	#10
Conductor - CopperWeld Solid Tap Range	#10
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Run • CU C Str-Run • CU Weld C Solid-Run • CU Weld C Str-Run • CU C Str-Tap • CU Weld C Solid-Tap • CU Weld C Str-Tap • CU C Solid-Tap

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL 486A • UL486B
Standards - Industry Standards Met	<ul style="list-style-type: none"> • UL 486A • UL486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)