



Representative

Catalog Number: 3135
Product ID: 7TAA106020R0008
UPC Number: 78621003135
EAN Number: 05414363140887
Status: Active

Metal-Clad and Armored Cable Fitting, 90 Degree Bend, Trade Size 3/4 Inch, Knockout Size 3/4 Inch, Cable Range 0.906 to 1.093 Inch, Steel with Zinc Plating, Nylon Insulated

- All the advantages of the straight connector with only one screw to tighten, except in the larger sizes where there are two.
- A peep hole on top provides for easy inspection of the ABC bushing.
- Narrow design makes it easy to install connectors in adjacent knockouts.
- To connect and effectively bond armored cable or flexible metal conduit to a box or an enclosure.

North American Specifications (UNSPSC)

UNSPSC	39121419 Flex connectors
IGCC	4573 Flex connectors
Brand Name	T&B
Type	Armored Cable/Flexible Metal Conduit Fittings
Special Features	By Far The Easiest and Best to Install When Making Sharp Bends At The Enclosure or Equipments
Application	For Use with Armored Cable and Flexible Metal Conduit
Standard	UL E23018, CSA
Size	3/4 Inch
Connection	90 Degree
Conductor Range	0.906 to 1.093 Inch
Material	Steel
Finish	Electro Zinc Plated
Color	Metallic
Insulation	Nylon

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	3/4 inch
Model	90°-elbow
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Other
Material housing	Steel
Surface protection	Zinc coated
Thread length	29.37mm

Packaging

Inner Quantity	10
Inner Dimensions (inches)	4x4.5x6
Outer Quantity	50
Outer Dimensions (inches)	21.7x5.2x7
Weight Uom	30 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Technical Drawing / Data Sheet Canada	Available on Website

Header

3D Model

Available on Website

For further technical assistance, please contact us...

Thomas & Betts Canada
700, Thomas Avenue
Saint-Jean-sur-Richelieu, QC
J2X 2M9
www.tnb.ca

T&B Technical Support
<http://www.tnb.ca/en/contactus/?id=ALL>

Hours: 7h00 - 18h00
Monday-Friday