E-Z-Code°

EZL-100 Thermal Label Printer

EZ as 1-2-3...press, type, and print!

EZL-100[®] Thermal Label Printer

- One-touch hotkeys create labels instantly for wire wrapping, terminal blocks, device covers, patch panels, and labels in a series
- Symbols for common electrical and datacom applications, including ohm, ground, phone, data, and fax
- Five print sizes including XS, S, M, L, and XL
- Horizontal and vertical print orientation
- Automatically underlines the number <u>9</u> to prevent confusion on wire and cable
- Memory stores up to eight custom labels and automatically recalls last label
- Auto-shutoff saves battery life by turning printer off after five minutes (if idle)
- Backlit display can be turned on or off for use in low lighting conditions
- Multiple line printing of up to four lines per label
- Barcode printing of two of the most commonly used barcodes — Code-39 and Code-128
- Durable/non-smearing thermal transfer technology
- Multiple power sources uses six "AA" batteries or AC adapter (not included)
- Large display with 2-line x 15-character views (30 total)





At last, a label printer designed for electricians and the way they work! T&B's new EZL-100 Label Printer packs everything you need to make wire marking fast and simple.

T&B's EZL-100 printer features handy "Hot Keys," a one-touch method to make labels for wire wrapping, patch panels, labels in a series, terminal blocks, and more. There are also common electrical and datacom symbols at your touch. And its rugged design ensures years of use.

Best of all, our permanent-adhesive labels won't smear. You'll wrap up your job with attractive, easy-to read wire labels that'll make your work easier and safer. All for a price that's easy on your wallet.

..... Specifications

- Dimensions: 4.5" (114mm) W x 8.3" (212mm) H x 2.8" (70mm) D
- Power: 9V DC, using 6 "AA" batteries or AC adapter
- Weight: 2.0 lbs. (890 grams)
- batteries or AC adapter
- CAT. NO.
 DESCRIPTION

 EZL-100
 Printer (includes (1) ¾" white nylon, quick-load cassette tape, quick start card, and user manual). AC power adapter not included

 EZL-100-Kit
 Kit (includes EZL-Case, EZL-100 Printer (1), EZ-MP34 (1) and EZ-WN34, (1) tape, EZL-ADP adapter, and batteries

 EZL-Case
 Hard Case for EZL-100 Printer

 EZL-ADP
 Adapter for EZL-100 Printer 9V, 1.5A

Thomas Betts

United States Tel: 901.252.8000 800.816.7809 Fax: 901.252.1354 **Canada** Tel: 450.347.5318 Fax: 450.347.1976 Technical Services Tel: 888.862.3289

E-Z-Code[®]

EZL-75 Thermal Label Printer and EZL Printer Labels

Quick and cost-effective labeling solution!

EZL-75 Thermal Label Printer

If your labeling needs don't quite justify all the high-end features of T&B's EZL-100, now there's a lower cost solution for simple labeling. The EZL-75 thermal label printer is just as easy to use as the EZL-100. Simply type and print. Or don't even bother typing. Instead, use hot keys to choose among the EZL-75's built-in library of symbols and more than 150 commonly used words for security, location and voice/data/video labeling.



- Hot keys provide one-touch flagging for wires and cables and fixed-length labels for faceplates and security panels
- Incremental alpha and numeric printing makes printing distribution panel labels fast and simple
- 13-character backlit display enhances readability
- Multiple line printing supports up to 2 lines per label
- Durable bumper safeguards against damage in the tool box
- Uses the same label cassettes (up to $\frac{1}{2}$ " width) as EZL-100
- Specifications
- Dimensions: 4.5" (114mm) W x 7.5" (191mm) H x 2.1" (53mm) D
- Power: 9V DC, using 6 "AA" (not included)batteries or AC adapter
- Weight: 0.8 lbs. (363 grams)

CAT. NO.	DESCRIPTION
EZL-75	Printer (includes (1) ½" white nylon quick-load cassette tape, quick
	start card, and user manual. AC power adapter not included
EZL-ADP	Adapter for EZL-75 Printer 9V, 1.5A

Surface Applications		Vinyl and Flex Nylon	Perm. Polyester	Heat Shrink
Wire	9	•		•
Cable	====	•		•
Curved	\frown	•		
Smooth		•	•	
Flat		•	•	
Textured	\sim	•	•	
Highly Textured	\sim	•		
Length	Η	11.5'	18.0'	5.0"
Width	Ι	1/2", 3/" 3/"	3%", 1⁄2" 3⁄4"	1/4", 3/8" 1/2", 3/4"

High-performance labels that last!

Wire Marker Labels for EZL Printers

- · Perfect for wire and cable
- Print heat-shrink sleeves on the spot!
- Clear, non-smudging lettering
- Chemical/solvent resistant
- Available in yellow, white, and metallic markers
- Flame retardant, Polvolefin material, 3:1 shrink ratio
- · Easy-to-peel, split-back design



Easy barcode printing!

CAT. NO.	LABEL SIZE (IN.)	RECOMMENDED WIRE SIZE (AWG)	LENGTH
Clear Polyester			
EZ-CP12	1/2"	Flat Applications Only	18'
EZ-CP34*	3/11	Flat Applications Only	18'
Red Vinyl			
EZ-RV34*	3/11	Any	18'
White Permanent Polyester			
EZ-WP38	3/8"	Flat Applications Only	18'
EZ-WP12	1/2"	Flat Applications Only	18'
EZ-WP34*	3/4"	Flat Applications Only	18'
Metallic Permanent Polyester			
EZ-MP38	3/8"	Flat Applications Only	18'
EZ-MP12	1/2"	Flat Applications Only	18'
EZ-MP34*	3/4"	Flat Applications Only	18'
White Flexible Nylon			
EZ-WN12	1/2"	Any	12.5'
EZ-WN34*	3/1	Any	12.5'
Yellow Flexible Nylon			
EZ-YN12	1/2"	Any	12.5'
EZ-YN34*	3/"	Any	12.5'
Heat-Shrink White Polyolefin La	bels		
EZ-WHS14	1/4"	10 – 16	5'
EZ-WHS38	3/8"	6 - 14	5'
EZ-WHS12	1/2"	4 - 6	5'
EZ-WHS34*	3/11	2-4	5'
Heat-Shrink Yellow Polyolefin La	abels		
EZ-YHS14	1/4"	10 – 16	5'
EZ-YHS38	3/8"	6 - 14	5'
EZ-YHS12	1/2"	4 - 6	5'
EZ-YHS34*	3/1	2 – 4	5'

* Labels fit EZL-100 only.

Technical Services Tel: 888.862.3289

Thomas®Betts www.tnb.com

DANGER Do

OPERATE

Tel: 450.347.5318

United States Tel: 901.252.8000 800.816.7809 Fax: 901.252.1354

Canada Fax: 450.347.1976